

Vertical quick-action clamp

With open clamping arm and angular base



Application:

For quick clamping of workpieces.

Version:

- Galvanised and passivated
- Stainless steel rivet
- Ergonomic, oil-resistant handle with large hand rest and soft components.

Delivery:

With tempered and galvanised thrust bolt

Art. no.	26213 030
Size	3
Hole distance	24 mm
Bore diameter	6.5 mm
Clamping height	71 mm
Retaining force	1400 N
Max. tensile force	2500 N
Thumbscrew size	M8 x 45 mm



EAN-Code

4020772090333