

electronic pocket vernier calipers

Digital ABS slides CoolantProof IP67

Mitutoyo

Application:

For measuring external, internal, step and depth dimensions.

Execution:


- Digimatic
- ABSOLUTE system for reliable measurement
- High-contrast display

Advantage:

- High resistance to water and dust (protection class IP67)
- Survive temporary, complete immersion in water without damage

Delivery:

Delivered in box



Art. no.	32018 192
Brand	MITUTOYO
Manufacturer Part Number	500-712-20
Min./max. length measuring range	0-150 mm
Data transmission type	DIGIMATIC
Depth gauge rod	Flat
IP protection class	IP 67
With drive wheel	Yes
Error limit	0.02 mm
Length of jaw	40 mm
Design	Metric
Digit height	9 mm
Length of cross tips	21 mm
Digit increment	0.01 mm
Type of locating	With locking screw
Preset function	No
With mm / inch switching	No
Length	233 mm
With automatic shut off	Yes
Battery designation	1,5 V SR44
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.002 kg
Battery voltage	1.55 V
Type of rechargeable battery/battery	Silver oxide
Calibration Group	A
ISO	13385-1
Functions	Absolute function, Origin (Dimension preset), Automatic switch-off
Gross Weight	0.429 kg
Product Group	3MA

EAN

4946368693934