

Workplace mats made of PVC, manufactured to request

Textured structure, height 19 mm, with non-slip RedStop™ backing



Application:

For high durability in dry industrial environments.

Execution:

- Very robust, closed PVC mat, with textured surface, laminated with Uni-Fusion™ technology
- with RedStop™ anti-slip backing to prevent mats sliding on smooth floors
- Non-slip surface R9 to DIN 51130 and BG Rule BGR181
- Upper surface resistant to most chemicals, fire protection class Cfl-S1
- Thickness: 19 mm (5 mm PVC laminated on 14 mm microcellular vinyl)
- Four all-round-chamfered safety edges, thus no risk of tripping
- weight: 6.9 kg per m²
- REACH-compliant and silicone-free
- Available upon request: in grey and optional material thickness 25.4 mm

Advantage:

- Top-of-the range model with an optimum combination of unique ergonomic properties and excellent holding and anti-slip features
- Foam, cushioned underside protects from cold floors and reduces symptoms of fatigue when standing for extended periods



Art. no.	50225 651
Brand	NOTRAX
Surface structure	Burling / closed
Material	PVC - Polyvinyl chloride
Width	910 mm
Material thickness	19 mm
Mat design	Bulk stock
Min. temperature resistance	-20 °C
Max. temperature resistance	70 °C
Suitable for wet areas	No
Antistatic	No
Anti-fatigue	Yes
Non-slip	Yes
Compliant with REACH	Yes
Colour	Black
Gross Weight	7.500 kg
Product Group	5AD

EAN

0662641829268