

Electrohydraulic forklift truck

Carrying capacity 1200 kg



Application:

Suitable for use on long routes where electric drive provides many benefits, ideal device for semi-professional use in warehouse settings

Version:

- torsion-free pole and frame construction, robot welding, signal green, powder coated
- With electric lifting and travel drive
- infinitely adjustable travelling speed, precise lifting and lowering processes, all functions (e.g. raising and lowering) via push buttons in drawbar
- Grip column made of sheet steel, safety knob and signal on the tiller head
- Ergonomic tow bar with large control elements for direction and speed
- The lifting shut off is designed such that in the event of 80% discharge, the lift function is blocked, however a drive to the next charging station is still possible
- Two-part plastic housing for easy access to the components
- With entry points made of special steel, forks correspond to the pallet standard
- Steering deflection 180°—compact construction ensures a manoeuvrable and quick operation, even at full load height
- starter batteries

Advantage:

- versatile and rapid operation, including at full load height with 4-point mounting, side steering and compact design

Delivery:

Including battery with low charge display, charger (24 V / 11.5 A) and operating instructions, ready to use



Art. no.	50262 725
Travel drive	Electro-hydraulic
Fork roller diameter	82 mm
Turning radius	1460 mm
Load-carrying capacity	1200 kg
Fork length	1150 mm
Fork arm width	150 mm
Fork, external distance	560 mm
Min. lift height	90 mm
Lift height	2500 mm
Fork castor design	Single
Castor-wheel diameter	250 mm
Material of steering wheels	Rubber
Length	1760 mm
Width	800 mm
Min. overall height	1787 mm
Max. overall height	2992 mm
Battery voltage	24 V
Rechargeable battery/battery capacity	85 Ah
Output of lifting motor	2.2 kW
Stroke speed without load	0.19 m/s
Stroke speed at nominal load	0.11 m/s
Drive motor capacity	0.7 kW
Speed without load	5.2 km/h
Speed at nominal load	4.7 km/h
Max. surmountable tilt without load	10 %
Max. surmountable tilt with load	5 %
Colour	Black, Green
Surface	Powder-coated