

## Magnesium high-pressure die casting pipe cutter for 3–35 mm pipe diameter

For thin-walled metal pipes aluminium, copper, INOX

ZENTEN

### Application:

For cutting pipes with a clean cut.

### Execution:

- For thin-walled metal pipes (aluminium, copper, INOX)
- With cutting wheel and four guide rollers for optimum grip on the pipe
- Magnesium die-cast body – lightweight yet with identical stress properties
- Steel-mounted spindle, removable deburring tool.



<b>Art. no.</b>	<b>57001 500</b>
<b>Brand</b>	ZENTEN
<b>Manufacturer Part Number</b>	7 135-0
<b>Model</b>	kompakt+
<b>Suitable for min./max. pipe outer diameter</b>	3-35 mm
<b>Material of housing</b>	Die-cast magnesium
<b>Gross Weight</b>	0.369 kg
<b>Product Group</b>	580

### EAN

8422514713504