



11P

with tube



Packing	C1
Loose / Box [-50]	10
Taped / Reel [-51]	25



Part No	Inductance	f _L	Tol	Q	f _Q	SRF	DCR	Rated DC Current
	L (mH)	(MHz)	± (%)	min	(MHz)	min (MHz)	max (Ω)	
11P-100K-YY	0.01	0.02	10	70	0.796	20.0	0.035	3500
11P-101K-YY	0.10	0.02	10	40	0.796	3.40	0.20	950
11P-221K-YY	0.22	0.02	10	40	0.796	2.30	0.32	700
11P-331K-YY	0.33	0.02	10	30	0.796	1.88	0.60	590
11P-471K-YY	0.47	0.02	10	25	0.796	1.55	0.70	470
11P-561K-YY	0.56	0.02	10	20	0.796	1.50	0.80	430
11P-701K-YY	0.70	0.02	10	15	0.796	1.40	0.83	375
11P-761K-YY	0.76	0.02	10	15	0.796	1.40	0.90	360
11P-102K-YY	1.0	0.02	10	55	0.252	1.00	1.85	360
11P-222K-YY	2.2	0.02	10	50	0.079	0.70	2.7	360
11P-272X-YY	2.7	0.02	5,10	47	0.252	0.63	3.5	325
11P-332X-YY	3.3	0.02	5,10	47	0.252	0.60	3.7	190
11P-103X-YY	10	0.02	5,10	50	0.079	0.35	23	110
11P-123X-YY	12	0.02	5,10	50	0.079	0.32	24	100
11P-153X-YY	15	0.02	5,10	50	0.079	0.29	28	90
11P-183X-YY	18	0.02	5,10	50	0.079	0.28	34	85
11P-223X-YY	22	0.02	5,10	50	0.079	0.25	39	80
11P-273X-YY	27	0.02	5,10	50	0.079	0.21	48	70
11P-333X-YY	33	0.02	5,10	50	0.079	0.20	56	65
11P-373X-YY	37	0.02	5,10	50	0.079	0.19	62	60
11P-393X-YY	39	0.02	5,10	50	0.079	0.19	62	60
11P-473X-YY	47	0.02	5,10	50	0.079	0.18	73	55
11P-563X-YY	56	0.02	5,10	50	0.079	0.14	115	50
11P-683X-YY	68	0.02	5,10	50	0.025	0.13	120	50
11P-823X-YY	82	0.02	5,10	50	0.025	0.12	150	45
11P-104X-YY	100	0.02	5,10	30	0.025	0.11	155	40
11P-124X-YY	120	0.02	5,10	50	0.025	0.09	186	37
11P-154X-YY	150	0.02	5,10	30	0.025	0.08	205	35

Core Material : Ferrite

Revision date : 17 Jun 2021

Operating Temperature : -55°C to +125°C (including component self-heating)

SPQ :	Packing Form	Loose / Box	Taped / Reel
	Radial	250 [-50]	500 [-51]

Remarks: - Also available without tube.
- Also available with shorter leads.