


Data Sheet

Type Number 373
Designation IEC SR 68
System Silver oxide / Zinc /
 Alkaline - Electrolyte



Nominal Voltage 1,55 V
Typical Capacity C 29 mAh
 Load 47 kOhm, at 20 °C down to 1.2 V

Weight (approx.) 0,5 g
Volume 0,12 ccm
Coding..... Date of Manufacturing
 Month/Year

Temperature Ranges min max.
 Storage 0 °C 60 °C
 Discharge 0 °C 60 °C

Dimensions min max.
 Diameter (Ø)..... 9,35 9,5
 Height (A/B) 1,47 1,65

Segment Watch

Main Applications Watch
 Photo
 Electronic

Typical Capacities (at 20 °C)

Discharge Type	Load	End Voltage:	1.2 V
Continuous 24h/d,7d/w Current [µA]:	47000 Ω 33	Time:	850 h
		Capacity [mAh]:	29
		Energy [mWh]:	45