


	REVISED	DR	APP



1. TEST

WAVELENGTH	1310nm
INSERTION LOSS	≤ 0.20db
WORKING TEMPERATURE	-40~85℃

2. RoHS2.0 (2011/65/EU) ,(2015/863/EU) Compliant

Fiber optical coupler use it for distribution boxes, patch panels, wall mounts or other applications.

With the fiber optical coupler you can easily link two fiber optic patch cords.

- Connections: LC-Duplex jack to LC-Duplex jack
- for polishing type: Ultra Physical Contact (UPC) or Physical Contact (PC)
- Alignment Sleeve Material: ceramic
- for fiber mode: Singlemode
- for category: OS1 / OS2
- Mounting type: with flange, with metal clip, with shutter
- Connector style: Duplex

- Working temperature: -40 to +85 °C
- Storage temperature: -40 to +70 °C
- Housing material: PC

with dust covers



④	CLIP	STEEL
③	SHELL	PC
②	FERRULE	CERAMIC FERRULE
①	DUST CAP	PLASTIC/WHITE
NO	PART NAME	PICTURES AND COLORS CAN DIFFER FROM THE PRODUCT

	DESCRIPTION		FO COUPLER, LC-LC, SHUTTER, DUPLEX			
	SIZE	A4	DATE		CHECKED	TOL
	UNIT	MM	DRAWN		APPROVED	
	CUSTOM TARIF NO.: 85366910000					