

SCREWDRIVER AND SOCKET WRENCHES FOR ELECTRONICS

With slim, ergonomically formed handles made of dissipative plastic.
The rotatable centering head guarantees precision without exhaustion.

Blade: high grade chrome molybdenum steel, hardened over its full length, matt chrome-plated
Handle: black precision handle with yellow centering head, surface resistance $10^6 - 10^9$ Ohm
Standards: IEC 61340-5-1

Slotted screwdriver

No.	Blade-length mm	Blade-width mm	Blade-thickness mm	Blade Ø mm	Handle length mm	Weight g
4-603	40	1.5	0.25	2.0	80	11
4-605	40	2.0	0.40	2.0	80	11
4-606	50	2.5	0.40	2.5	95	17
4-607	50	3.0	0.50	3.0	95	18
4-608	60	3.5	0.60	3.5	110	26
4-609	60	4.0	0.80	4.0	110	28



Slotted screwdrivers

SCREWDRIVERS

Cross-recess screwdriver PH

No.	Size	Blade-length mm	Blade Ø mm	Handle length mm	Weight g
4-621	PH000	40	2.0	80	10
4-622	PH00	40	2.0	80	11
4-623	PH0	50	3.0	95	18
4-624	PH1	60	4.0	110	28



Cross-recess PH

Cross-recess screwdrivers PZ

No.	Size	Blade-length mm	Blade Ø mm	Handle length mm	Weight g
4-626	PZ1	60	4.0	110	28



PZ

Wrench Keys

No.	A/F mm	Blade length mm	Handle length mm	Weight g
6-631	0.7	40	80	10
6-632	0.9	40	80	11
6-633	1.3	40	80	12
6-634	1.5	50	95	16
6-635	2.0	50	95	17
6-636	2.5	60	110	22



Wrench Keys

Pentalob screwdrivers

No.	Size	Blade length mm	Handle length mm	Weight g
6-721	1	40	80	8
6-724	4	40	80	8



Pentalob

NEW