



## PCB TERMINAL STRIP 1 SOLDER PIN / POLE STAGGERED PIN SPACING 3.5 MM / 0.138 IN WITH PUSH BOTTONS WITH TEST SLOT FOR Ø


## **PDF DATASHEET**

© 1992 - 2011 CADENAS GmbH











## PCB TERMINAL STRIP 1 SOLDER PIN / POLE STAGGERED PIN SPACING 3.5 MM / 0.138 IN WITH PUSH BOTTONS WITH TEST SLOT FOR Ø 805-102 TO 805-124

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

ITEM-NO. (ITEM-NO.)	805-102
Cross section1 (Cross section / mm²)	0.2 - 1.5
Cross section2 (Cross section / AWG)	24 - 16
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	17.5
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	2
Height (Height / mm)	10.5
Width (Width / mm)	9.1
Depth (Depth / mm)	13.6
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	2
COLOR (COLOR)	grau
Comment (Comment)	L = (No. of poles x Pin Spacing) + 1,5 mm + 0, 6 mm
Dimensions (Dimensions)	1.1+0.1 mm