

## Xmore® quality USB Stick 2.0

### Product description



<b>Xmore® Partnumber</b>	USB004GXQC8A016R USB008GXQC8A016R	
<b>Flash Type</b>	Toshiba 15nm MLC	
<b>Capacity</b>	4GB / 8GB	
<b>Power Consumption</b>	Normal:	< 35 mA
	Standby:	< 0.25 mA
	Read:	< 60 mA
	Write:	< 60 mA
<b>Performance</b>	Read:	Up to 25 MB/s
	Write:	Up to 10 MB/s
<b>Temperature Range</b>	Storage:	-20°C to 85°C
	Operation:	0°C to 70°C
<b>Advance Flash Management</b>	Static and Dynamic wear-leveling Bad Block management	
<b>USB Mode</b>	USB 2.0 (backward compatible to USB 1.1)	

<b>RoHS compliant</b>	<b>USB-IF compliant</b>
<b>EMI compliant</b>	<b>ESD compliant</b>

## Technical draw

