



PKB 1 FOR SIGNAL TRANSFER


250V / 15 A

4×22-pole

15 A per potential rail

Screw plug-in terminals

[Link to Product](#)**Illustration**



Product may differ from Image

Technical Data

Operating voltage	max. 250 V AC
Operating current per bit	15 A per potential rail
Material group	(EN 60664-1) over voltage, category II

General data

Mounting method	DIN-rail mountable (EN 60715)
Connection	Screw plug-in terminal: max. 4 mm ² , single wire
Dimensions H × W × D	63×140×48 mm
Temperature range	-20...+60 °C

Commercial data

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1