



SINAMICS LINE REACTOR 380-480V 3AC 47-63HZ I_{LN} = 47,0A
STANDALONE

Order number	6SL3203-0CE23-8AA0
Phase number / of the input voltage	3
Type of voltage / of the input voltage	AC
Input voltage	380 ... 480
Output current / Rated value	47 A
Active power loss	
• at 50 Hz	Wert fehlt!
• at 60 Hz	Wert fehlt!
Type of electrical connection	
• for mains supply line	screw-type terminal
• for load-side outgoing feeder	screw terminals
Type of connectable conductor cross-section / for load-side outgoing feeder	Wert fehlt!
Connectable conductor cross-section	
• for mains supply line	16 mm ²
• for load-side outgoing feeder	16 mm ²
Type of electrical connection / for PE conductor	M5 x 10, washer, spring lock washer
Protection class IP	IP20
Width	190 mm
Height	220 mm
Depth	91 mm
Net weight	7.8 kg
Certificate of suitability	cURus

Further information

Information und Download Center

https://www.automation.siemens.com/mcms/infocenter/content/en/Pages/order_form.aspx

Technical documentation

<http://w3.siemens.com/mcms/mc-solutions/en/motion-control/support/technical-documentation/Pages/technical-documentation.aspx>

Industry Mall

<https://eb.automation.siemens.com/mall/en/WW/Catag/Product/6SL32030CE238AA0/all>

Industry Online Support

<http://support.automation.siemens.com/WW/view/en/6SL32030CE238AA0/all>