



Sample photo

Order symbol: ALN 080806
Product nbr: 7811130
Description: Enclosure
Remarks: Aluminium

EAN: 6418074016065
EI. number:
Finland: 3420044
Electric No. Sweden: 2536311

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	82	77	57	ARM 0808	DIN-15 Mounting rail
inch:	3.2	3.0	2.2	TRM 0808	DIN-15 Mounting rail
Materials:				MR 75003	Selftapping taptite screw M3
Material:	Aluminium			MRS 28540	Wall fastening lug (2 pcs)
Base colour:	RAL 7001			Rating:	
Cover screws material:	Stainless steel			Ingress Protection (EN 60529): IP66/IP67/IP68	
Cover colour:	RAL 7001			Impact Resistance (EN 62262): IK08	
Gasket material:	Polyurethane			NEMA Class: NEMA 1, 4, 4X, 12, 13	
Temperatures:				Certificates:	
Temperature °C (short term):	-50 ... 140 °C			SGS Fimko	
Temperature °C (continuous):	-50 ... 80 °C				
Temperature °F (short term):	-60 ... 285 °F				
Temperature °F (continuous):	-60 ... 175 °F				
Accessories:					
AM 0808	Mounting plate				

