



Standard lamps
Operation lighting


For special features, specific benefits and areas of use see page 114



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D max. mm	Total length L max. mm	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h	Burning position	PU
X0843396	6V 4.5A E14	6		4.5	E14	36	64	56	480	400			



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D max. mm	Total length L max. mm	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h	Burning position	PU
00847512	22.8V 110W ceramic cap +2-pole AMP St	22.8	110		special	11	46	35.25	2,900	700			



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D max. mm	Total length L max. mm	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h	Burning position	PU
89002440BS	Halogen lamp 24V 40W Blackshield	24	40		E11	30	55	40	950	500			

Signal lamps

Medical lamps operation technology

Photo, studio and stage lamps

Domestic lamps

Other special lamps