



Sample photo

Order symbol: PCTQ3 153410
Product nbr: 7025700
Description: Enclosure, PC
Remarks: Smoked transparent cover (quick-locking)

EAN: 6418074099143
EI. number:
Finland: 3424199

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and quick-locking cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	340	150	101	TRH 34	DIN-35 Mounting rail
inch:	13.4	5.9	4.0	TRH 15	DIN-35 Mounting rail
Materials:				TF 28037	Wall fastening lug (4 pcs)
Material:	ABS			TH A	Grey plastic hinges (2 pcs)
Base colour:	Grey			EU 3 QuickLock set 60	QuickLock screws (60 pcs)
Cover screws material:	Stainless steel			MR 28036EU Set 60	Mounting screws (60 pcs)
Cover colour:	Clear transparent			EU 3 Plug set 60/30	EU 3 Cover screw plug set 60/30
Gasket material:	Polyurethane			EU 3 Plug set 60/30 BL	EU 3 Cover screw plug set 60/30 black
Temperatures:				Rating:	
Temperature °C (short term):	-40 ... 120 °C			Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (continuous):	-40 ... 80 °C			Impact Resistance (EN 62262): IK07/IK08	
Temperature °F (short term):	-40 ... 250 °F			Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960	
TM 1534	Mounting plate			Certificates:	
				SGS Fimko	
				Gost R	

