



Minimum cable  $\phi$ :  $\phi_{Fmin}=3,0$   
 Maximum cable  $\phi$ : - with rubber bushing :  $\phi_{Fmax}=6,5$   
 - without rubber bushing :  $\phi_{Fmax}=9,5$

|                |                   |
|----------------|-------------------|
|                |                   |
|                |                   |
|                |                   |
| 09 67 009 0349 | M3                |
| 09 67 009 0344 | 4-40 UNC          |
| Part number    | jack screw thread |

|       |          |      |
|-------|----------|------|
|       |          |      |
|       |          |      |
|       |          |      |
| 33112 | 28/09/05 | JMDR |
| 32329 | 15/11/04 | TR   |
| Mod.  | Dat.     | Name |

|   |          |      |
|---|----------|------|
|   | Dat.     | Name |
| Detail.   | 15/11/04 | TR   |
| Insp.   |          |      |
| Stand.  |          |      |
|  |          |      |
| HARTING EURL<br>F-95972 Paris   |          |      |

|   |   |                            |
|---|---|----------------------------|
|  | D-Sub hood 9 poles<br>top entry, full metal hood<br>with short jack screw | Maßstab/<br>Scale<br>1,5:1 |
|   | TB 09 67 009 034X<br>Sub. TB 09 67 009 0344 / TB 09 67 009 0348           | Blatt/ Page<br>2 / 4       |