





	<b>Schnecken eingängig rechts, brüniert</b>						
	Stahl / Steel C45						
	Modul	dk	do	ls	L	N	B
	0,5	8	7	12	16	5,5	3 H7



	<b>Schneckenrad</b>						
	Messing / Brass M 58						
	Modul	SP	OP	Z	b	L	N
<b>275169</b>	0,5	11,4	10	20	3	8	8
<b>275170</b>	0,5	21,5	20	40	3	8	10
<b>275171</b>	0,5	31,5	30	60	3	8	15

**mit Stellschraube M3**




B H7	
3	
4	
4	