



AOH(X) & AOH(X) .. G

Generic code	Rubix engineering code	d1	d2	l	a	G	b	g	e	t	Weight (kg)	Dismounting nut	Locknut	Locking device
		(mm)												
AH308-AKN	890519	35	40	29	3	M 45x1.5	6	-	-	-	0.09	KM9-AKN	KM7-AKN	MB7-AKN
AH2308-AKN	890486	35	40	40	3	M 45x1.5	7	-	-	-	0.13	KM9-AKN	KM7-AKN	MB7-AKN
AH309-AKN	890520	40	45	31	3	M 50x1.5	6	-	-	-	0.11	KM10-AKN	KM8-AKN	MB8-AKN
AH2309-AKN	890487	40	45	44	3	M 50x1.5	7	-	-	-	0.16	KM10-AKN	KM8-AKN	MB8-AKN
AH310-AKN	891203	45	50	35	3	M 60x2	7	-	-	-	0.16	KM12-AKN	KM9-AKN	MB9-AKN
AHX310-AKN	890567	45	50	35	3	M 55x2	7	-	-	-	0.14	KM11-AKN	KM9-AKN	MB9-AKN
AH2310-AKN	891413	45	50	50	3	M 60x2	8	-	-	-	0.23	KM12-AKN	KM9-AKN	MB9-AKN
AHX2310-AKN	890541	45	50	50	3	M 55x2	9	-	-	-	0.21	KM11-AKN	KM9-AKN	MB9-AKN
AH311-AKN	891204	50	55	37	3	M 65x2	7	-	-	-	0.19	KM13-AKN	KM10-AKN	MB10-AKN
AHX311-AKN	890568	50	55	37	3	M 60x2	7	-	-	-	0.16	KM12-AKN	KM10-AKN	MB10-AKN
AH2311-AKN	891414	50	55	54	3	M 65x2	9	-	-	-	0.29	KM13-AKN	KM10-AKN	MB10-AKN
AHX2311-AKN	890542	50	55	54	3	M 60x2	10	-	-	-	0.25	KM12-AKN	KM10-AKN	MB10-AKN
AH312-AKN	890521	55	60	40	3	M 70x2	8	-	-	-	0.22	KM14-AKN	KM11-AKN	MB11-AKN
AHX312-AKN	890569	55	60	40	3	M 65x2	8	-	-	-	0.19	KM13-AKN	KM11-AKN	MB11-AKN
AH2312-AKN	891415	55	60	57	3	M 70x2	10	-	-	-	0.34	KM14-AKN	KM11-AKN	MB11-AKN
AHX2312-AKN	890543	55	60	58	3	M 65x2	11	-	-	-	0.30	KM13-AKN	KM11-AKN	MB11-AKN
AH313-AKN	890522	60	65	42	3	M 75x2	8	-	-	-	0.25	KM15-AKN	KM12-AKN	MB12-AKN
AH313G-AKN	890523	60	65	42	3	M 70x2	8	-	-	-	0.23	KM14-AKN	KM12-AKN	MB12-AKN
AH2313-AKN	890488	60	65	61	3	M 75x2	12	-	-	-	0.40	KM15-AKN	KM12-AKN	MB12-AKN
AH2313G-AKN	890489	60	65	61	3	M 70x2	12	-	-	-	0.40	KM14-AKN	KM12-AKN	MB12-AKN
AHX2313-AKN	891238	60	65	61	3	M 75x2	12	-	-	-	0.40	KM15-AKN	KM12-AKN	MB12-AKN
AH314-AKN	891205	65	70	43	4	M 80x2	8	-	-	-	0.28	KM16-AKN	KM13-AKN	MB13-AKN
AHX2314-AKN	890544	65	70	64	4	M 80x2	12	-	-	-	0.47	KM16-AKN	KM13-AKN	MB13-AKN
AHX2314G-AKN	890545	65	70	64	4	M 75x2	12	-	-	-	0.47	KM15-AKN	KM13-AKN	MB13-AKN