

Product information

98 20 25

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Screwdrivers for slotted screws

IEC 60900 DIN EN 60900



⚡ 1000 V ⚡

General	
Article No.	98 20 25
EAN	4003773062325
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	32 g
Dimensions	177 x 24 x 24 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Blade length	75 mm
Length of non-insulated blade	15 mm
Handle length	102 mm
Blade width	2.5 mm
Blade thickness	0.4 mm
VDE tested	yes

technical change and errors excepted