# P4GC

# APC Power-Saving Timer Essential SurgeArrest, 4 Outlet Wall Tap, 120V





#### Overview

Lead time Usually in Stock

### Physical

White
2.01 in (5.1 cm)
6.50 in (16.5 cm)
0.55 lb(US) (0.25 kg)
3.70 in (9.4 cm)

#### Input

Input Frequency	50/60 Hz
Plug standard	NEMA 5-15P
Maximum Input Current per phase	15 A
Nominal Input Voltage	120 V

## Output

Number of power socket outlets	4
Outlet standard	NEMA 5-15R

#### Conformance

UL 1449 TVSS Rating	400
Product certifications	ETL
Standards	UL 1449
Equipment protection policy	Lifetime: \$50000

## Environmental

Ambient air temperature for operation	32113 °F (045 °C)	
Relative humidity	095 %	
Operating altitude	010000 ft	
Ambient air temperature for storage	23113 °F (-545 °C)	
Storage altitude	050000 ft (0.0015240.00 m)	

# Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	40 dB
Peak current	72 kA common mode
Surge energy rating	1080 J

# Ordering and shipping details

0 11 0	
Category	11309 - APC RESALE PRODUCTS
GTIN	00731304269267
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

# Packing Units

r doming orme	
Package 1 Height	9.65 in (24.5 cm)
Package 1 width	8.90 in (22.6 cm)
Package 1 Length	2.64 in (6.7 cm)
SCC14	10731304269264
Number of Units in Package 2	6
Package 2 Weight	7.88 lb(US) (3.57 kg)
Package 2 Height	11.68 in (296.67 mm)
Package 2 width	12.13 in (308.10 mm)
Package 2 Length	19.85 in (504.19 mm)
Number of Units in Package 3	288

## Contractual warranty

Warranty	Lifetime