

Manual lever snips 2 BR 4

Max. cutting thickness 4 mm

Application:

For cutting sheet metal, flat and round steel (not suitable for stainless steel sheets).

Execution:

- Robust shear body made from tempered steel
- Special tool steel blade, specially hardened and ground

Advantage:

- Lever arm with weight-equalising spring used as accident prevention
- With infinitely variable hold-down clamp for safe working processes

Art. no.	53790 010
Model	2BR4
Surface of the handle	Lacquered
Knife insert length	120 mm
Max. material thickness for steel	4 mm
Weight	8 kg
Gross Weight	12.000 kg
Product Group	580

EAN

8695544461312

