

Manual pick-up magnet



Application:

For moving welded parts etc. from one place to another (max. temperature: 60°)

Version:

- Protects hands and fingers from hot and sharp-edged steel

Art. no.	77350 100
Load-carrying capacity	50 kg
Surface area length	80 mm
Length	126 mm
Surface area width	80 mm
Width	80 mm
Height	100 mm
Width of lever	124 mm
Length of lever	190 mm
Weight	1.6 kg
Max. temperature	60 °C



EAN-Code

4030266269152