







**Designed for Professionals**

<b>Pliers &amp; Cutters</b>	<b>6-27</b>
<b>Screwdrivers</b>	<b>28-47</b>
<b>Cable Routing</b>	<b>48-55</b>
<b>Electricians' Specialist Tools</b>	<b>56-65</b>
<b>Toolkits</b>	<b>66-71</b>
<b>ESD &amp; Precision</b>	<b>72-103</b>
<b>Power Tool Accessories</b>	<b>104-129</b>
<b>Building &amp; Decorating</b>	<b>130-139</b>
<b>Striking Tools</b>	<b>140-145</b>
<b>Sawing, Cutting &amp; Filing</b>	<b>146-155</b>
<b>Automotive &amp; Engineering</b>	<b>156-167</b>
<b>Marking &amp; Measuring</b>	<b>168-175</b>
<b>Water Systems</b>	<b>176-181</b>
<b>Lighting</b>	<b>182-187</b>

**For over 100 years, C.K. has been at the forefront of hand tool manufacturing, producing high quality tools that meet the most demanding needs of trade professionals.**

Backed by our quality guarantee, C.K. tools are engineered to offer leading performance, durability, accuracy and strength, all of which are key requirements for professional results.

Driven by research through an extensive panel of cross trade professionals, tools are developed to assist with every day tasks; an approach proven to produce innovative tools that transform traditional working practices.







# Pliers & Cutters

<b>Redline VDE</b>	<b>11</b>
<b>Redline</b>	<b>13</b>
<b>Classic</b>	<b>16</b>
<b>Ratchet Crimping Pliers</b>	<b>17</b>
<b>Crimping Pliers</b>	<b>20</b>
<b>Waterpump Pliers</b>	<b>21</b>
<b>Heavy Duty Cutters</b>	<b>22</b>
<b>Pincers &amp; Top Cutters</b>	<b>23</b>
<b>Conduit Cutters</b>	<b>24</b>
<b>Pipe Cutters</b>	<b>24</b>
<b>Circlip Pliers</b>	<b>25</b>
<b>Snips</b>	<b>26</b>
<b>Riveting Pliers</b>	<b>26</b>
<b>Punch Pliers</b>	<b>27</b>
<b>Fencing Pliers</b>	<b>27</b>



# RedLine™ VDE

Premium quality insulated pliers and cutters

1. Two component, ergonomic design, with anti-slip horns for increased comfort, control and safety.
2. Induction hardened jaws for outstanding long term performance.
3. Cutting jaws with C.K optimised geometry for unsurpassed cutting performance.
4. Special alloy steel, drop forged, hardened and tempered for exceptional strength and durability.
5. VDE approved - individually tested to 10,000V for safe live working up to 1,000V.



Conforms to IEC 60900. Approved and independently audited by the German VDE institute.



Redline VDE



**VDE Combicutter1**

Pattress screw shear for damage free cutting of 3.5mm pattress screws.

BS EN60900, VDE0682/201, ASTM-F 1505, ISO 5749

Item No.	Length	Wire Size 1	Wire Size 2	Wire Size 3	Quantity
431004	160mm (6")	2.0mm	2.8mm	>4.0mm	3



**VDE Combicutter3**

Pattress screw shear for damage free cutting of 3.5mm pattress screws. Wire stripping notches for effortless & damage free stripping of 1.5 & 2.5mm<sup>2</sup> wire. Wire bending anvil for quick & damage free doubling back of copper wire.

BS EN60900, VDE0682/201, ASTM-F 1505, ISO 5749

Item No.	Length	Wire Size 1	Wire Size 2	Wire Size 3	Quantity
431008	160mm (6")	2.0mm	2.8mm	>4.0mm	3



**VDE Combicutter1 Max**

Pattress screw shear for damage free cutting of 3.5mm pattress screws & 4mm conduit cover screws.

EN 60900, VDE0682/201, ASTM-F 1505

Item No.	Length	Wire Size 1	Wire Size 2	Wire Size 3	Quantity
T39071-1180	180mm (7")	2.5mm	3.0mm	>4.0mm	3



**VDE Combicutter3 Max**

Pattress screw shear for damage free cutting of 3.5mm pattress screws & 4mm conduit cover screws. Wire stripping notches for effortless & damage free stripping of 1.5 & 2.5mm<sup>2</sup> wire. Wire bending anvil for quick & damage free doubling back of copper wire.

EN 60900, VDE0682/201, ASTM-F 1506

Item No.	Length	Wire Size 1	Wire Size 2	Wire Size 3	Quantity
T39071-3180	180mm (7")	2.5mm	3.0mm	>4.0mm	3



**VDE Combicutter2**

Pattress screw shear for damage free cutting of 3.5mm pattress screws. Wire stripping notches for effortless & damage free stripping of 1.5 & 2.5mm<sup>2</sup> wire.

BS EN60900, VDE0682/201, ASTM-F 1505, ISO 5749

Item No.	Length	Wire Size 1	Wire Size 2	Wire Size 3	Quantity
431009	160mm (6")	2.0mm	2.8mm	>4.0mm	3



**VDE Wire Stripping Side Cutter**

Wire stripping notches for effortless & damage free stripping of 1.5 & 2.5mm<sup>2</sup> wire.

BS EN60900, VDE0682/201, ASTM-F 1505, ISO 5749

Item No.	Length	Wire Size 1	Wire Size 2	Wire Size 3	Quantity
431019	160mm (6")	2.0mm	2.8mm	>4.0mm	3





## VDE Side Cutter

Induction hardened cutting jaws with optimised geometry for unsurpassed cutting performance.

BS EN60900, VDE0682/201, ASTM-F 1505, ISO 5749

Item No.					
431018	140mm (5 1/2")	1.4mm	1.9mm	>4.0mm	3
431017	160mm (6")	2.0mm	2.8mm	>4.0mm	3
431005	180mm (7")	2.5mm	3.0mm	>4.0mm	3



## VDE High Leverage Side Cutter

33% slimmer than the previous model for greater accessibility in tight access areas. High leverage design for increased cutting capacity.

BS EN 60900, VDE0682/201, ASTM-F 1505

Item No.					
T37021 180	180mm	2.2mm	3.8mm	6mm	3
T37021 200	200mm	2.5mm	4.2mm	6mm	3



## VDE Cable Cutters

Shearing action for clean cut results. Razor sharp, parrot beak blades for effortless cuts. Suitable for copper & aluminium wire only.

BS EN 60900, VDE0682/201, ASTM-F 1505

Item No.			
431030	160mm (6")	15.0mm	3
431031	210mm (8 1/4")	20.0mm	3



## VDE Electricians Pliers

Specially designed for electrical installation work where space is restricted. Tapered nose - streamlined for better access, and ideal for gripping nuts and cutting wires in recessed cabinets. Gutter nut holder - specially profiled jaw for securely holding square nuts used on cable trays and cabinets. Pin holder - machined at 90° to the angled face for holding cable clips/ nails upright while hammering.

EN 60900, VDE0682/201, ASTM-F 1506

Item No.					
T39077-180	180mm (7")	1.6mm	2.5mm	>4.0mm	3



## VDE Combination Pliers

Precision engineered jaws for exceptional grip. Extra long cutting edges for increased cutting capacity.

BS EN60900, VDE0682/201, ASTM-F 1505, ISO 5746

Item No.					
431001	165mm (6 1/2")	1.6mm	2.5mm	>4.0mm	3
431002	185mm (7")	1.6mm	2.5mm	>4.0mm	3
431003	200mm (8")	2.0mm	2.8mm	>4.0mm	3



## VDE Snipe Nose Pliers - Straight

Serrated inside jaws for secure gripping.

BS EN60900, VDE0682/201, ASTM-F 1505, ISO 5745

Item No.					
431013	175mm (6 1/2")	1.4mm	2.0mm	>4.0mm	3
431014	200mm (8")	1.6mm	2.0mm	>4.0mm	3





### VDE Snipe Nose Pliers - Bent

Serrated inside jaws for secure gripping. Bent nose for special access needs.

BS EN60900, VDE0682/201, ASTM-F 1505, ISO 5745

Item No.					
431015	200mm (8")	1.6mm	2.5mm	>4.0mm	3



### VDE Wire Stripping Pliers

Micro adjustment for damage free, repeatable results. Spring assisted opening for convenience.

BS EN 60900, VDE0682/201, ASTM-F 1505

Item No.			
431012	160mm (6")	0.3 - 5.0mm	3



### VDE Pliers Set - 3 Piece

CONTENTS: Combicutter 160mm, Combination Pliers 185mm, Snipe Nose Pliers 200mm.

BS EN60900, VDE0682/201

Item No.	
T3805	3

## Redline



### Redline Side Cutter

Induction hardened cutting jaws with optimised geometry for unsurpassed cutting performance.

ISO 5749

Item No.					
T3750 145	140mm (5 1/2")	1.4mm	1.9mm	>4.0mm	3
T3750 160	160mm (6")	2.0mm	2.8mm	>4.0mm	3
T3750 180	180mm (7")	2.5mm	3.0mm	>4.0mm	3



### Redline High Leverage Side Cutter

33% slimmer than the previous model for greater accessibility in tight access areas.

High leverage design for increased cutting capacity.

Item No.					
T3721 180	180mm (7")	2.2mm	3.8mm	>6.0mm	3
T3721 200	200mm (8")	2.5mm	4.2mm	>6.0mm	3



### Redline Cable Cutters

Shearing action for clean cut results. Razor sharp, parrot beak blades for effortless cuts. Suitable for copper & aluminium wire only.

Item No.			
T3964 6	160mm (6")	16.0mm	3

# RedLine™

Premium quality  
pliers and cutters

1. Two component, ergonomic design, with anti-slip horns for increased comfort, control and safety.
2. Induction hardened jaws for outstanding long term performance.
3. Cutting jaws with C.K optimised geometry for unsurpassed cutting performance.
4. Special alloy steel, drop forged, hardened and tempered for exceptional strength and durability.







**Redline Combination Pliers**

Precision engineered jaws for exceptional grip. Extra long cutting edges for increased cutting capacity. ISO 5746

Item No.					
T3867 6	160mm (6")	1.6mm	2.5mm	>4.0mm	3
T3867 7	180mm (7")	1.6mm	2.5mm	>4.0mm	3
T3867 8	200mm (8")	2.0mm	2.8mm	>4.0mm	3



**Redline Wire Stripper**

Micro adjustment for damage free, repeatable results. Spring assisted opening for convenience. ISO 5743

Item No.			
T3754	160mm (6")	0.3 - 5.0mm	3



**Redline Snipe Nose Pliers**

Serrated inside jaws for secure gripping. ISO 5745

Item No.					
T3909 5	140mm (5 1/2")	1.2mm	1.6mm	>4.0mm	3
T3909 6	170mm (6 3/4")	1.4mm	1.9mm	>4.0mm	3
T3906 8	200mm (8")	1.6mm	2.0mm	>4.0mm	3



**Cutter, Snipe & Combination Pliers Set**

CONTENTS: Combination Pliers 180mm, Side Cutters 160mm, Snipe Nose Pliers 200mm.

Item No.	
T3803	1



**Redline Bent Nose Pliers**

Serrated inside jaws for secure gripping. Bent nose for special access needs. ISO 5745

Item No.					
T3907 8	200mm (8")	1.6mm	2.0mm	>4.0mm	3



**Cutter, Snipe & Stripping Pliers Set**

CONTENTS: Wire Stripping Pliers 160mm, Side Cutters 160mm, Snipe Nose Pliers 200mm.

Item No.	
T3804	1


# Classic™

## Professional general purpose pliers & cutters

1. Induction hardened jaws for outstanding long term performance.
2. High alloy steel, drop forged, hardened and tempered for exceptional strength and durability.
3. Heads polished and lacquered for corrosion protection.
4. Wipe clean PVC handles for added convenience.



### Classic



#### Classic Side Cutters

Induction hardened cutting jaws with optimised geometry for unsurpassed cutting performance.

ISO 5749

Item No.	Length	Wire	Tube	Sheet	Box
T3623B 5	140mm (5 1/2")	1.2mm	1.6mm	>4.0mm	6
T3623B 6	160mm (6")	1.6mm	2.1mm	>4.0mm	6



#### Classic Heavy Duty Side Cutters

High leverage design for increased cutting capacity.

ISO 5749

Item No.	Length	Wire	Tube	Sheet	Box
T3627B 7	180mm (7")	2.2mm	3.8mm	>6.0mm	6



#### Classic Combination Pliers

Precision engineered jaws for exceptional grip. Extra long cutting edges for increased cutting capacity.

ISO 5746

Item No.	Length	Wire	Tube	Sheet	Box
T3621B 6	160mm (6")	1.6mm	2.5mm	>4.0mm	6
T3621B 7	180mm (7")	1.6mm	2.5mm	>4.0mm	6
T3621B 8	200mm (8")	2.0mm	2.8mm	>4.0mm	6





**Classic Snipe Nose Pliers**

Serrated inside jaws for secure gripping.  
ISO 5745

Item No.			
T3626B 8	200mm (8")	1.6mm 2.0mm >4.0mm	6



**Classic Cable Cutters**

Special alloy steel construction with razor sharp, induction hardened cutting edges for outstanding cutting performance. Shearing action for clean cut results. Special profile blade for effective cable cutting & wire stripping. Suitable for copper & aluminium wire only.

Item No.			
T3963 160	160mm (6")	9mm	3
T3963	210mm (8 1/4")	11mm	3
T3963 240	240mm (9 1/2")	13mm	3

**Ratchet Crimping Pliers**



**Terminal Crimper .25-2.5mm 2K**

Designed for the safe and secure crimping of green, red, and blue insulated terminals. Also suitable for green, red and blue butt and parallel splicers.

Item No.		
T3680A	✓	3



**Terminal Crimper 0.5-6mm 2K**

Designed for the safe and secure crimping of red, blue and yellow insulated terminals. Also suitable for red, blue and yellow butt and parallel splicers.

Item No.		
T3682A	✓	3



**Terminal Crimper 1-10mm 2K**

Designed for the safe and secure crimping of uninsulated terminals.

Item No.		
T3697A	✓	3



## Ratchet crimping pliers

1. Auto-stop ratchet system releases when correct pressure is applied to ensure precise crimping.
2. Precision engineered dies for quality crimps and safe connections.
3. Dies manufactured from fully hardened carbon alloy steel for strength and durability.
4. Heavy duty construction, tested up to 40,000 cycles, guaranteed for 30,000 crimps per tool.
5. Ergonomic two component handle for ease and comfort in use.



### Bell Mouth Crimper 6-25mm 2K

Designed for the safe and secure crimping of bell mouth ferrules.

Item No.			mm <sup>2</sup> /AWG	
T3676A	✓	350mm	6 - 25 / 10 - 4	3



### Ferrule Crimper 0.14-2.5mm 2K

Designed for the safe and secure crimping of small bootlace ferrules.

Item No.		
T3692A	✓	3



### Ferrule Crimper 0.25-6mm 2K

Designed for the safe and secure crimping of medium bootlace ferrules.

Item No.		
T3684	✓	3





**Ferrule Crimper 10-25mm 2K**

Designed for the safe and secure crimping of large bootlace ferrules.

<b>Item No.</b>		
T3683A	✓	3



**Modular Plug Crimper 6/8P**

Designed for the safe and secure attachment of modular plugs without die changes. Built in wire stripper/cutter mechanism for convenience.

<b>Item No.</b>			
430028	✓	220mm	3



**Modular Crimper 4/6/8P**

Designed for the safe and secure attachment of modular plugs without die changes. Built in wire stripper/cutter mechanism for convenience.

<b>Item No.</b>			
430020	✓	220mm	3



**Modular Crimper 6/8P 2K**

Designed for the safe and secure crimping of Modular Plugs 6P and 8P. Built in wire stripper and cutters for convenience.

<b>Item No.</b>		
T3852A	✓	3



**Modular Crimper 4/6/8P 2K**

Designed for the safe and secure crimping of Modular Plugs 4P, 6P and 8P. Built in wire stripper and cutters for convenience.

<b>Item No.</b>		
T3681A	✓	3



**Pass Through Modular Crimper 8P 2K**

Cuts, strips, crimps and trims pass through Modular Plugs 8P Capacity 8P8C (RJ45).

<b>Item No.</b>		
T3853	✓	3



## Coax, BNC, TNC Crimper

Designed for the safe & secure crimping of BNC/TNC connectors to coaxial cable.

Item No.			
430026	✓	230mm	3



## Coax, BNC, TNC Crimper 2K

Designed for the safe and secure crimping of COAX - BNC and TNC connectors.

Item No.		
T3698A	✓	3



## Solar PV Crimper 2K

Designed for the safe and secure crimping of Solar PV cable connectors.

Item No.			
T3671A	220mm	MC3 & MC4	3

## Crimping Pliers



## Compact Modular Crimper 6/8P

Compact ergonomic design for convenient storage and easy handling. Crimps both 6 and 8 position modular connectors (including RJ11 and RJ45). Cuts and strips CAT3, CAT5e and flat cables. Heavy duty carbon steel body for strength and durability.

Item No.				
T3673	✓	6P & 8P	140mm	3



## Crimping Pliers

Designed for the safe & secure crimping of bootlace ferrules. Hardened & tempered high alloy carbon steel for increased strength & durability. Matte chrome plated for corrosion protection. Contoured grips with anti-slip horns for comfort & safety.

Item No.			mm <sup>2</sup> / AWG	
430005	✓	145mm	0.25 - 2.5 / 23 - 13	3
430006	✓	220mm	0.5 - 16 / 20 - 5	3



## Multi-Function Crimping Plier

Specially hardened steel for durability, with black soft comfort grips. Four function tool for wire cutting, wire stripping, crimping and bolt/wire shearing.

Item No.		
430024	250mm	3



**Waterpump Pliers**



**Waterpump Pliers**

Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Induction hardened jaws for outstanding long term performance. Box joint design with double pivot support for strength. Slim head & jaws for access to confined spaces. Contoured anti-slip handles for comfortable & powerful operation.

Item No.	Length	Jaw Capacity	Quantity
T3650 250	250mm (10")	47mm	3



**Heavy Duty Waterpump Pliers**

Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Box joint design with double pivot support for strength. Slim head & jaws for access to confined spaces. Contoured anti-slip handles for comfortable & powerful operation.

DIN ISO 8976

Item No.	Length	Jaw Capacity	Quantity
T3659A 175	180mm (7")	25mm (1")	3
T3659A 240	240mm (9 1/2")	32mm (1 1/4")	3
T3659A 300	300mm (12")	45mm (1 3/4")	3



**Waterpump Pliers - Standard**

Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Induction hardened jaws for outstanding long term performance. Laid on slip joint design for secure adjustment.

DIN ISO 8976

Item No.	Length	Jaw Capacity	Quantity
T3651 09	250mm (10")	38mm (1 1/2")	3



**Push Button Waterpump Pliers**

Push button adjustment for quick and secure jaw adjustment. Long slim head & jaws for access to confined spaces. Extra wide jaws for greater working capacity. Chrome vanadium alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Box joint for extra stability.

Item No.	Length	Jaw Capacity	Quantity
T3653 180	180mm (7")	42mm	6
T3653 250	250mm (10")	50mm	6
T3653 300	300mm (12")	70mm	6



**High Capacity Waterpump Pliers**

Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Induction hardened jaws for outstanding long term performance. 11 adjustment point, non slip groove joint mechanism with a large 110mm jaw capacity. Slim head & jaws for access to confined spaces. Contoured anti-slip handles for comfortable & powerful operation.

Item No.	Length	Jaw Capacity	Quantity
T3629A 400	400mm	110mm (4")	1

## Heavy Duty Cutters



### Ratchet Cable Cutter

Compact heavy duty cutter for clean effortless cutting. High quality chrome molybdenum profiled steel blade. Ratchet disengage lever for quick cable loading. Integral locking mechanism for safe storage. Designed to cut hard drawn copper cable, aluminium cable or 200 pair communication cables. Not for use on steel or ACSR cable.

Item No.			
430007	190mm	32mm	3
Z3677 1	Moving blade		1
Z3677 2	Fixed blade		1



### Heavy Duty Ratchet Cable Cutter

High-grade special tool steel cutting jaws, forged and hardened for an extended working life. Heavy duty ratchet action for the effortless cutting of large diameter cable. Suitable for copper and aluminium cables up to 52mmØ and SWA cable up to 36mmØ.

Item No.			
T3678	52mm Cu/Al	36mm SWA	1
Z3678 1	Moving blade		1
Z3678 2	Fixed blade		1



### Heavy Duty Cable Shears

High-grade special tool steel cutting jaws, forged and hardened for an extended working life. Parrot-beak cutting jaws to prevent cable slippage. For large diameter copper and aluminium cables up to 27mmØ.

Item No.		
T3679	27mm	1



### Wire Rope Cutter

Heavy duty construction, drop forged alloy steel, hardened & tempered for exceptional strength & durability. Induction hardened specially profiled shearing blades for clean cutting of a wide range of wire & cables including: bowden cable, steel wire, fencing wire; stranded wire rope, copper & aluminium cables, steel rods, etc. PVC coated handles for comfort and grip.

Item No.				
T3744	190mm	6mm	4mm	10



### Wire Cutters - Heavy Duty

Heavy duty construction, drop forged alloy steel, hardened & tempered for exceptional strength & durability. Induction hardened jaws for outstanding long term performance. Wipe clean PVC handles for added convenience. Black lacquered for corrosion protection.

Item No.			
T3961A 08	200mm (8")	2.0mm	3
T3961A 10	250mm (10")	3.0mm	5



**Bolt Cutters**

For cutting round material and hard wire up to 40HRC. Head and cutting edges manufactured from hot drop forged chrome vanadium steel. Induction hardened cutting edges, plastic coated tubular handles. Replacement heads are separately available.

Item No.		785Nmm <sup>2</sup> (51TONS SQ <sup>2</sup> )	1226Nmm <sup>2</sup> (80TONS SQ <sup>2</sup> )	
T4358 12	340mm (13")	6mm	5mm	1
T4358 15	400mm (16")	7mm	6mm	1
T4358 18	450mm (18")	10mm	7mm	1
T4358 25	610mm (24")	11mm	9mm	1
T4358 36	900mm (35")	15mm	13mm	1
Z4358 121				
Z4358 151				
Z4358 181				
Z4358 251				
Z4358 301				



**Bolt Cutters - Pocket**

Compact cutters ideal for fencing, meshes and low tensile wire. Hot drop forged chrome vanadium steel jaws with induction hardened cutting edges for strength and durability. Compound action mechanism applies extreme cutting forces.

Item No.		785Nmm <sup>2</sup> (51TONS SQ <sup>2</sup> )	1226Nmm <sup>2</sup> (80TONS SQ <sup>2</sup> )	
T4371A	250mm (10")	5mm	3mm	2

**Pincers & Top Cutters**



**Pincers**

Optimised jaw design for effective gripping & extracting of screws, nails, fixings, etc. Specially profiled cutting blades for cutting metal rod & wire. High alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Wipe clean PVC handles. Black lacquered for corrosion protection.

Item No.			>4.0mm icon"/>	
T4108A 06	160mm (6")	2.0mm	>4.0mm	3
T4108A 07	180mm (7")	2.0mm	>4.0mm	3
T4108A 08	200mm (8")	2.0mm	>4.0mm	3



**Top Cutters - Standard**

High alloy steel, drop forged, hardened & tempered for strength & durability. Induction hardened jaws for outstanding long term cutting performance. Wipe clean PVC handles for added convenience. Black lacquered for corrosion protection.

Item No.				>4.0mm icon"/>	
T3988 180	180mm (7")	2.5mm	3.2mm	>4.0mm	3
T3988 200	200mm (8")	2.8mm	3.5mm	>4.0mm	3



**Top Cutters - Steel Fixers**

Special slimline design for binding & twisting wire. Induction hardened jaws for outstanding long term cutting performance. High alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Wipe clean PVC handles for added convenience. Black lacquered for corrosion protection.

Item No.			
T4112A 08	220mm (8 1/4")	2.0mm	1
T4112A 10	250mm (10")	2.0mm	3
T4112A 11	280mm (11")	2.0mm	3



## Conduit Cutters



### Ratcheting Conduit Cutter

Heavy duty aluminium body - strong & light. Ratchet action razor sharp stainless steel blade for effortless cutting of: PVC conduit, blue water mains, plastic pipe, rubber hose, pneumatic pipe, electrical sleeving, etc. Complete with special adaptor for straight or mitre cutting of small rectangular cross-section trunking.

Item No.			
430003	220mm	32mm	3
Z2239B			



### PVC Pipe & Conduit Cutter

Glass fibre reinforced polycarbonate body - strong & light. Razor sharp stainless steel blade for efficient cutting of: PVC conduit, blue water mains, plastic pipe, rubber hose, pneumatic pipe, electrical sleeving, etc.

Item No.			
430001	195mm	28mm	3



### Ratchet Multifunction Cutter

Heavy duty aluminium body. Lever action razor sharp stainless steel blade for effortless cutting of: PVC conduit, blue water mains, plastic pipe, rubber hose, pneumatic pipe, electrical sleeving, wooden dowel, etc. 5 interchangeable anvils (flat, double radius, single radius, 90° square and mitre). Allow a variety of cross sections to be cut, both straight and mitred.

Item No.	
T2240	3
Z2240 1	
Z2240 2	
Z2240 3	
Z2240 4	
Z2240 5	
Z2240 6	

## Pipe Cutters



### Pipe Cutter

Adjustable pipe cutter for copper, brass, aluminium and thin walled steel pipe. Easy grip handle. New longer life easy glide steel insert body threads. Replaceable hardened steel cutting blade for long life performance. No tools required for convenience. Black die cast lacquered body for strength and corrosion resistance.

Item No.		
T2231A	3 - 30mm	5



### Mini Pipe Cutter

Compact adjustable mini pipe cutter for copper, brass, aluminium and thin walled steel pipe. New longer life easy glide steel insert body threads. Replaceable hardened steel cutting blade for long life performance. No tools required for convenience. Black die cast lacquered body for strength and corrosion resistance.

Item No.		
T2232A	3 - 25mm	10



### Pipe Cutter - Spare Wheel

Suitable for T2231 & T2232 Pipe Cutters.

Item No.		
T2235	19.5mm	10

**Circlip Pliers**



**Circlip Pliers - Inside Straight**

High alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Chequered handles for grip. DIN 5256C

Item No.	↔	∅	DIN	📦
T3710 0	140mm (5 1/2")	8 - 13mm	J0	5
T3710 5	140mm (5 1/2")	12 - 25mm	J1	5
T3710 7	180mm (7")	19 - 60mm	J21	5
T3710 8	220mm (8 1/4")	40 - 100mm	J3	5
T3710 11	300mm (12")	85 - 140mm	J4	5



**Circlip Pliers - Outside Straight**

High alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Chequered handles for grip. DIN 5254A

Item No.	↔	∅	DIN	📦
T3711 0	140mm (5 1/2")	3 - 10mm	A0	5
T3711 5	140mm (5 1/2")	10 - 25mm	A1	5
T3711 7	180mm (7")	19 - 60mm	A2	5
T3711 8	220mm (8 1/4")	40 - 100mm	A3	5
T3711 11	300mm (12")	85 - 140mm	A4	5



**Circlip Pliers - Inside Bent**

High alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Chequered handles for grip. DIN 5256D

Item No.	↔	∅	DIN	📦
T3712 5	140mm (5 1/2")	12 - 25mm	J11	5
T3712 7	180mm (7")	19 - 60mm	J21	5
T3712 8	220mm (8 1/4")	10 - 100mm	J31	5



**Circlip Pliers - Outside Bent**

High alloy steel, drop forged, hardened & tempered for exceptional strength & durability. Chequered handles for grip. DIN 5256B

Item No.	↔	∅	DIN	📦
T3713 0	140mm (5 1/2")	3 - 10mm	A01	5
T3713 5	140mm (5 1/2")	10 - 25mm	A11	5
T3713 7	180mm (7")	19 - 60mm	A21	5
T3713 8	220mm (8 1/4")	40 - 100mm	A31	5



**Circlip Pliers - Adjustable**

Push button changeover from inside to outside configuration for convenience.

Item No.	📦
T3716	3


## Snips



### Cable Snips

Designed for fast and efficient cutting of aluminium & copper wires and plastic sheathed cables. Stainless steel razor sharp shearing blades for outstanding cutting performance. Spring assisted blade opening with safety closing catch for convenience. PVC coated handles for comfort and grip.

Item No.			
430008	165mm (6 1/2")	10mm	3



### Tin Snips

Forged alloy steel for strength & durability. Hardened & tempered jaws for high cutting performance. Stop pin to prevent finger nipping during use.

Item No.		
T4536 08	200mm (8")	3
T4536 10	250mm (10")	3



### Compound Action Snips

Compound action, high leverage design for easy cutting of steel, stainless steel, titanium etc. Forged chrome molybdenum steel jaws, hardened and tempered for long term cutting performance. Ergonomic grips with slip guards for safety. Blades configured for either, right hand curve, left hand curve or straight cuts.

Item No.			
T4537AS	240mm (10")	Straight	3
T4537AL	240mm (10")	Left	3
T4537AR	240mm (10")	Right	3
Z4537 1			


## Riveting Pliers



### Riveting Pliers

Heavy duty steel construction for exceptional strength & durability. Colour coded interchangeable nose bushes for convenience (nose spanner included). 3 jaw mechanism for increased grip and outstanding long term performance - 50% greater gripping strength than a standard 2 jaw riveter. Ergonomic anti-slip handles.


Item No.		
T3820	260mm (10 1/2")	3
T3820AS		1



### Riveting Plier Nozzles

Nozzles for T3820.

Item No.
Z3820 12
Z3820 15
Z3820 18



### Lazy Tong Riveter

Heavy duty steel construction for exceptional strength & durability. Anti shock design protects from injuries to wrist, arm or shoulder. Cushion grip handle for superior grip & comfort. Colour coded interchangeable nose bushes.

Item No.		
T3822A	305 - 780mm (12 - 32 1/2")	1
Z3822A/34		





### Pop Riveting Tool

Manufactured from hardened steel and aluminium for longer life. High leverage anti slip handles for power and ease of operation. Swivel head with extended nose for access in confined spaces. Interchangeable nose bushes for 2.38mm (3/32"), 3.15mm (1/8"), 4mm (5/32") & 4.8mm (3/16") rivets. Storage clip/nozzle spanner included.

### Washers (Pack of 100)

Galvanised steel for corrosion resistance.

Item No.
T3829

Item No.		
T3824 12	3.15mm (1/8")	6
T3824 15	4mm (5/32")	6
T3824 18	4.8mm (3/16")	6



### Rivets - Aluminium (Pack of 50)

Colour coded for simple size identification.

### Punch Pliers



Item No.		
T3819A 408	3.15 x 6mm (1/8 x 1/4")	15
T3819A 412	3.15 x 9mm (1/8 x 3/8")	15
T3819A 415	3.15 x 12mm (1/8 x 1/2")	15
T3819A 508	4 x 6mm (5/32 x 1/4")	15
T3819A 512	4 x 9mm (5/32 x 3/8")	15
T3819A 515	4 x 12mm (5/32 x 1/2")	15
T3819A 612	4.8 x 16mm (3/16 x 3/8")	15
T3819A 615	4.8 x 16mm (3/16 x 1/2")	15
T3819A 620	4.8 x 16mm (3/16 x 5/8")	15

### Revolving Punch Pliers

Specially hardened steel punches and brass anvil for long term cutting performance. 6 punch revolving head marked with size for convenience. Black lacquered coating for corrosion protection. Suitable for leather, plastic, card, etc.

Item No.		
T3817	220mm (8 1/4")	5

### Fencing Pliers



### Fencing Pliers

Heavy duty multi-purpose tool to hammer and draw out staples; strains, twists and splices wire. Manufactured to the original German pattern. High grade steel polished head. Red PVC handles.

Item No.			
T3866	270mm (10 5/8")	645g	3





# Screwdrivers

<b>Dextro VDE</b>	<b>31</b>
<b>Dextro VDE Slim</b>	<b>32</b>
<b>Stubby VDE Slim</b>	<b>35</b>
<b>Dextro</b>	<b>37</b>
<b>HD Classic</b>	<b>39</b>
<b>Triton XLS</b>	<b>43</b>
<b>Ratchet Screwdrivers</b>	<b>46</b>
<b>Impact Drivers</b>	<b>46</b>
<b>Magnetiser / Demagnetiser</b>	<b>46</b>



# dextro<sup>TM</sup> VDE

## Premium quality insulated screwdrivers

1. Tip type marking for easy identification.
2. Ergonomically shaped, dual component handle for increased comfort, control and safety.
3. Long fine neck for precise fingertip control.
4. Ridges along the head give extra grip in that last 1/4 turn.
5. Handle injection moulded directly to blade giving the ultimate bond for increased reliability and durability.
6. VDE approved - individually tested to 10,000V for safe live working up to 1,000V.
7. Premium quality chrome vanadium steel blade for exceptional strength and durability.
8. Precision machined tip for an exact screw fit and damage free screwdriving.



Conforms to IEC 60900. Approved and independently audited by the German VDE institute.

## Dextro VDE



## VDE Screwdrivers - Slotted Parallel

BS EN 60900, VDE0682/201, ASTM-F 1505, ISO 2380-2

Item No.					
T49144-025	2.5mm (3/32")	75mm (3")	0.4mm (0.016")	95mm (3 3/4")	6
T49144-030	3.0mm (1/8")	100mm (4")	0.5mm (0.020")	95mm (3 3/4")	6
T49144-035	3.5mm (9/64")	100mm (4")	0.6mm (0.024")	95mm (3 3/4")	6
T49144-040	4.0mm (5/32")	100mm (4")	0.8mm (0.031")	107mm (4 1/32")	6
T49144-055	5.5mm (7/32")	125mm (5")	1.0mm (0.039")	120mm (4 3/4")	6
T49144-065	6.5mm (1/4")	150mm (6")	1.2mm (0.047")	120mm (4 3/4")	6
T49144-080	8.0mm (5/16")	175mm (7")	1.2mm (0.047")	135mm (5 1/16")	6
T49144-100	10.0mm (25/64")	200mm (8")	1.6mm (0.063")	135mm (5 1/16")	6



## VDE Screwdrivers - Pozidriv

BS EN 60900, VDE0682/201, ASTM-F 1505, DIN ISO 8764

Item No.					
T49143-0	PZ0	3.5mm (9/64")	60mm (2 3/8")	95mm (3 3/4")	6
T49143-1	PZ1	5.0mm (3/16")	80mm (3 1/8")	107mm (4 1/32")	6
T49143-2	PZ2	6.0mm (15/64")	100mm (4")	107mm (4 1/32")	6
T49143-2200	PZ2	6.0mm (15/64")	200mm (8")	120mm (4 3/4")	6
T49143-3	PZ3	8.0mm (5/16")	150mm (6")	135mm (5 1/16")	6



## VDE Screwdrivers - Phillips

BS EN 60900, VDE0682/201, ASTM-F 1505, DIN ISO 8764

Item No.					
T49142-0	PH0	3.5mm (9/64")	60mm (2 3/8")	95mm (3 3/4")	6
T49142-1	PH1	5.0mm (3/16")	80mm (3 1/8")	107mm (4 1/32")	6
T49142-2	PH2	6.0mm (15/64")	100mm (4")	120mm (4 3/4")	6
T49142-3	PH3	8.0mm (5/16")	150mm (6")	135mm (5 1/16")	6



## VDE Screwdrivers - Modulo

BS EN 60900, VDE0682/201, ASTM-F 1505

Item No.					
T49145-1	1	5.0mm (3/16")	80mm (3 1/8")	107mm (4 1/32")	6
T49145-2	2	6.0mm (15/34")	100mm (4")	120mm (4 3/4")	6



## VDE Screwdriver Set/2 - Modulo

CONTENTS: Modulo 1 x 80mm &amp; Modulo 2 x 100mm.

BS EN 60900, VDE0682/201, ASTM-F 1505

Item No.			
T49146	1 & 2		6



## VDE Screwdriver Set/5 - SLP/PH

CONTENTS: 3 x slotted parallel, sizes: 2.5 x 75, 4 x 100 & 5.5 x 125mm. 2 x Phillips, sizes: PH1 x 80 & PH22 x 100mm.  
BS EN 60900, VDE0682/201, ISO 2380-2, DIN ISO 8764

Item No.	i	⊖	⊕	📦
T49182D	Set of 5	2.5, 4.0 & 5.5mm	PH 1 & 2	18



## VDE Screwdriver Set/7 - SLP/PZ

CONTENTS: 4 x slotted parallel, sizes: 2.5 x 75, 4 x 100, 5.5 x 125 & 6.5 x 150mm. 3 x Pozidriv, sizes: PZ0 x 60, PZ1 x 80 & PZ2 x 100mm.  
BS EN 60900, VDE0682/201, ISO 2380-2, DIN ISO 8764

Item No.	i	⊖	⊕	📦
T49193D	Set of 7	2.5, 4.0, 5.5 & 6.5	PZ 0, 1 & 2	18



## VDE Screwdriver Set/7 - SLP/PH

CONTENTS: 4 x slotted parallel, sizes: 2.5 x 75, 4 x 100, 5.5 x 125mm & 6.5 x 150mm. 3 x Phillips, sizes: PH0 x 60, PH1 x 80 & PH2 x 100mm.  
BS EN 60900, VDE0682/201, ISO 2380-2, DIN ISO 8764

Item No.	i	⊖	⊕	📦
T49192D	Set of 7	2.5, 4.0, 5.5 & 6.5mm	PH 0, 1 & 2	18



## VDE Screwdriver Set/5 - SLP/PZ

CONTENTS: 3 x slotted parallel, sizes: 2.5 x 75, 4 x 100 & 5.5 x 125mm. 2 x Pozidriv, sizes: PZ1 x 80 & PZ2 x 100mm.  
BS EN 60900, VDE0682/201, ISO 2380-2, DIN ISO 8764

Item No.	i	⊖	⊕	📦
T49183D	Set of 5	2.5, 4.0 & 5.5mm	PZ 1 & 2	18

## Dextro VDE Slim



## VDE Slim Screwdrivers - Slotted

BS EN 60900, VDE0682/201, ASTM-F 1505, ISO 2380-2

Item No.	⊖	🔧	⊖	🔧	📦
T49244-035	3.5mm (9/64")	100mm (4")	0.6mm (0.024")	95mm (3 3/4")	6
T49244-040	4.0mm (5/32")	100mm (4")	0.8mm (0.031")	95mm (3 3/4")	6
T49244-055	5.5mm (7/32")	125mm (5")	1.0mm (0.039")	107mm (4 1/8")	6



## VDE Slim Screwdrivers - Pozidriv

BS EN 60900, VDE0682/201, ASTM-F 1505, DIN ISO 8764

Item No.	⊕	⊖	🔧	🔧	📦
T49243-1	PZ1	5.0mm (3/16")	100mm (4")	95mm (3 3/4")	6
T49243-2	PZ2	6.0mm (15/64")	125mm (5")	107mm (4 1/8")	6






## Premium quality insulated screwdrivers

The C.K. DextroVDE Slim screwdrivers provide easy access to recessed screws. Eliminating the need to remove insulation and compromise safety, they are slim enough to fit into the tightest of spaces, yet still offer outstanding torsional strength and active torque feedback for an extended working life.

1. Slim shafted insulated blades - allow access to recessed screws and fixings.
2. VDE approved - individually tested to 10,000V for safe working up to 1,000V.
3. German manufactured - quality and performance assured.
4. Dual component, ergonomic handle - specifically designed for use by electricians.
5. Premium quality chrome vanadium steel blades - for exceptional strength and durability.



Conforms to IEC 60900. Approved and independently audited by the German VDE institute.

# Screwdrivers



## VDE Slim Screwdrivers - Phillips

BS EN 60900, VDE0682/201, ASTM-F 1505, DIN ISO 8764

Item No.	⊕	∅	↔	↔	📦
T49242-1	PH1	5.0mm (3/16")	100mm (4")	95mm (3 3/4")	6
T49242-2	PH2	8.0mm (5/16")	125mm (5")	107mm (4 1/2")	6



## VDE Slim Screwdrivers - Modulo

BS EN 60900, VDE0682/201, ASTM-F 1505

Item No.	⊗	∅	↔	↔	📦
T49245-1	MOD1	5.0mm (3/16")	100mm (4")	95mm (3 3/4")	6
T49245	MOD1.5	5.0mm (3/16")	100mm (4")	95mm (3 3/4")	6
T49245-2	MOD2	6.0mm (15/34")	125mm (5")	107mm (4 1/2")	6



## VDE Slim Screwdriver Set

CONTENTS: 3 x slotted parallel, sizes: 3.5 x 100, 4 x 100 & 5.5 x 125mm. 2 x Pozidriv, sizes: PZ1 x 100 & PZ2 x 125mm.

BS EN 60900, VDE0682/201, ISO 2380-2, DIN ISO 8764

Item No.	i	⊖	⊗	📦
T49283D	Set of 5	3.5, 4.0 & 5.5mm	PZ 1 & 2	18



## VDE Slim Glo Screwdriver Set

Glow in the dark handles. Never lose your tools again. CONTENTS: 3 x slotted parallel, sizes: 3.5 x 100, 4 x 100 & 5.5 x 125mm. 2 x Pozidriv, sizes: PZ1 x 100 & PZ2 x 125mm

BS EN 60900, VDE0682/201, ISO 2380-2, DIN ISO 8764

Item No.	i	⊖	⊗	📦
T49283PD	Set of 5	3.5, 4.0 & 5.5mm	PZ 1 & 2	18



## VDE Interchangeable Slim Set 16pc

VDE approved - individually tested to 10,000v for safe working up to 1,000v. Soft grip handles for increased comfort. Quick lock mechanism for quick and easy blade interchange. Toughened alloy steel blades for exceptional durability. Compact fabric storage pouch with integral belt loop. Slim shafted 1000V insulated blades allow access to recessed screws and fixings. CONTENTS: 1000 V VDE Interchangeable Handle, 1000 V Precision VDE Interchangeable handle, 1000V VDE Slim Screwdriver Blades: Modulo 1 x 80, Modulo 2 x 100, Pozidriv 1 x 80, Pozidriv 2 x 100, Slotted 3.5 x 100, Slotted 4.5 x 100, Slotted 5.5 x 100, Slotted 6.5 x 100, PH 1 x 80, PH 2 x 100, T10 x 100, T15 x 100, T20 x 100, T25 x 100, Fabric Storage Pouch. - Replacement blades available.

Item No.	i	i	📦
T4935	Set of 16		6
T4935PH1	PH1	Replacement Blade	6
T4935PH2	PH2	Replacement Blade	6
T4935S55	Slotted 5.5mm	Replacement Blade	6
T4935S65	Slotted 6.5mm	Replacement Blade	6
T4935T10	T10	Replacement Blade	6
T4935T15	T15	Replacement Blade	6
T4935T20	T20	Replacement Blade	6
T4935T25	T25	Replacement Blade	6



## VDE Slim Interchangeable Screwdriver Set

VDE approved - individually tested to 10,000V for safe working up to 1,000V. Soft grip handles for increased comfort. Quick lock mechanism for quick and easy blade interchange. Toughened alloy steel blades for exceptional durability. Compact fabric storage pouch with integral belt loop. Slim shafted 1000V insulated blades allow access to recessed screws and fixings. CONTENTS: 1000V VDE High Torque Screwdriver Handle, 1000V VDE Precision Screwdriver Handle, 1000V VDE Screwdriver Blades: 3.5x100mm, 4.5x80mm, and 6.0x100mm. PZ1x80mm and PZ2x100mm. MOD1 and MOD2. Fabric storage pouch.

BS EN 60900, VDE0682/201, ASTM-F 1505, ISO 2380-2, DIN ISO 8764

Item No.	i	i	📦
T4925		Set	1
T4925S35	Slotted 3.5mm	Replacement Blade	
T4925S45	Slotted 4.5mm	Replacement Blade	
T4925S60	Slotted 6.0mm	Replacement Blade	
T4925PZ1	Pozidriv 1	Replacement Blade	10
T4925PZ2	Pozidriv 2	Replacement Blade	10
T4925MOD1	Modulo 1	Replacement Blade	10
T4925MOD2	Modulo 2	Replacement Blade	10

## Stubby VDE Slim



### Stubby VDE Slim Screwdrivers - Slotted

EN 60900, VDE0682/201, ASTM-F 1505

Item No.					
T48344-040	4.0mm (5/32")	46mm (1 13/16")	0.8mm (0.031")	60mm (2 23/64")	6
T48344-055	5.5mm (7/32")	46mm (1 13/16")	1.0mm (0.039")	60mm (2 23/64")	6



### Stubby VDE Slim Screwdriver - Pozidriv

EN 60900, VDE0682/201, ASTM-F 1505

Item No.					
T48343-2	PZ 2	6.0mm (15/64")	46mm (1 13/16")	60mm (2 23/64")	6



### Stubby VDE Slim Screwdriver - Modulo

EN 60900, VDE0682/201, ASTM-F 1505

Item No.					
T48345-2	MOD 2	6.0mm (15/34")	46mm (1 13/16")	60mm (2 23/64")	6



### Stubby VDE Slim Screwdriver Set/4

CONTENTS: T48344-040 SL4.0mm x 1, T48344-050 SL5.5mm x 1, T48343-2 PZ2 x 1, T48345-2 MOD x 1

EN 60900, VDE0682/201, ASTM-F 1505

Item No.	
T48349	Set of 4



## VDE Screwdrivers

1. Ideal for use in confined spaces.
2. Slim shafted insulated blades ~ allow access to recessed screws and fixings.
3. VDE approved ~ individually tested to 10,000V for safe working up to 1,000V.
4. Premium quality chrome vanadium steel blades for exceptional strength and durability.





# dextro™

## Premium quality screwdrivers

1. Tip type marking for easy identification.
2. Ergonomically shaped, dual component handle for increased comfort, control and safety.
3. Long fine neck for precise fingertip control.
4. Ridges along the head give extra grip in that last 1/4 turn.
5. Handle injection moulded directly to blade giving the ultimate bond for increased reliability and durability.
6. Premium quality chrome vanadium steel blade for exceptional strength and durability.
7. Precision machined tip for an exact screw fit and damage free screwdriving.



## Dextro



## Dextro Screwdrivers - Slotted Parallel

ISO 2380-2

Item No.					
T49125-025	2.5mm (3/32")	75mm (3")	0.4mm (0.061")	95mm (3 3/4")	6
T49125-030	3.0mm (1/8")	75mm (3")	0.5mm (0.020")	95mm (3 3/4")	6
T49125-03025	3.0mm (1/8")	250mm (10")	0.5mm (0.020")	95mm (3 3/4")	6
T49125-035	3.5mm (9/64")	100mm (4")	0.6mm (0.024")	95mm (3 3/4")	6
T49125-040	4.0mm (5/32")	125mm (5")	0.8mm (0.031")	107mm (4 1/2")	6
T49125-055	5.5mm (7/32")	150mm (6")	1.0mm (0.039")	120mm (4 3/4")	6



## Dextro Screwdrivers - Slotted Flared

ISO 2380-2

Item No.					
T49110-040	4.0mm (5/32")	75mm (3")	0.8mm (0.031")	107mm (4 1/2")	6
T49110-055	5.5mm (7/32")	100mm (4")	1.0mm (0.039")	120mm (4 3/4")	6
T49110-065	6.5mm (1/4")	150mm (6")	1.2mm (0.047")	120mm (4 3/4")	6
T49110-100	10.0mm (25/64")	200mm (8")	1.6mm (0.063")	135mm (4 5/16")	6



## Dextro Screwdrivers - Pozidriv

ISO 8764

Item No.					
T49113-0	PZ0	3.5mm (9/64")	60mm (23/8")	95mm (3 3/4")	6
T49113-1	PZ1	5.0mm (3/16")	75mm (3")	107mm (4 1/2")	6
T49113-1250	PZ1	5.0mm (3/16")	250mm (10")	107mm (4 1/2")	6
T49113-2	PZ2	6.0mm (15/64")	150mm (6")	120mm (4 3/4")	6
T49113-2250	PZ2	6.0mm (15/64")	250mm (10")	120mm (4 3/4")	6
T49113-3	PZ3	8.0mm (5/16")	150mm (6")	135mm (5 1/16")	6



## Dextro Screwdrivers - Phillips

ISO 8764

Item No.					
T49112-0	PH0	3.5mm (9/64")	60mm (2 3/8")	95mm (3 3/4")	6
T49112-1	PH0	5.0mm (3/16")	80mm (3 1/8")	107mm (4 1/2")	6
T49112-1250	PH1	5.0mm (3/16")	250mm (10")	107mm (4 1/2")	6
T49112-2	PH2	6.0mm (15/64")	100mm (4")	120mm (4 3/4")	6
T49112-2250	PH2	6.0mm (15/64")	250mm (10")	120mm (4 3/4")	6
T49112-3	PH3	8.0mm (5/16")	150mm (6")	135mm (5 1/16")	6



## Dextro Screwdrivers - Torx

Item No.	Icon	Ø	Length	Length	Quantity
T49117-06	T 06	3.0mm (1/8")	70mm (2 3/4")	95mm (3 3/4")	6
T49117-07	T 07	3.0mm (1/8")	70mm (2 3/4")	95mm (3 3/4")	6
T49117-08	T 08	3.0mm (1/8")	70mm (2 3/4")	95mm (3 3/4")	6
T49117-09	T 09	3.0mm (1/8")	70mm (2 3/4")	95mm (3 3/4")	6
T49117-10	T 10	3.0mm (1/8")	80mm (3 1/8")	107mm (4 1/2")	6
T49117-15	T 15	3.5mm (9/64")	80mm (3 1/8")	107mm (4 1/2")	6
T49117-20	T 20	4.0mm (5/32")	90mm (3 1/2")	107mm (4 1/2")	6
T49117-25	T 25	4.5mm (11/64")	90mm (3 1/2")	107mm (4 1/2")	6
T49117-27	T 27	5.5mm (7/32")	110mm (4 1/4")	120mm (4 3/4")	6
T49117-30	T 30	6.0mm (15/64")	110mm (4 1/4")	120mm (4 3/4")	6
T49117-40	T 40	7.0mm (9/32")	120mm (4 3/4")	135mm (5 1/8")	6



## Dextro Screwdrivers - Robertson

Item No.	Icon	Ø	Length	Length	Quantity
T49118-1	Size 1	6.0mm (15/64")	125mm (5")	120mm (4 3/4")	6
T49118-2	Size 2	6.0mm (15/64")	125mm (5")	120mm (4 3/4")	6
T49118-3	Size 3	6.0mm (15/64")	125mm (5")	120mm (4 3/4")	6



## Dextro Screwdriver Set/5 - SL/PZ

CONTENTS: 3 x slotted flared, sizes: 4 x 75, 5.5 x 100 & 6.5 x 150mm. 2 x Pozidriv, sizes: PZ1 x 80 & PZ2 x 100mm. ISO 2380-2, DIN ISO 8764

Item No.	i	Ø	Icon	Icon	Quantity
T49153	Set of 5	4.0, 5.5 & 6.5mm	PZ1 & PZ2		1



## Dextro Screwdriver Set/7 - SL/PZ

CONTENTS: 3 x slotted flared, sizes: 4 x 75, 5.5 x 100 & 6.5 x 150mm. 1 x slotted parallel, size: 3.0 x 75mm. 3 x Pozidriv, sizes: PZO x 60, PZ1 x 80 & PZ2 x 100mm. ISO 2380-2, DIN ISO 8764

Item No.	i	Ø	Icon	Quantity
T49163D	Set of 7	3.0, 4.0, 5.5 & 6.5mm	PZO, 1 & 2	



## Dextro Screwdriver Set/7 - SL/PH

CONTENTS: 3 x slotted flared, sizes: 4 x 75, 5.5 x 100 & 6.5 x 150mm. 1 x slotted parallel, size: 3 x 75mm. 3 x Phillips, sizes: PH0 x 60, PH1 x 80 & PH2 x 100mm. ISO 2380-2, DIN ISO 8764

Item No.	i	Ø	Icon	Icon	Quantity
T49162D	Set of 7	3.0, 4.0, 5.5 & 6.5mm	PH0, 1 & 2		18



HD Classic



HD Screwdrivers - Slotted Parallel

ISO 2380-2

Item No.					
T4965 03	3mm (1/8")	75mm (3")	0.5mm (0.02")	70mm (2 3/4")	6
T4965 04	4mm (5/32")	100mm (4")	0.8mm (0.03")	80mm (3 1/8")	6
T4965 05	4.5mm (11/64")	125mm (5")	0.8mm (0.03")	80mm (3 1/8")	6
T4965 06	5mm (3/16")	150mm (6")	0.8mm (0.03")	90mm (3 1/2")	6
T4965 08	5mm (3/16")	200mm (8")	0.8mm (0.03")	90mm (3 1/2")	6
T4965 12	6mm (15/64")	300mm (12")	1.0mm (0.04")	100mm (4")	6



HD Long Screwdrivers - Slotted Parallel

ISO 2380-2

Item No.					
T4975 06	3mm (1/8")	150mm (6")	0.5mm (0.02")	80mm (3 1/8")	6
T4975 08	3mm (1/8")	200mm (8")	0.5mm (0.02")	80mm (3 1/8")	6
T4975 10	4mm (5/32")	250mm (10")	0.8mm (0.03")	80mm (3 1/8")	6



HD Screwdrivers - Slotted Flared

ISO 2380-2

Item No.					
T4810 03	5mm (3/16")	75mm (3")	0.8mm (0.03")	90mm (3 1/2")	6
T4810 04	6mm (15/64")	100mm (4")	1.0mm (0.04")	100mm (4")	6
T4810 05	7mm (9/32")	125mm (5")	1.0mm (0.04")	100mm (4")	6
T4810 06	8mm (5/16")	150mm (6")	1.2mm (0.05")	110mm (4 1/4")	6
T4810 08	9mm (11/32")	200mm (8")	1.2mm (0.05")	120mm (4 3/4")	6
T4810 10	10mm (3/8")	250mm (10")	1.6mm (0.06")	130mm (5 1/8")	6
T4810 12	12mm (1/2")	300mm (12")	2.0mm (0.08")	130mm (5 1/8")	6



HD Screwdrivers - Strike Through

Strike through design for the most demanding applications.


ISO 2380-2

Item No.					
T4811 04	6mm (15/64")	100mm (4")	1.0mm (0.04")	100mm (4")	6
T4811 06	8mm (5/16")	150mm (6")	1.2mm (0.05")	110mm (4 1/4")	6
T4811 08	10mm (3/8")	200mm (8")	1.6mm (0.06")	120mm (4 3/4")	6
T4811 10	13mm (1/2")	250mm (10")	2.0mm (0.08")	130mm (5 1/8")	6

# HD classic

## Classic heavy duty screwdrivers

1. Shatter resistant acetate handle - wipe clean, oil and acid resistant.
2. Large square shape handle design for maximum torque.
3. Handle injection moulded directly to blade giving the ultimate bond for increased reliability and durability.
4. Anti roll flats to prevent the screwdriver rolling off sloping surfaces.
5. Chrome plated toughened alloy steel blade for increased strength and durability.
6. Precision machined tip for an exact screw fit and damage free screwdriving.





## HD Screwdrivers - Phillips

DIN ISO 8764

Item No.	+	Ø	↔	↔	📦
T4812 0	PH0	3.5mm (9/64")	65mm (2 1/2")	70mm (2 3/4")	6
T4812 1	PH1	5mm (3/16")	80mm (3 1/8")	90mm (3 1/2")	6
T4812 2	PH2	6mm (15/64")	100mm (4")	100mm (4")	6
T4812 3	PH3	8mm (5/16")	150mm (6")	110mm (4 1/4")	6
T4812 4	PH4	10mm (3/8")	200mm (8")	120mm (4 3/4")	6



## HD Long Screwdrivers - Phillips

ISO 8764

Item No.	+	Ø	↔	↔	📦
T4977 1	PH1	5mm (3/16")	250mm (10")	100mm (4")	6
T4977 2	PH2	6mm (15/64")	250mm (10")	110mm (4 1/4")	6



## HD Screwdrivers - Pozidriv

DIN ISO 8764

Item No.	+	Ø	↔	↔	📦
T4813 0	PZ0	3.5mm (9/64")	60mm (2 1/2")	70mm (2 3/4")	6
T4813 1	PZ1	5mm (3/16")	80mm (1/8")	90mm (3 1/2")	6
T4813 2	PZ2	6mm (15/64")	100mm (4")	100mm (4")	6
T4813 3	PZ3	8mm (5/16")	150mm (6")	110mm (4 1/4")	6
T4813 4	PZ4	10mm (3/8")	200mm (8")	120mm (4 3/4")	6



## HD Long Screwdrivers - Pozidriv

ISO 8764

Item No.	+	Ø	↔	↔	📦
T4987 1	PZ1	5mm (3/16")	250mm (10")	100mm (4")	6
T4987 2	PZ2	6mm (15/64")	250mm (10")	110mm (4 1/4")	6



## HD Stubby Screwdrivers - Slotted

ISO 2380-2

Item No.	—	↔	—	↔	📦
T4814 25	6.5mm (1/4")	25mm (1")	1.2mm (0.05")	60mm (2 3/8")	6
T4814 31	8mm (5/16")	25mm (1")	1.2mm (0.05")	60mm (2 3/8")	6



## HD Stubby Screwdrivers - Phillips

DIN ISO 8764

Item No.	+	Ø	↔	↔	📦
T4815 1	PH1	5mm (3/16")	25mm (1")	60mm (2 3/8")	6
T4815 2	PH2	6mm (15/64")	25mm (1")	60mm (2 3/8")	6





## HD Stubby Screwdrivers - Pozidriv

DIN ISO 8764

Item No.	⊕	∅	↔	↔	📦
T4816 1	PZ1	5mm (3/16")	25mm (1")	60mm (2 3/8")	6
T4816 2	PZ2	6mm (15/64")	25mm (1")	60mm (2 3/8")	6



## HD Screwdriver Bit Holder

High strength stainless steel magnetic bit holder for 1/4" bits.

Item No.	📦
T4581	6



## HD Nut Spinners

Extra deep socket for reaching nuts through which bolts protrude.

DIN 3125

Item No.	∅	↔	↔	📦
T4334M 03	3mm	130mm (5 1/8")	90mm (3 1/2")	3
T4334M 035	3.5mm	130mm (5 1/8")	90mm (3 1/2")	3
T4334M 04	4mm	130mm (5 1/8")	90mm (3 1/2")	3
T4334M 045	4.5mm	130mm (5 1/8")	90mm (3 1/2")	3
T4334M 05	5mm	130mm (5 1/8")	90mm (3 1/2")	3
T4334M 055	5.5mm	130mm (5 1/8")	90mm (3 1/2")	3
T4334M 06	6mm	130mm (5 1/8")	90mm (3 1/2")	3
T4334M 07	7mm	130mm (5 1/8")	100mm (4")	3
T4334M 08	8mm	130mm (5 1/8")	100mm (4")	3
T4334M 09	9mm	130mm (5 1/8")	100mm (4")	3
T4334M 10	10mm	130mm (5 1/8")	100mm (4")	3
T4334M 11	11mm	120mm (4 3/4")	110mm (4 1/4")	3
T4334M 12	12mm	120mm (4 3/4")	110mm (4 1/4")	3
T4334M 13	13mm	120mm (4 3/4")	110mm (4 1/4")	3



## HD Screwdriver Set/8 - SLF/PZ

CONTENTS: 4 x slotted flared, sizes: 6 x 100, 6.5 x 25, 7 x 125 & 8 x 100mm. 2 x slotted parallel, sizes: 3 x 75 & 4 x 100mm. 2 x Pozidriv, sizes: PZ1 x 80 & PZ2 x 100mm.

ISO 2380-2, DIN ISO 8764

Item No.	📦
T4999B	3

**Triton XLS**



**Triton Screwdrivers - Slotted Parallel**

ISO 2380-2

Item No.					
T4725-030	3.0mm (1/8")	75mm (3")	0.6mm (0.024")	89mm (3 5/8")	6
T4725-040	4.0mm (5/32")	100mm (4")	0.8mm (0.031")	100mm (4")	6
T4725-055	5.5mm (7/32")	250mm (10")	1.0mm (0.039")	100mm (4")	6



**Triton Screwdrivers - Slotted Flared**

ISO 2380-2

Item No.					
T4720-055	5.5mm (7/32")	100mm (4")	1.0mm (0.039")	100mm (4")	6
T4720-065	6.5mm (1/4")	150mm (6")	1.2mm (0.047")	108mm (4 1/4")	6
T4720-100	10mm (25/64")	200mm (8")	1.6mm (0.063")	118mm (4 5/8")	6



**Triton Screwdrivers - Phillips**

Item No.					
T4722-0	PH0	3.0mm (1/8")	60mm (2 3/8")	89mm (3 5/8")	6
T4722-1	PH1	5.0mm (3/16")	75mm (3")	100mm (4")	6
T4722-1250	PH1	5.0mm (3/16")	250mm (10")	100mm (4")	6
T4722-2	PH2	6.0mm (15/64")	100mm (4")	108mm (4 1/4")	6
T4722-2250	PH2	6.0mm (15/64")	250mm (10")	108mm (4 1/4")	6
T4722-3	PH3	8.0mm (5/16")	150mm (6")	118mm (4 5/8")	6



**Triton Screwdrivers - Pozidriv**

Item No.					
T4723-0	PZ0	3.0mm (1/8")	60mm (2 3/8")	89mm (3 5/8")	6
T4723-1	PZ1	5.0mm (3/16")	75mm (3")	100mm (4")	6
T4723-1250	PZ1	5.0mm (3/16")	250mm (10")	100mm (4")	6
T4723-2	PZ2	6.0mm (15/64")	100mm (4")	108mm (4 1/4")	6
T4723-2250	PZ2	6.0mm (15/64")	250mm (10")	108mm (4 1/4")	6
T4723-3	PZ3	8.0mm (5/16")	150mm (6")	118mm (4 5/8")	6



**Flexible Shafted Screwdriver**

Strong yet flexible shaft for access to screws and fixings in awkward places. Soft grip tri-lobe handle for exceptional comfort and control. Magnetic bit holder for positive bit retention. For use with 6mm - 1/4" hexagon screwdriver bits (not included).

Item No.				
T4760	200mm	110mm	6mm	6
T4760CBOX				1



**Triton Screwdriver Bit Holder**

Large softgrip tri-lobe handle for high torque applications. Strong and corrosion resistant stainless steel sleeve. Magnetic base and c-ring securely retains the bit in place.

Item No.		
T4516	6mm (1/4")	12

# triton XLS

Professional general purpose screwdrivers

1. Tip type marking for easy identification.
2. Large soft grip tri-lobe handle for exceptional comfort and high torque turns.
3. Handle injection moulded directly to blade giving the ultimate bond for increased reliability and durability.
4. Anti roll flats to prevent the screwdriver rolling off sloping surfaces.
5. Chrome plated, toughened alloy steel blade for increased strength and durability.
6. Magnetic tip holds the screw securely to the tip to aid positioning and setting.





### Triton Screwdriver Set/5 - SL/PH

CONTENTS: 2 x slotted flared, sizes: 5.5 x 100 & 6.5 x 150mm. 1 x slotted parallel, size: 4 x 100mm. 1 x Phillips, sizes: PH1 x 75 & PH2 x 100mm.

ISO 2380-2, DIN ISO 8764

Item No.



T4726

1



### Insulated Triton Set/5 - SL/PH

CONTENTS: 3 x slotted parallel, sizes: 2.5 x 75, 4 x 100 & 5.5 x 125mm. 2 x Phillips, sizes: PH1 x 80 & PH x 100mm.

BS EN 60900, ISO 2380-2, DIN ISO 8764

Item No.



T4728

1



### Triton Screwdriver Set/5 - SL/PZ

CONTENTS: 2 x slotted flared, sizes: 5.5 x 100 & 6.5 x 150mm. 1 x slotted parallel, size: 4 x 100mm. 2 x Pozidriv, sizes: PZ1 x 75 & PZ2 x 100mm.

ISO 2380-2, DIN ISO 8764

Item No.



T4727

1



### Insulated Triton Set/5 - SL/PZ

CONTENTS: 3 x slotted parallel, sizes: 2.5 x 75, 4 x 100 & 5.5 x 125mm. 2 x Pozidriv, sizes: PZ1 x 80 & PZ2 x 100mm.

BS EN 60900, ISO 2380-2, DIN ISO 8765

Item No.



T4729

1

T4729CBOX

1



## Ratchet Screwdrivers



### Ratchet Screwdriver/Socket Set

Hi-torque ratchet mechanism for durability. Left & right hand rotation plus lock action for convenience. Magnetic shaft for secure bit retention. Cushion grip handle with convenient internal bits storage compartment. CONTENTS: Ratchet screwdriver, Sockets: 6, 7, 8, 10, 11 and 13mm / 3/16, 1/4, 5/16, 11/32, 3/8 and 7/16", Slotted: 3 / 4 / 4.5 / 5 / 6 / 7 / 8 and 9mm, Phillips: PH0, PH1, PH2 and PH3, Pozidriv: PZ0, PZ1, PZ2 and PZ3, Tamperproof TX: T8, T10, T15, T20, T25, T27, T30 and T40, Hexagon: 1.5 / 2 / 2.5 / 3 / 4 / 5 / 5.5 and 6mm, 1/4" adaptor.

Item No.	i	📦
T4826D	Set of 46	3




### Ratchet Screwdriver & Bits Set

Magnetic shaft for secure bit retention. Hi-torque ratchet mechanism with left & right hand rotation plus lock action. Supplied with 10 bits. Cushion grip handle with convenient internal bits storage compartment. CONTENTS: Ratchet screwdriver. Screwdriver bits: 1 x slotted, sizes: 3.0, 4.7 & 6.3mm. 1 x PH, size: 1, 2 & 1 x hexagon, sizes: 3, 4 & 5mm.

Item No.	i	📦
T4829D	Set of 11	3

## Impact Drivers



### Impact Screwdriver & Bits Set

Heavy duty steel body - strong and durable. Chrome plated for corrosion protection. Shock absorbing grip for comfort & protection. Twist to reverse function for convenience. High strength chrome vanadium bits. Steel case for convenient storage. CONTENTS: Impact driver, 1/2" to 1/4" drive adaptor, Screwdriver bits: 1 x slotted, sizes: 8 & 10mm, 1 x Phillips, sizes: 2 & 3

Item No.	i	📦
T4928	Set of 6	2
T4928 362		10
T4928 363		10
T4928 802		10
T4928 803		10
T4928 36P2		10
T4928 36P3		10
T4928 36M08		10
T4928 36M10		10
T4928 36M12		10

## Magnetiser / Demagnetiser



### Magnetiser/Demagnetiser

To induce magnetism in screwdrivers, tweezers, etc. Pass slowly through lower (+) section. To remove magnetism, pass through upper (-) section. Display Packed.

Item No.	🏷️	📦
T1350	90g	3







**C.K.**  
**MIGHTY RODS**  
Mighty-Rods 10m Cable

Aggravates tire-fills Mighty-Rods Set, 10m



375 kg  
Tensile  
Strength

**CRIPPLE-FIXED**  
**WIGGLER-FIX**  
connections  
glued, indented, crimped

10 x 16  
(6mm)

**OPTIMAL BLEND**  
of rigidity & flexibility

**HIGH SHEEN RODS**  
anti-snap, anti-splitter



# Cable Routing

<b>MightyRods PRO</b>	<b>51</b>
<b>MightyScope</b>	<b>52</b>
<b>MightyRods</b>	<b>52</b>
<b>Cable Routing</b>	<b>54</b>
<b>Draw Tapes</b>	<b>54</b>







Next gen advanced technology

MightyRods PRO cable rods encompass a fusion of advanced technological features that deliver the ultimate in cable rod performance.

Improving on-the-job efficiency, MightyRods PRO cable rods get the job done.



### 100% SPLINTER PROOF RODS

SplinterSHIELD is an advancement in cable rod technology. The durable SplinterSHIELD coating fully encases the inner fibreglass rod to prevent harmful splintering.



### UNSURPASSED STRENGTH

Through the use of an innovative triple fixing system, the super tough zinc-plated steel Mighty-Fix connectors offer unsurpassed tensile strength in excess of 275kg. Furthermore, the ultra-slim profile reduces snagging and provides accessibility through smaller holes.




## MightyRods PRO



### MightyRods PRO 12m Super Set

12 meters of 100% splinter-proof rods. 4 rod flexibilities for overhead, under floor, tight angled and obstructed runs. Super flexible, low friction, Spira-FLEX rod for tight angled access points. Glow in the dark phosphorescent GLO rod for guiding a run of rods in low light conditions. Accessories: flexi-lead (mini-flex), ring, hook, gender changer, flat bullet, domed bullet, in-line swivel, torch, magnet, chain. CONTENTS: 2 x 1m rods 7mmØ / 8 x 1m rods 6mmØ / 1 x Rod SpiraFLEX 4mmØ / 1 x rod GLO 6mmØ / 1 x FlexiLead / 1 x Hook / 1 x Flat Bullet / 1 x Domed Bullet / 1 x Magnet / 1 x Ring / 1 x Gender Changer / 1 x In-line Swivel / 1 x Torch / 1 x Chain.

Item No.		
T5422	12 x 1m	1



### MightyRods 3pc Accessory Pack

Upgrade your MightyRod kit with this Super Kit upgrade pack. CONTENTS: Torch, Magnet and Chain.

Item No.		
T5441	3pc	1



### MightyRods PRO Cable Socks

Tapered woven steel mesh cable sock that provides a quick and secure method for securing cables to rods.

Item No.	Ø	
T5442 06	6 - 10mm	6
T5442 11	11 - 15mm	6



### MightyRods PRO 10m Standard Set

10 meters of 100% splinter-proof rods. 4 rod flexibilities for overhead, under floor, tight angled and obstructed runs. Super flexible, low friction, Spira-FLEX rod for tight angled access points. Accessories: flexi lead (mini-flex), ring, hook, gender changer, flat bullet, domed bullet, in-line swivel. CONTENTS: 2 x 1m rods 7mmØ / 7 x 1m rods 6mmØ / 1 x Rod SpiraFLEX 4mmØ / 1 x FlexiLead / 1 x Hook / 1 x Flat Bullet / 1 x Domed Bullet / 1 x Ring / 1 x Gender Changer / 1 x In-line Swivel.

Item No.		
T5421	10 x 1m	1



### MightyRods PRO 5m Starter Set

5 meters of 100% splinter-proof rods. 2 rod flexibilities for overhead, under floor, tight angled and obstructed runs. Accessories: flexi lead (mini-flex), ring, hook. CONTENTS: 5 x 1m rods of 6mmØ / 1 x Flexi Lead / 1 x ring / 1 x Hook.

Item No.		
T5420	5 x 1m	1



### MightyRods PRO 3.3m Toolbox Set

Slimline connectors reduce snagging and provide accessibility through smaller holes. 33cm rods are ideal for tight access applications. Convenient sized set for storage in tool box or tool bag. CONTENTS: 10 x 330mm rods with 6 mm Ø / 1 x flexible rod 190mm / 1 x ring / 1 x hook / 5mm adaptor.

Item No.		
T5419	10 x 330mm	1



## MightyRods PRO 6mm Rods - 2 Pack

A pair of flexible 6mmØ rods ideal for most common routing needs.

Item No.	Ø	i	📦
T5430	6mm	Flexible	1



## MightyRods PRO 7mm Rods - 2 Pack

A pair of more rigid 7mmØ rods ideal for overhead runs. They also provide greater control during straight cable runs.

Item No.	Ø	i	📦
T5431	7mm	Rigid	1



## MightyRods PRO 6mm Rod - GLO

A flexible 6mmØ rod, this phosphorescent GLO rod guides the way when routing in low light conditions.

Item No.	Ø	i	i	📦
T5432	6mm	Flexible	Phosphorescent	1



## MightyRods PRO 4mm SpiraFLEX

This super flexible 4mmØ rod is the perfect solution when access is tight or when navigating around obstacles. The innovative helical profile and PET material reduces friction and minimises snagging.

Item No.	Ø	i	📦
T5433	4mm	Super-Flexible	1



## MightyRods 7pc Accessory Pack

A full range of accessories from the MightyRod PRO Standard kit. CONTENTS: 1 x Flexi Lead, Hook, Ring, Gender Changer, Flat Bullet, Domed Bullet and In-line Swivel.

Item No.	i	📦
T5440	7pc	1

## MightyScope




## MightyScope Inspection Camera

The MightyScope comes with an onboard Wi-Fi hotspot that will stream in high resolution with a wireless range of up to 15m (50'). High resolution real time HD viewing with the ability to save photos and videos direct to your smart device gallery. The bright white LED's can be adjusted from the App to view in complete darkness when pushed into dark and confined spaces. This helps you investigate and diagnose problems. In the MightyScope App settings select to have the image view either normal view or always up. Digital zoom function - Digital zoom will give you a close up view from your MightyScope camera. Waterproof and dustproof - When the back cap is screwed on, the MightyScope is IP67 rated. Charge time - Quick Charge USB-C. From 0% - 100% battery charge in 100 minutes. Mode runtime - Light off: up to 110 minutes. Dimmed: up to 90 minutes. Full Beam: up to 70 minutes.

EN 55032:2015+A1 2020 EN 61000-3-2:2019+A1 2021 EN 61000-3-3:2013+A1 2019+A2 2021 EN55035:2017+A11:2020 EN301 489-1 V2,2,3 , EN301 489-17 V3,2,4 EN300 328-1 V2,2,2, EN50665:2017, EN IEC 62311:2020 EN IEC 62368-1-2020+A11 2020 EN IEC 62368-1:2020+A11:2020 Protection against Electric Shock - Class III

Item No.	↔	📶	☔
T5600	94mm x 24mm	15m	IP67

## MightyRods



## MightyRods 10m Cable Rods Set

10 meters of high sheen fibreglass and resin composite rods. Slimline connectors reduce snagging and provide accessibility through smaller holes. 5mmØ rods offer the optimal balance of rigidity and flexibility for the majority of cable routing requirements. CONTENTS: 10 x 1m rods, cable hook, 190mm coiled steel flexi lead, mini eye & ring, 5mm adaptor.

Item No.	↔	Ø	📦
T5410	10 x 1m	5mm	3



## Wireless inspection camera

Featuring adjustable bright white LEDs, HD streaming, built in Wi-Fi hotspot - wireless and rechargeable, digital zoom function and a free and easy to use app.

Wireless inspection camera for the end user needing to inspect, photograph or record video in locations with limited access or visibility. Can be used with C.K MightyRods/PRO cable routing products.

- Visual Inspection
- Cable Installation
- Maintenance
- Repair Work
- Job Site Ready

**NEVER  
LOSE SIGHT**








## MightyRods 3.3m Cable Rods Set

Conveniently sized set for storage in toolbox or tool bag. Ideal for tight access applications. Combined total length of 3.3m. 5mmØ rods offer the optimal blend of rigidity & flexibility. CONTENTS: 10 x 330mm rods, cable hook, 190mm coiled steel flexi lead, mini eye & ring, thread adaptor.

Item No.		
T5411		10



## Gloworm Cable Router

Ideal for running cables around tight corners, through insulation filled walls, underneath flooring and across ceilings. Natural curvature aids routing around short tight bends - can also be straightened out for straight line runs. Innovative glow in the dark phosphorescent polymer construction aids routing in low light conditions.

Item No.		
T5460	4m	5



## MightyRods Carry Case

Durable polyester construction with reinforced base. Adjustable shoulder strap for convenient carrying. Two external pockets: Large pocket, capable of accommodating C.K MightyRods Toolbox cable rod set. Small pocket, to accommodate cable rod accessories.

Item No.		
T5450	1200mm	1

## Cable Routing



## SpiraFLEX Draw Tapes

Innovative spiral design significantly reduces frictional resistance allowing for longer cable runs. Manufactured from an advanced polyethylene terephthalate (PET) material - super flexible and immensely tough. Considerably less kinking and coiling compared to nylon and steel tapes. Compatible with C.K MightyRod accessories. Supplied within a protective impact resistant rewindable cassette.

Item No.			
T5510	10m	4mm	3
T5520	20m	4mm	3
T5530	30m	4mm	3

## Draw Tapes



## Steel Wire Draw Tape - 50m

Superior quality draw tape. Steel core wire for exceptional tensile strength. POM (Polyoxymethylene) coating for abrasion resistance and minimal friction when pulling cable. Flexible head attachment for navigating conduit with multiple bends.

Item No.			
495055	50m (164ft)	5.5mm	10



## POM Draw Tape - 30m

High quality draw tape constructed of three intertwining POM (Polyoxymethylene) strands. Helical tape structure for reduced friction and high tensile strength. Flexible head attachment for navigating conduit with multiple bends. Robust plastic casing for convenience during storage and transportation.

Item No.	Length	Ø	Icon
495056	30m (98ft)	6mm	10



## Nylon Draw Tapes

Nylon draw tape for low friction and high strength during cable pulling applications. Flexible head attachment for navigating conduit with multiple bends. Red coloured tape for improved visibility in conduit with existing cables. Robust plastic casing for convenience during tape rewind, storage and transportation. Non-conductive properties for safe working practices.

Item No.	Length	Ø	Icon
495050	10m (33ft)	4mm	5
495051	15m (49ft)	4mm	5
495052	20m (66ft)	4mm	5
495053	25m (82ft)	4mm	5
495054	30m (98ft)	4mm	5



## Draw Eye for Draw Tapes - 4mm

Draw Eye for pulling cable through conduit. For Draw Tapes with a diameter of 4mm.

Item No.	Ø	Icon
495058	4mm	100



## Flexible Head and Draw Eye - 4mm

Flexible head for guiding cable through conduit. Draw Eye for pulling cable through conduit. For Draw Tapes with a diameter of 4mm. CONTENTS: 1 x flexible head / 1 x draw eye.

Item No.	Ø	Icon
495057	4mm	100



## Electricians Draw Tape Reel

For pulling cables into conduit tubes. Special flexible spring steel for outstanding strength & reliability. Hooked end for smooth feed & minimal snagging. Housed in a heavy duty dispenser for convenient storage. Integral braking system for non-slip cable pull through.

Item No.	Length	Icon
495008	15.2m (50ft)	1



## Electricians Draw Tape

Lead spring guide for smooth feed & minimal snagging. Polymer tape for strength & reliability. Non-conductive & non-corroding for safety & long life.

Item No.	Length	Icon
495005	10m	3
495006	20m	3
495007	30m	2




## Draw Tape Lubricant

Reduced friction whilst pulling cable through conduit. Formula: Water, Petroleum Wax, Stabilizer. Store at temperatures between 40-120°F / 4-48°C. Compatible with all common cable insulation materials. Creates a thin, non-conductive film that won't clog conduit. Odourless.

Item No.	Volume	Icon
495059	950ml	12





WIRE  
STRIPPER  
↓  
10-24  
0.2-6.0



# Electricians' Specialist Tools

<b>Cable &amp; Wire Stripping</b>	<b>58</b>
<b>Cable &amp; Wire Cutting</b>	<b>60</b>
<b>Cable Tie Guns</b>	<b>61</b>
<b>Cable Tackers</b>	<b>62</b>
<b>Electrical Installation</b>	<b>63</b>
<b>Mainstesters</b>	<b>63</b>
<b>Voltage Detectors</b>	<b>63</b>
<b>Switch Keys</b>	<b>64</b>
<b>Hexagon Keys</b>	<b>64</b>
<b>Re-Threading Tools</b>	<b>65</b>
<b>Electrical Installation</b>	<b>65</b>
<b>Soldering</b>	<b>65</b>




# ARMOURSlice™

Strip away the hassle

## SWA cable stripper

Strips armoured cable up to 50% faster than conventional methods.

1. Scores armour strands to a uniform depth for a clean break off.
2. Rugged metal alloy body with integrated blade holder.
3. Strips cables from 12mm up to 36mm.



## Cable & Wire Stripping



### ArmourSlice SWA Cable Stripper

Scores armour strands to a uniform depth for a clean break off and trouble free gland connection. Automatic cable clamp applies constant pressure throughout the cut with no retightening necessary. Wide cable clamp ensures perfect blade to cable alignment for precise cuts.

Item No.	i	● I	📦
T2250	ArmourSlice	12 - 36mmØ	3
T2255	Pack of 5 Spare Blades		6



### Automatic Wire Stripper Pro

Replaceable stainless steel cutting blade - for long life. Automatic single action stripping of wires without adjustment - for copper/aluminium wire 0.05 - 8.5mm<sup>2</sup>. Unique two component contoured handle for comfort and secure grip. Micro adjustment knob for precise, repetitive stripping of copper, aluminium wire, solid or stranded.

Item No.	📦
T3943	8



### Auto Cable/Wire Stripper


Designed for stripping flat cables up to 12mm in width. Removes both the external sheathing and internal conductor insulation. Automatic size adjustment for convenience. Integrated wire bending hole for termination preparation. Replaceable blades.

Item No.	mm <sup>2</sup> /AWG	📦
T1260	0.75 - 2.5 / 18 - 14 AWG	6



**Single Core Auto Wire Stripper**

Designed for stripping solid & stranded wires from 0.2 - 6.0mm (24-10 AWG). Automatic wire size adjustment for convenience. Integrated wire cutter. Comfortable dual-compound soft grip handle design. Adjustable length stop (6 - 18mm). Replaceable blades.

Item No.	mm <sup>2</sup> / AWG	
T1261	0.2 - 6.0mm / 24 - 10 AWG	8



**Flat & Round Cable Stripper**

Modular - Intelligent bracket change system for all common cable types 4 - 28mm Ø. Universal - Compatible with flat cable 1.5 - 10mm including LSOH/LSF. Built for safety - Recessed blade with protection mechanism reduces injuries. Intuitive Design - Ergonomic handle for increased comfort, unique sight window to monitor cut progress. TÜV AND GS Approved.

Item No.	Ø
T1290	4 - 28mm (0.16 - 2.75")
T1291	1.5 - 10mm inc. LSOH/LSF
Z1290 1	2.5mm LSOH/LSF
Z1290 2	6mm LSOH/LSF
Z1290 3	10mm LSOH/LSF



**Universal Cable Stripper**


Razor sharp, pre-set stripping blades for fast, precise and damage free stripping of all common round cables. Suitable for stripping cables with 8 - 15mmØ. 2 stripping notches with length stop for stripping conductors. Suitable for stripping wires of 1.5, 2.5mm<sup>2</sup> (16, 14 AWG). Internal length stop can be re-positioned for left and right hand use.

Item No.	Ø	
T1270	4 - 15mm (3/16 - 9/16")	12



**Coax Cable Stripper**

Razor sharp, pre-set stripping blades for fast, precise and damage free stripping of all common coaxial cables. Suitable for stripping cables of 4.8 - 7.5mmØ. Also suitable for stripping 3-core flex. Both ends of tool marked for correct order of use. Dual compound handle for improved grip and safety.

Item No.	Ø	
T1271	4.8 - 7.5mm (3/16 - 19/64")	18



**Cable Knife**

Blade repositions for cutting both around and along cable sheathing. Adjustable cutting depth to prevent damage to inner conductors. Titanium-Nitride (TIN) coated blade to prolong blade sharpness. Spare cutting blade stored within the handle.

Item No.	Ø	
T1280	8 - 28mm (5/16 - 1 1/8")	6



**DataComms Cable Stripper**

Razor sharp, pre-set stripping blades for fast, precise and damage free stripping of datacomms cables. Pre-set precision stripping blades for damage free conductor stripping.

Item No.	
T1272	140



## Fibre Optic Cable Stripper

For fibre-optic, coaxial and other insulated cables with 6 - 25mm diameter. For plastic tubes with 6 - 25mm diameter. Precise setting options: operate with one hand, manual adjustment from circular to longitudinal cuts with swivel lever. Exact positioning of cable in the housing socket prior to stripping. Easy and safe stripping, even through hard outer sheaths. Ergonomic housing made out of high-performance plastic. Replacement blade easily interchangeable. Lightweight.

### Item No.

430009



## Kabifix Cable Stripper

Dual purpose cable stripper and plastic tube cutting tool. Cutting blade automatically repositions from cutting around, to cutting along the sheath for fast and damage free stripping. Hardened steel blade for outstanding long term performance. High grade polyamide construction - light and strong. Adjustable cutting depth for damage free stripping.

### Item No.

430004



6 - 28mm



3

395041

10



## VDE Cable Sheath Strip Knife

A specially adapted knife for slitting the outer sheath of cables without damaging the inner conductors with a double edged blade to cut on the push and pull stroke. Other features include: Comfortable dual component handle. VDE approved - tested to 10,000V for safe working up to 1,000v. Hardened stainless steel blade. Supplied with protective cap for safe storage.

### Item No.

T0990



185mm (3 1/2")



6

## Cable & Wire Cutting



## Electricians Knife

Locking pocket knife. With a durable, sharp, high carbon steel blade and wire stripping notch for fast and convenient cable & wire stripping.

### Item No.

484001



95mm



3



**Electricians Scissors**

Heavy duty design for shearing soft cables up to 22mm diameter, insulation materials, tape, cable ties and many other materials. Micro serrated stainless steel blades, hollow ground for self sharpening, superior cutting performance. Integrated cutting notch for effective cable & wire stripping. Belt pouch for convenient storage. Blade length: 42mm.

Item No.	Diagram	Quantity
492001		6



**Kevlar Scissors**

Specially designed for cutting DuPont Kevlar® fibres in fibre optic cables - also suitable for cutting DuPont Kevlar® webbing, plastic canvas, upholstery and many other materials. High carbon alloy steel with molybdenum and vanadium blades, hardened for long lasting cutting performance - guaranteed for up to 1000 cuts. Precision hollow-ground, micro-serrated jaw prevents the fibres from slipping and ensures a clean cut. Ergonomic, thermoplastic moulded handles allow for left and right handed users. Note: DuPont and Kevlar® are trademarks or registered trademarks of E.I. du Pont de Nemours and Company.

Item No.	Diagram	Weight	Quantity
T4505		90g	12

**Cable Tie Guns**



**Cable Tie Gun**

Designed for automatic tensioning and trimming of cable ties. Glass fibre reinforced polyamide construction - light and strong. Tension adjuster for the perfect tensioning of different widths of cable ties. For cable ties from 2.4 - 4.8mm.

Item No.	Diagram	Quantity
495003		12



**Cable Tie Gun - Heavy Duty**

Designed for automatic tensioning and trimming of cable ties. Heavy duty stainless steel construction for outstanding long term performance. Tension adjuster for the perfect tensioning of different widths of cable ties. Capacity: 4.7 - 13mm cable ties.

Item No.	Diagram	Quantity
495004		10




## Cable Tackers



### Cable Tacker - Low Voltage Cable


Heavy duty, tough cast aluminium body for strength & durability. Bi-material ergonomic handle for comfort & reduced fatigue. Unique staple loading & clearing mechanism for fast & convenient use. Handle safety locking system prevents accidental operation. Fires half round staples for use on low voltage cable max 6.4mm diameter (interchangeable with Arrow T25).

Item No.	Diagram	Quantity
T6227	 7.5mm	3



### Cable Tacker - Telecom Cable


Heavy duty, tough cast aluminium body for strength & durability. Bi-material ergonomic handle for comfort & reduced fatigue. Unique staple loading & clearing mechanism for fast & convenient use. Handle safety locking system prevents accidental operation. Fires half round staples for use on telecom data cable max 4.8mm diameter.

Item No.	Diagram	Quantity
T6228	 4.8mm	3



### Telecom Staples - Half Round

High quality telecom cable staples, galvanised for corrosion protection. White coated tops for discreet fixing - to suit C.K T6228 Telecom cable tacker.

Item No.	Diagram	Quantity
495024	 4.8 x 10mm	10



### Cable Staples - Half round

High quality steel cable staples, galvanised for corrosion protection. Suits C.K cable tacker T6227 and compatible versions. 1000 staples.

Item No.	Diagram	Quantity
495022	 7.5 x 14mm	10
495021	 7.5 x 10mm	10

Electrical Installation



**Conduit Bush Wrench**

Innovative head design allows for all sizes of conduit bushes to be tightened/untightened even with cabling in place. Zinc phosphate coated, tough alloy steel for increased strength and durability. Soft grip, tri-lobe handle for exceptional comfort and control.

Item No.		
T4755	190mm (7 1/2")	6
T4755CBOX		



**Punch Down Tool**

For the fast and secure seating of data wires into terminals. Suitable for a wide range of terminal block types. One step action for automatic seating & trimming of excess wires. Handle includes wire extractor hook & flat head spudger.

Item No.		
495033	180mm (7")	3



**MC4 Solar Spanners**

Performance: The perfect solution to tighten and disassemble MC4 connectors used in the installation of photovoltaic equipment. Easy to use: Simply insert the spanner pins into the securing clips of the two connectors, release and gently pull apart to separate the two connectors. Durable: Manufactured from reinforced plastic which is durable, light and easy to carry. Universal: Suitable for all common connectors used to extend photovoltaic lines of solar panels, photovoltaic connectors, photovoltaic solar cables, solar generators and solar line connectors.

Item Number		
T4348	1000V	340
T4348 2	1500V	400

Mainstesters



**Mainstester - 120-250V AC**

Insulated for protection. Neon light for high visibility. Pocket clip.

Item No.			
440005	65mm	3mm	3



**VDE Mainstester - Pocket Clip**

VDE approved mainstester for assured safety. Neon light for high visibility. Pocket clip.

DIN 57680 -6 VDE 680 -6 - Cert no 40011575

Item No.				
440007	65mm	3mm	0.5mm	12



**VDE Mainstester - 125-250V AC**

Premium quality VDE approved for assured safety. Neon light for high visibility. Finger slip guard for added safety. Integrated pocket clip.

DIN 57680 -6 VDE 680 -6 Cert No 109826

Item No.			
440008	150mm	3mm	12
440009	190mm	3.5mm	12



**Long Mainstester - 120-250V AC**

VDE approved mainstester for assured safety. Neon light for high visibility. Pocket clip.

DIN 57680 -6 VDE 680 -6 Cert No 40016094

Item No.				
440012	100mm	4mm	0.6mm	12



**Heavy Duty Mainstester - 120-250V AC**

Extended shaft for long reach applications. Insulated for protection. Neon light for high visibility.

Item No.				
440013	120mm	4mm	0.6mm	12

## Voltage Detectors



### Voltage Detector - Visual

Suitable for non-contact AC voltage tests, e.g. earthing/ground connection checks, proper connection checks, broken wire detection, etc. Bright red LED illumination on detection of AC voltage. Double insulated to ensure safe use near live circuitry. Ergonomic, dual component body construction with a handy pocket clip.

EMC BS EN 61326-1-2-3, BS EN 61000-3

**Item No.**



T2271A

6



### Voltage Detector - Visual & Audible

Suitable for non-contact AC voltage tests, e.g. earthing/ground connection checks, proper connection checks, broken wire detection, etc. Bright red LED illumination & audible alarm on detection of AC voltage. Double insulated to ensure safe use near live circuitry. Ergonomic, dual component body construction with a handy pocket clip.

EMC BS EN 61326-1-2-3, BS EN 61000-4


**Item No.**



T2272A

6

## Switch Keys



### Universal Switch Key - 9 in 1

Cross key design with swivel ends offering 9 different key types. Heavy duty cast alloy construction for strength. PH2 screwdriver bit included.

**Item No.**



T4451-2

50



### Universal Switch & Cabinet Key

Multi-purpose tool for locking systems of electric, gas and water enclosures and other technical installations in buildings such as air conditioning and ventilation systems, shut-off valves, mains consoles etc. Heavy duty cast alloy construction for strength. 6mm bit driver adaptor & double ended screwdriver bit included (PH2 / Slotted 1.0 x 7 mm). Fittings: 1/4" hexagon for bits, Square 5mm, 6 - 7mm, 7 - 8mm, Three-Square 9mm, Tapered-Square 4 - 10mm.

**Item No.**



495015

1



### Cabinet Wrench Key - 8 in 1

Greater ergonomics, comfort and accessibility for users, without sacrificing versatility. Suitable for electrical, gas and water cabinet closures, it offers users the versatility of two 360° rotating key heads, incorporating double functionality. The double-joint design improves ergonomics over standard keys, allowing users to transform the key into a T handle for high-torque applications. With a compact profile manufactured from durable glass reinforced polymer, users will welcome the additional comfort, when in use or when carried in a pocket.

**Item No.**



T4456

75



### Cabinet Cross Key - 12 in 1

Features key heads with double function for convenience and versatility. Durable die-cast Zinc construction for industrial applications. Includes screwdriver bit adaptor and double ended bit. Suitable for all current electrical, gas and water cabinet closures.

**Item No.**



T4455

100

Hexagon Keys



Insulated T Handle Hex Keys

VDE approved - individually tested to 10,000V for safe working up to 1,000V. Premium quality S2 steel blade, tempered and hardened for exceptional strength & durability. Dual component, ergonomic handle for comfort and control. IEC60900 VDE 0682-201

Item No.		
T4422 03	3mm	6
T4422 035	3.5mm	6
T4422 04	4mm	6




Insulated T Handle Hex Key Set

VDE approved - individually tested to 10,000V for safe working up to 1,000V. Premium quality S2 steel blade, tempered and hardened for exceptional strength & durability. Dual component, ergonomic handle for comfort and control. IEC60900 VDE 0682-201

Item No.
T4422 SET

Re-Threading Tools



Re-Threading Tools

Tough, impact resistant handle. High speed steel tap for a clean cut and long life. Precision ground threads for accurate threading. 50mm long blade for improved access.

Item No.				
495028	M3.5	0.6mm	113mm	12
495029	M4	0.7mm	113mm	12

Soldering



Soldering Irons

High quality, heavy duty construction for professional use. Long life tips suitable for use with lead free solder. Individually tested to 10,000V for safe live working up to 1,000V. EMC, LDV, ROHS, WEEE

Item No.		
495009	Soldering iron 25W - UK 3 pin plug	1
495010	Soldering iron 40W - UK 3 pin plug	1
495011	Soldering iron 25W - Euro 2 pin plug	1
495012	Soldering iron 40W - Euro 2 pin plug	1
495013	Spare tip set for 25W	1
495014	Spare tip set for 40W	1



Soldering Wire

Lead free special alloy. 2.5% flux incorporated. Solder wire: ISO-core Sn99CU1. EN 61190/DIN29545-1 DIN29453

Item No.			
T6052 51	500g	1mm	20
T6052 52	500g	2mm	20







# Toolkits

**Toolkits**

**68**

**Tool Storage**

**71**

## Toolkits



### Professional Tool Kit

A complete electrician's tool kit featuring Combicutter3 side cutters and Dextro screwdrivers, all contained in the award winning C.K technicians toolcase. CONTENTS: Technician's tool case; Redline VDE Combicutter3 160mm; Combination pliers 185mm; Snipe nose pliers 175mm; 7 x Dextro VDE screwdrivers, slotted, sizes: 2.5 x 75 & 4 x 100mm; Pozidriv, sizes: PZ1 x 80 & PZ2 x 100mm; Phillips, sizes: PH1 x 80 & PH2 x 100mm; Modulo, size: 2; VDE mainstester; Tape 5m/16ft; Junior hacksaw; Electrician's knife; Automatic wire stripper PRO; Pocket level; Re-threading tool M3.5; Claw hammer.

#### Item No.

T5982



### Electrician's Tool Kit - European

A complete electrician's tool kit featuring Dextro screwdrivers, all contained in the award winning C.K technicians toolcase. CONTENTS: Technician's toolcase. Redline VDE side cutters 165mm. Combination pliers 175mm. Snipe nose pliers 175mm. 7 x Dextro VDE screwdrivers, slotted, sizes: 2.5 x 75 & 4 x 100mm; Pozidriv, sizes: PZ1 x 80 & PZ2 x 100mm; Phillips, sizes: PH1 x 80 & PH2 x 100mm; Modulo, sizes: 1 & VDE mainstester. ST Tape 8m. Mini hacksaw. Electrician's knife. Automatic wire strippers. Cable knife. Plasterboard saw.

#### Item No.

T1630 FKIT



1



### Professional Plus Tool Kit

Our most comprehensive kit yet, the new C.K Professional Plus Tool Kit is built for greater productivity and efficiency. Includes innovations such as the Combicutter3, the ArmourSlice SWA Cable Stripper and DextroVDE slim glo screwdrivers. All contained within the C.K Magma Pro Tool Case Plus, the ultimate bag to organise and protect your tools. CONTENTS: Technicians Pro Tool Case, RedLine VDE Combination Pliers 185mm, RedLine VDE Snipe Nose Pliers 175mm, RedLine VDE CombiCutter3 160mm, DextroVDE GLO Slim Screwdriver Set/5 PZ/SL, Conduit Bush Wrench, ArmourSlice SWA Cable Stripper, VDE Precision Screwdriver Set/7, VDE Cable Knife, Japanese Prybar, Electricians Scissors, Softech Tape 5m/16ft, Automatic Wire Stripper PRO, Coax Cable Stripper, Pocket Spirit Level 210mm, LED Pocket Inspection Light, Re-threading tool M3.5x0.6.

#### Item No.

T5983



### EV Charging Point Tool Kit

The COMPLETE toolkit for EV Charger Installation. Built for greater efficiency and productivity. Configured using industry expertise and best practices. Technicians Wheeled Case for versatile storage and mobility. CONTENTS: Technicians Wheeled Case, SpiraFLEX Draw Tape 10m, ArmourSlice SWA Cable Stripper, Conduit Bush Wrench, Voltage Detector, Waterpump Pliers 250mm, RedLine VDE Side Cutter 160mm, RedLine VDE Electricians Plier 180mm, RedLine VDE Heavy Duty Cable Cutter 210mm, AT Tape Measure 5m / 16ft, Pocket Level, Junior Hacksaw, Hacksaw Blades, VDE Cable Sheath Stripping Knife, Folding Utility Knife, Sealant Gun, Automatic Wire Stripper Pro, Claw Hammer, VDE Torque Screwdriver, Insulated T Handle Hex Key Set, VDE Interchangeable Slim Blade Set, Socket & Spanner Set, 6 - 25mm Ratchet Crimping Pliers, 0.25 - 6.0mm Ratchet Crimping Pliers, 1.5 - 10mm Ratchet Crimping Pliers, Compact Crimper.

#### Item No.

T5984





### EV Charging Point PTA Kit

A complete set of power tool accessories to support the EV tool kit. From drilling through walls to fixing clips, the PTA Kit covers all the bases for a standard EV installation. CONTENTS: T3121 C.K SDS Concrete Drill Bit Set of 7, AV08014 Mansonry 1m SDS Drill Bit Set - 3 piece set, T3063 C.K Multi Purpose Drill Set Of 5, T2942P C.K Flat Wood Bit Set/6, T3202 020 C.K Sheet Steel Hole Saw 20mm, T3202 025 C.K Sheet Steel Hole Saw 25mm, T3202 032 C.K Sheet Steel Hole Saw 32mm, T4510 C.K Blue Steel Impact Screwdriver Bit - PZ Set of 10.

**Item No.**

T5985



### Solar Installer Tool Kit

A carefully crafted kit including all the tools needed for the installation and maintenance of Solar PV equipment in domestic and commercial applications. Suitable for a variety of solar systems and designed for greater efficiency and confidence on the job. CONTENTS: C.K Magma Rucksack Plus, Ratchet Crimping Plier Solar PV, Cable Cutter 210mm, Jokari SE-Strip Wire Stripper 2.5mm-6mm, Coloured SureDrive 3/8in Socket & Spanner Set, MC4 Solar Connection Spanner 1000V, MC4 Solar Connection Spanner 1500V, Dextro VDE Screwdriver SLP 4X100, Dextro VDE Screwdriver PZ2x100, Magnetic Nut Drivers Set/7pc, XT Tape Measure 7.5M 25FT, Hexagon Key Metric Folding Set/8pc.

**Item Number**

T5988



4



### Electricians Apprentice Kit

The ultimate apprentice kit including all the tools needed for installation, commissioning, testing and maintenance across domestic and commercial electrical work. Configured using the latest Electrical Training Phase Two syllabus, each tool has been hand-picked to get the job done with confidence and efficiency. CONTENTS: MA2635 C.K Magma Rucksack Plus, 431003 RedLine VDE Combination Pliers, 431008 RedLine VDE CombiCutter3, 431014 RedLine VDE Snipe Nose Pliers, T3943 Automatic Wire Stripper Pro, T3653 250 Push Button Waterpump Pliers, T4366 200 Adjustable Wrench 200mm, T0905 C.K Hacksaw, T0834 C.K Junior Hacksaw, T0832 C.K Sabretooth Plasterboard Saw, T4755 Conduit Bush Wrench, 484001 Electricians Knife, T49193D Dextro VDE Screwdriver Set, T3482 Pocket Level 210mm/8 1/4in, T3494 16 Level-Box Section, T3442 25 ST Tape 7.5/25ft, T0083 6 C.K Engineers File Round, T4443M Ball-ended Long-arm Hexagon Set, T1280 Cable Stripper, T2272A Non Contact Voltage Detector, T4229 16 Steel Claw Hammer 16oz.

**Item No.**

T5987



### Complete Tool Kit

Professional quality tools for everyday tasks - A carefully crafted tool kit with a selection of tools to tackle multiple tasks for building and plumbing. Spacious and robust tool tote to expand the kit with other tools from the C.K range. CONTENTS: MA2636 C.K Magma 18inch Open Tool Tote, T0954 C.K Folding Utility Knife, T3442 16 ST Tape 5m/16ft, T3621B 7 Classic Combination Pliers, T3623B 6 Classic Side Cutter 160mm, T4366 200 Adjustable Wrench 200mm, T4727 Triton Xls Screwdrivers, T0834 C.K Junior Hacksaw, T3494 16 Level-Box Section, F3659A 240 Waterpump Plier 240mm, T4229 16 Steel Claw Hammer 16oz.

**Item No.**

T5971



## Contractor Tool Kit

A flexible selection of tools for general maintenance and repair contained within the C.K Magma technician's tote. CONTENTS: C.K Magma Technician's Tote, VDE Side Cutter 160mm, VDE Combination Pliers 185mm, VDE Snipe Nose Pliers 175mm, VDE Screwdrivers, PZD 1 & 2, VDE Screwdrivers, Slotted 2.5 x 75; 4.0 x 100mm, Waterpump Pliers 250mm, Tape 5 Meter / 16 ft, Mini Hacksaw, Pocket Spirit Level, Universal Cable Stripper.

### Item No.

T5981



## Core Tool Kit

Professional Quality Tools for Everyday Tasks - A carefully crafted tool kit with a basic selection of tools to tackle common tasks either around the home or on site. Can be used as part of a larger tool kit and as a compact grab and go bag for smaller jobs. CONTENTS: MA2718 C.K Magma Tool Roll, T0954 C.K Folding Utility Knife, T3442 16 ST Tape 5m/16ft, T3621B 7 Classic Combination Pliers, T3623B 6 Classic Side Cutter 160mm, T4522 Bit Clip Phillips/PZD/SDV, T4521 Bit Clip Slotted 8 Piece, T4516 Triton Xls Screwdriver Bit Holder, T0834 C.K Junior Hacksaw.

### Item No.

T5970



## Essential Tool Kit

Entry level tool kit containing the bare essentials. CONTENTS: C.K Magma Essential Tool Pouch, VDE CombiCutter 3 160mm, VDE Combination Pliers 185mm, VDE Screwdriver, PZ2, VDE Screwdrivers, Slotted 2.5 x 75 & 4.0 x 100mm.

### Item No.

T5980



## VDE Pliers & Screwdrivers Kit - PZ

Collection of VDE pliers, cutters & screwdrivers stored within a zipper wallet. CONTENTS: Zip Case, VDE Side Cutter 160mm, VDE Combination Pliers 185mm, VDE Snipe Nose Pliers 175mm, VDE Screwdrivers, PZD 1 & 2, VDE Screwdrivers, Slotted 2.5 x 75; 4.0 x 100 & 5.5 x 125mm, Voltage detector, visual indicator 70-1000V, CAT IV.

BS EN 60900 , VDE 682/201, ASTM-F 1505

### Item No.

T5953



1



## VDE Pliers & Screwdrivers Kit - PH

Collection of VDE pliers, cutters & screwdrivers stored within a zipper wallet. CONTENTS: Zip Case, VDE Side Cutter 160mm, VDE Combination Pliers 185mm, VDE Snipe Nose Pliers 175mm, VDE Screwdrivers, PH 1 & 2, VDE Screwdrivers, Slotted 2.5 x 75; 4.0 x 100 & 5.5 x 125mm, Voltage detector, visual indicator 70-1000V, CAT IV.

BS EN 60900 , VDE 682/201, ASTM-F 1505

### Item No.

T5954



1



## Technicians Tool Kit

Collection of essential tools for the mobile technician. CONTENTS: Zip Case, Precision Wire Stripper 0.25 - 0.80mm, Inspection mirror, telescopic 38mm, ESD Side Cutter 125mm, ESD Snipe Nose Pliers 130mm, 7 ESD Electronic Screwdrivers: Phillips 0x60 and 1x80mm. Slotted 2.5x75 ; 3.0x100 ; 3.0x150 ; 4.0x100 and 4.0x150mm, Precision Tweezers, ESD Bit Driver, Bit set with the following CONTENTS: magnetic bit holder; 8 Bits Slotted sizes 3, 4, 4.5, 5, 5.5, 6, 7, 8; 4 Bits PZD sizes 0, 1, 2, 3; 4 Bits Phillips sizes 0, 1, 2, 3; 8 Bits TX sizes 8, 10, 15, 20, 25, 27, 30, 40; 8 Bits Hexagon sizes 1.5, 2, 2.5, 3, 4, 5, 5.5, 6.

### Item No.

T5956



1



**Electricians Service Case**

Professional ABS tool case with aluminium frame. 2 high quality press button locks, lockable, additional 3-digit combination lock. Bottom tray 59mm high, with variable dividers. Bottom tray lid, flush fitting, 14 compartments. Tool board double sided, 32 tool compartments and elastic band for 12 parts, detachable. 1 fixed Din A4 document compartment with additional compartments. CONTENTS: T20050 Jokari Auto Stripper, T3773EF Classic Side Cutter, F431013 RedLine VDE Snipe Nose Pliers, T3650 250 Waterpump Plier 250mm, F431015 RedLine VDE Bent Snipe Nose Pliers, F431002 RedLine VDE Combi Pliers 180mm, F431004 RedLine VDE Combicutter1 160mm, T4406 Hexagon Key, 440007 Mainstester VDE 120-250V, T49144-030 Dextro VDE Screwdriver, T49144-040 Dextro VDE Screwdriver, T49144-055 Dextro VDE Screwdriver, T49144-065 Dextro VDE Screwdriver, T49143-1 Dextro VDE Screwdriver, T49143-2 Dextro VDE Screwdriver, T49142-1 Dextro VDE Screwdriver, AV06040 Multi-Purpose Snips, T49142-2 Dextro VDE Screwdriver, F84001 Electricians Knife, T10280 Jokari Cable Knife, T0836A C.K Mini Hacksaw, T1643 Rigid Service Case, 356001 French Pattern Electricians Hammer, T4455 Cabinet Cross-Key 12 in 1, T3442M 8 ST Tape 8M, T4880X 256 Xonic Screwdriver.

**Item No.**

T1641

**Tool Storage**



**Rigid Service Case**

Tough ABS plastic service case with aluminium frame for the safe transportation of tools and equipment. CONTENTS: over 40 pockets and straps, 14 adjustable compartments and a fixed document compartment making this case ideal for a wide range of service engineer trades.

**Item No.**

T1643



**Tool Wallet**

Tough fabric zip up carry case with elasticated internal loops. 340mm x 245mm with expansion of up to 65mm to accommodate tools.

**Item No.**

316001



1




**Electronic Service Case**

Professional ABS tool case with aluminium frame. 2 high quality press button locks, lockable, additional 3-digit combination lock. Bottom tray 59mm high, with variable dividers. Bottom tray lid, flush fitting, 14 compartments. Tool board double sided, 32 tool compartments and elastic band for 12 parts, detachable. 1 fixed Din A4 document compartment with additional compartments for CD. T20050 Jokari Auto Stripper, T3773EF Classic Side Cutter, T3777 Classic Snipe Nose Plier, T2328 Radio Tweezers Bent 61/4in, F431004 RedLine VDE Combicutter1 160mm, F431002 RedLine VDE Combi Pliers 180mm, F431014 RedLine VDE Snipe Nose Pliers, 440007 Mainstester VDE 120-250V, T5913 32 Inspection Mirror 32mm, T4334M 055 HD Classic Nut Spinner, T4334M 07 HD Classic Nut Spinner, T4334M 08 HD Classic Nut Spinner, T4334M 10 HD Classic Nut Spinner, T49144-030 Dextro VDE Screwdriver, T49144-040 Dextro VDE Screwdriver, T49144-055 Dextro VDE Screwdriver, T49144-065 Dextro VDE Screwdriver, T49143-0 Dextro VDE Screwdriver, T49143-1 Dextro VDE Screwdriver, T49142-0 Dextro VDE Screwdriver, T49142-2 Dextro VDE Screwdriver, 484001 Electricians Knife, AV06040 Multi-Purpose Snips, 492001 Electricians Scissors 140mm, T10280 Jokari Cable Knife, T1643 Rigid Service Case, T4455 Cabinet Cross-Key 12 in 1, 330013 Wire Stripper Adjustable, T4406 Hexagon Key, T4880XES256 Xonic ESD Screwdriver.

**Item No.**

T1642





# ESD & Precision

<b>SensoPlus ESD Pliers &amp; Cutters</b>	<b>76</b>
<b>Precision Pliers &amp; Cutters</b>	<b>80</b>
<b>Ecotronic ESD</b>	<b>84</b>
<b>ESD Wire Stripping Pliers</b>	<b>86</b>
<b>Carbofib ESD</b>	<b>87</b>
<b>Precision Tweezers</b>	<b>88</b>
<b>Precision ESD Tweezers</b>	<b>92</b>
<b>Triton ESD</b>	<b>94</b>
<b>Xonic ESD</b>	<b>96</b>
<b>Xonic Precision Screwdrivers</b>	<b>98</b>
<b>Precision Screwdrivers</b>	<b>100</b>
<b>Precision Ceramic Trimmers</b>	<b>100</b>
<b>Plastic Trimmers</b>	<b>101</b>
<b>Precision Wire Strippers</b>	<b>102</b>
<b>Other</b>	<b>103</b>



The C.K ESD and Precision range is designed for professionals who need hand tools for ultra fine work, where use of intricate components or tight access are issues, for example in the electronics and fine mechanics industries.

The international standard IEC 61340-5-1 for protection of electronic devices from electrostatic phenomena prohibits the use of non-ESD (electrostatic dissipative) products in Electrostatic Protected Areas (EPAs). C.K offers a wide variety of hand tools in compliance with these standards.



### What is ESD?

ESD stands for ElectroStatic Discharge.

ESD can cause unseen damage to electronic components during manufacture of electronic assemblies and equipment. If the damaged component fails immediately, the result can be a board that fails quality control tests and requires rework. This represents lost production and additional manufacturing costs.

Worse than this, a component may be partially damaged and weakened. It may suffer a change or drift in characteristics. It may remain within specification, but fail later when in use by a customer. It has been estimated that 90% of damages to devices may be incurred in this way.


In manual assembly most ESD arises from charged personnel, if they are not grounded.

One of the main principles used to protect ESD sensitive components from ESD damage is to only handle sensitive components in an ESD Protected Area (EPA) under protected and controlled conditions. An EPA is an area in which static electricity is kept below levels that could cause damage to electronic components handled within the area.



### Precision box joint

The box joint construction of our pliers and cutters is a specialised technique which physically slots one half of the plier through the other. Although more difficult to manufacture, the doubly supported pivot gives smooth and accurate action, longer product life, and removes the requirement for readjustment.



### Hot drop forged blanks

Hot drop forging gives maximum strength to our tools through optimising the grain structure.



### Spot welded double leaf springs

Spot welded springs mean that no replacements or adjustments are necessary. The action of each pair of pliers will be consistent and controlled with no maintenance costs.






### Cutting Edges

The geometry of the cutting blade affects both the cutting action and performance, and the lifetime of the product. The sharper the angle, the fewer cutting forces are generated. Reduced cutting forces not only lead to a smoother and easier feeling cut, but also limits potentially damaging pressure or 'cutting shock' to sensitive components. There is a trade-off however. The blade will wear more quickly and the cutting capacity will be lower.



#### Mini Bevel

- Standard cut.
- Highest cutting capacity.
- Robust and long lasting.



#### Full Flush

- Almost full flush cutting.
- Cutting shock slightly reduced.



#### Extra Full Flush

- Perfectly flush cutting.
- Suitable for non-shock cutting.

### Key

	Mini Bevel cut
	Full Flush cut
	Extra Full Flush cut
	Smooth jaws
	Serrated jaws
<b>CF</b>	Carbon-fibre tips and SA-steel
<b>SA</b>	Stainless steel (No. 4435 / AISI 316)
<b>S</b>	Stainless steel
<b>C</b>	Carbon steel, hardened
<b>SA ESD</b>	Stainless steel, ESD-safe black, epoxy coating
	Piano Ømm AWG
	Hard Ømm AWG
	Medium/Hard Ømm AWG
	Soft Ømm AWG



#### Mirror polished surface

The micro-fine steel surface provides an attractive finish with no risk of flaking chrome plating which could damage circuits and components.




#### Careful choice of raw materials

We carefully select different high alloy carbon and chrome vanadium steels to match the varying demands of each product.

## Pliers & cutters

1. Special alloy steel, drop forged, hardened and tempered for exceptional strength and durability.
2. Precision box joint construction for permanent, adjustment free jaw alignment.
3. Induction hardened jaws for outstanding long term performance.
4. Mirror polished surface eliminates the risk of damage from flaking chrome.
5. Spot welded double leaf springs for consistent, repetitive action.
6. Ergonomically designed dual component handles for increased comfort and control.
7. Fully ESD compliant for safe use on sensitive electronic components.



### SensoPlus ESD Pliers & Cutters




#### ESD Side Cutter

Relieved jaws.

IEC 61340. 5.1 & 5.2


Item No.	⊘	⊘	●	↔	i	📦
T3766DF 110	1.5 / 15	0.8 / 20	-	120mm	🚫	1
T3766DEF110	1.5 / 15	0.6 / 22	-	120mm	✅	1
T3766DEF 120	1.0 / 18	0.6 / 22	-	125mm	✅	1



#### ESD Side Cutter

IEC 61340. 5.1 & 5.2

Item No.	⊘	⊘	●	↔	i	📦
T3773D 115	1.5 / 15	1.0 / 18	0.4 / 26	125mm	🚫	1
T3773DF 115	1.5 / 15	1.0 / 18	-	125mm	🚫	1
T3773DEF115	1.5 / 15	0.8 / 20	-	125mm	✅	1



#### ESD Tungsten Carbide Side Cutter

Tungsten carbide edges, relieved jaws.

IEC 61340. 5.1 & 5.2


Item No.	⊘	●	○	↔	i	📦
T3787DF 115	1.8 / 13	1.0 / 18	0.4 / 22	125mm	🚫	1



**ESD Side Cutter**

IEC 61340. 5.1 & 5.2


Item No.						
T3780DF 110	1.5 / 15	0.8 / 20	-	120mm		1
T3780DEF 110	1.0 / 18	0.6 / 22	-	120mm		1



**ESD Side Cutter**

Tungsten carbide edges.  
IEC 61340. 5.1 & 5.2

Item No.					<b>WC</b>	
T3779D 115	2.0 / 12	1.0 / 18	0.6 / 22	120mm		1



**ESD Side Cutter**

IEC 61340. 5.1 & 5.2


Item No.						
T3775D	2.0 / 12	1.5 / 15	0.7 / 21	140mm		1



**ESD Bevel Side Cutter**

IEC 61340. 5.1 & 5.2


Item No.						
T3781D 115	1.5 / 15	1.0 / 18	0. / 28	125mm		1
T3781DF 115	1.5 / 15	1.0 / 18	-	125mm		1
T3781DEF 115	1.5 / 15	0.8 / 20	-	125mm		1



**ESD Bevel Wire Catch Side Cutter**

Wire catch facility to prevent waste material causing damage to sensitive equipment.  
IEC 61340. 5.1 & 5.2


Item No.						
T3782D 115	1.5 / 15	1.0 / 18	0.4 / 26	125mm		1
T3782DEF 115	1.5 / 15	0.8 / 20	-	125mm		1



**ESD Oval Head Cutter**

Tapered head.  
IEC 61340. 5.1 & 5.2

Item No.						
T3880DF 110	1.5 / 15	1.0 / 18	0.4 / 26	120mm		1
T3880DEF 110	1.0 / 18	0.6 / 22	-	120mm		1








**ESD Oblique Cutters**

Tungsten carbide edges.  
IEC 61340. 5.1 & 5.2


Item No.					WC	
T3760DF 110	2.0 / 12	1.0 / 18	0.6 / 22	120mm		1



**ESD Oblique Cutters**

Straight head.  
IEC 61340. 5.1 & 5.2

Item No.						
T3799DF 110	1.2 / 16	1.0 / 18	0.4 / 26	120mm		1
T3799DEF 110	1.0 / 18	0.8 / 20	-	120mm		1



**ESD Oblique Cutters**

IEC 61340. 5.1 & 5.2

Item No.						
T3778DF	1.6 / 14	1.0 / 18	0.3 / 28	125mm		1



**ESD Top Cutters**

IEC 61340. 5.1 & 5.2


Item No.						
T3776DEF 115	2.0 / 12	1.6 / 14	-	120mm		1



**ESD Oblique Tip Cutters**

Very slim, pointed jaws.  
IEC 61340. 5.1 & 5.2


Item No.						
T3871DF 120	0.8 / 20	0.6 / 22	-	130mm		1



**ESD Oblique Cutters**

IEC 61340. 5.1 & 5.2

Item No.						
T3786DF 120	0.8 / 20	0.6 / 22	-	130mm		1





**ESD Top Cutters**

Laid-on joint.

IEC 61340. 5.1 & 5.2

Item No.						
T3784DF	0.8 / 20	0.6 / 22	-	130mm		1



**ESD Bent Snipe Nose Pliers**

Bent nose.

IEC 61340. 5.1 & 5.2

Item No.			
T3767D 120	130mm		1



**ESD Snipe Nose Pliers**

IEC 61340. 5.1 & 5.2

Item No.			
T3772D 120	130mm		1
T3772 1D120	130mm		1



**ESD Bent Snipe Nose Pliers**

Bent nose.

IEC 61340. 5.1 & 5.2

Item No.			
T3769D 150	155mm		1



**ESD Snipe Nose Pliers**

IEC 61340. 5.1 & 5.2

Item No.			
T3777D 150	155mm		1



**ESD Flat Nosed Pliers**

IEC 61340. 5.1 & 5.2

Item No.			
T3770D 120	130mm		1
T3770 1D120	130mm		1



## ESD Needle Nose Pliers

IEC 61340. 5.1 & 5.2

Item No.	Length	Info	Icon	Quantity
T3783D	155mm			1

2 mm / .079"	11 mm / .433"	1.2 mm / .047"	7.5 mm / .295"	155 mm / 6.14"
--------------	---------------	----------------	----------------	----------------



## ESD Round Nosed Pliers

IEC 61340. 5.1 & 5.2

Item No.	Length	Info	Icon	Quantity
T3771D 120	130mm			1

2 mm / .079"	10 mm / .394"	1 mm / .039"	6 mm / .236"	130 mm / 5.14"
--------------	---------------	--------------	--------------	----------------



## ESD Pliers Set - 6 Piece

Set of 6 electronic pliers in zip case. CONTENTS: Side cutter T3773D with mini-bevel, Side cutter T3880DF with full flush cut, Side cutter T3766DF with full flush cut, Oblique cutter T3786DF with full flush cut, Snipe nose plier T3772D with smooth jaws, Flat nose plier T3770D with smooth jaws.

IEC 61340. 5.1 & 5.2

Item No.	Info	Icon	Quantity
T3703D	Set of 6		1

9 mm / .354"	6 mm / .236"	120 mm / 4.3/4"
--------------	--------------	-----------------



## ESD Tool Kit

Set of 14 electronic pliers and Xonic ESD screwdrivers in a hard case. CONTENTS: T3772D 120 Snipe nose pliers, T3773D 115 Side cutter, T2334 Positioning tweezer, T2343 Precision tweezer, T4880XESD Slotted screwdrivers: 1.5 x 60, 1.8 x 60, 2.5 x 60, 2.5 x 75, 3 x 100, 4 x 100, T4882XESD Phillips screwdrivers: PH000 x 60, PH00 x 60, PH0 x 60, PH1 x 80. IEC 61340. 5.1 & 5.2

Item No.	Info	Icon	Quantity
T3707DX	Set of 14		1

## Precision Pliers & Cutters



## Precision Side Cutters

Item No.	Icon 1	Icon 2	Icon 3	Info	Icon	Quantity
T3773	1.5 / 15	1.0 / 18	0.4 / 26			1
T3773F	1.5 / 15	1.0 / 18	-			1
T3773EF	1.5 / 15	0.8 / 20	-			1

11 mm / .433"	7.5 mm / .295"	115 mm / 4.1/2"
---------------	----------------	-----------------



## Precision Side Cutters

Tungsten carbide edges.

Item No.	Icon 1	Icon 2	Icon 3	WC	Icon	Quantity
T3779	2.0 / 12	1.0 / 18	0.6 / 22			1

11 mm / .433"	7.5 mm / .295"	125 mm / 5"
---------------	----------------	-------------




## Pliers & cutters



### Precision Side Cutters


Item No.					
T3775	2.0 / 12	1.5 / 15	0.7 / 21		1
T3775EF	2.0 / 12	1.3 / 18	-		1



### Precision Side Cutters


Laid-on joint.

Item No.					
T3774	1.5 / 15	1.0 / 18	0.4 / 26		1



### Precision Full Flush Side Cutters

Item No.					
T3780F	1.5 / 15	0.8 / 20	-		1
T3780EF	1.5 / 15	0.6 / 22	-		1



1. Special alloy steel, drop forged, hardened and tempered for exceptional strength and durability.
2. Precision box joint construction for permanent, adjustment free jaw alignment.
3. Induction hardened jaws for outstanding long term performance.
4. Mirror polished surface eliminates the risk of damage from flaking chrome.
5. Spot welded double leaf springs for consistent, repetitive action.
6. PVC handles for comfort and grip.





**Precision Bevel Side Cutters**

Item No.					
T3781	1.5 / 15	1.0 / 18	0.3 / 28		1
	11 mm / .433"		7.5 mm / .295"		115 mm / 4.1/2"
	13 mm / .512"				



**Precision Oval Head Cutters**

Item No.					
T3880F	1.5 / 15	0.8 / 20	-		1
	9 mm / .354"		6 mm / .236"		110 mm / 4.1/4"
	9 mm / .354"				



**Precision Oblique Cutters**

Wide head, long blades.

Item No.					
T3778F	1.6 / 14	1.2 / 16	0.5 / 24		1
	11 mm / .433"	18 mm / .709"		7.5 mm / .295"	
	9 mm / .354"				120 mm / 4.3/4"



**Precision Oblique Cutters**

Straight head.

Item No.					
T3799F	1.2 / 16	1.0 / 18	0.4 / 26		1
	10 mm / .394"	12 mm / .473"		6.5 mm / .256"	
	10 mm / .394"				110 mm / 4.1/4"



**Precision Oblique Tip Cutters**

Item No.					
T3786F 4	0.8 / 20	0.6 / 22	-		1
	11 mm / .433"	5 mm / .197"		6.5 mm / .256"	
	20 mm / .788"				120 mm / 4.3/4"



**Precision Top Cutters**

Wide head, long blades.

Item No.					
T3776F	1.6 / 14	1.2 / 16	0.5 / 24		1
	11 mm / .433"	15 mm / .590"		7.5 mm / .295"	
	6 mm / .236"				120 mm / 4.1/2"
T3776EF 5	2.0 / 12	1.6 / 14	-		1
	14 mm / .550"	23 mm / .900"		9 mm / .354"	
	9 mm / .354"				130 mm / 5.1/4"



**Precision Snipe Nose Pliers**

Item No.	Length	Tip	Quantity
T3772	120mm		1
T3772.1	120mm		1

 2.4 mm / .079" tip width, 10 mm / .394" height, 23 mm / .905" length	 1 mm / .039" tip width, 6 mm / .236" height, 130 mm / 5.14" length
--------------------------------------------------------------------------	------------------------------------------------------------------------



**Precision Snipe Nose Pliers**

Long nose.

Item No.	Length	Tip	Quantity
T3777	145mm		1

 2.4 mm / .079" tip width, 12.5 mm / .492" height, 40 mm / 1.575" length	 1.2 mm / .047" tip width, 7.5 mm / .295" height, 145 mm / 5.314" length
-----------------------------------------------------------------------------	-----------------------------------------------------------------------------



**Precision Bent Snipe Nose Pliers**

Bent nose.

Item No.	Length	Tip	Quantity
T3767	130mm		1

 2 mm / .079" tip width, 10 mm / .394" height, 20 mm / .788" length	 10 mm / .394" tip width, 6.5 mm / .250" height, 130 mm / 5.314" length, a=1 mm / .039"
------------------------------------------------------------------------	--------------------------------------------------------------------------------------------



**Precision Bent Snipe Nose Pliers**

Bent nose.

Item No.	Length	Tip	Quantity
T3769	145mm		1

 2.4 mm / .095" tip width, 12.5 mm / .492" height, 33 mm / 1.130" length	 20 mm / .788" tip width, 7.5 mm / .295" height, 33 mm / 1.130" length, a=1.2 mm / .047"	 145 mm / 5.314" length
-----------------------------------------------------------------------------	---------------------------------------------------------------------------------------------	----------------------------




**Precision Flat Nose Pliers**

Item No.	Length	Tip	Quantity
T3770	120mm		1

 1.5 mm / .059" tip width, 10 mm / .394" height, 22 mm / .866" length	 3.5 mm / .138" tip width, 6.5 mm / .250" height, 120 mm / 4.314" length
--------------------------------------------------------------------------	-----------------------------------------------------------------------------



**Precision Flat Nose Pliers**

Item No.	Length	Tip	Quantity
T3789	145mm		1

 1.5 mm / .059" tip width, 12 mm / .472" height, 40 mm / 1.575" length	 4.5 mm / .177" tip width, 7.5 mm / .295" height, 145 mm / 5.314" length
---------------------------------------------------------------------------	-----------------------------------------------------------------------------





**Precision Round Nose Pliers**

Item No.	Length	Info	Quantity
T3771	120mm		1

--	--



**Precision Pliers Set - 6 Piece**

Set of 6 electronic pliers in zip case. CONTENTS: Side cutter T3773 with mini bevel, Side cutter T3780F with full flush cut, Oblique cutter T3799F with full flush cut, Snipe nose plier T3772 with smooth jaws, Snipe nose plier T3767 with smooth jaws, Flat nose plier T3770 with smooth jaws.

Item No.	Info
T3703	Set of 6
T3703DL	Zip wallet

**Ecotronic ESD**



**Precision Needle Nose Pliers**

Item No.	Length	Info	Quantity
T3783	145mm		1

--	--



**Ecotronic Micro Side Cutters**

Micro, tapered cutting head. IEC 61340. 5.1 & 5.2

Item No.	Material	Info	Quantity
T3883	1.3 / 16		6

--	--	--



**Precision Wire Stripping Pliers**

Laid-on joint.

Item No.	Capacity	Info	Quantity
T3796 5	0.1 - 0.8mm		1

--	--



**Ecotronic Reverse Side Cutters**

Reverse action cutting blades. Cutting DIP pins on integrated circuits. IEC 61340. 5.1 & 5.2

Item No.	Material	Info	Quantity
T3884	1.3 / 16		6

--	--	--

## Dissipative pliers & cutters

1. Fully ESD compliant for safe use on sensitive electronic components.
2. Strong and secure riveted joint.
3. Black oxidised finish to protect against corrosion.
4. Ergonomic dual component handles for increased comfort and control.



### Ecotronic Slim Side Cutters

Slim, tapered cutting head.

IEC 61340. 5.1 & 5.2

Item No.			
T3885	1.3 / 16		6

18 mm / .709" 10 mm / .394" 9 mm / .354"	21° 5 mm / .197"	139 mm / 5.472"



### Ecotronic Relieved Side Cutters

Slim, tapered and relieved head.

IEC 61340. 5.1 & 5.2

Item No.			
T3886	1.3 / 16		6

21 mm / .827" 11 mm / .433" 10 mm / .394"	21° 5 mm / .197"	139 mm / 5.472"



### Ecotronic Side Cutters

IEC 61340. 5.1 & 5.2

Item No.			
T3887	1.6 / 14		6

21 mm / .827" 12 mm / .472" 10 mm / .394"	21° 6 mm / .236"	136 mm / 5.354"





**Ecotronic Side Cutters**

Tapered and relieved head.  
IEC 61340. 5.1 & 5.2

Item No.			
T3888	1.6 / 14		6



**Ecotronic Flat Nose Pliers**

IEC 61340. 5.1 & 5.2

Item No.			
T3891			6



**Ecotronic Long Snipe Nose Pliers**

IEC 61340. 5.1 & 5.2

Item No.			
T3889			6



**Ecotronic Bent Snipe Nose Pliers**

Bent tips.  
IEC 61340. 5.1 & 5.2

Item No.			
T3892			6



**Ecotronic Short Snipe Nose Pliers**

IEC 61340. 5.1 & 5.2

Item No.			
T3890			6

**ESD Wire Stripping Pliers**



**ESD Wire Stripping Pliers**

Six pre-set blade pairs: 0.2, 0.3, 0.4, 0.5, 0.6, 0.8mm.  
IEC 61340. 5.1 & 5.2

Item No.			
T3893	3 / 8	0.2 - 0.8mm	168mm



## Dissipative Tweezers


1. Carbon fibre tips allow for safe handling of highly sensitive electrical components.
2. High grade, stainless steel bow - acid and corrosion resistant.
3. Precision welded joint for consistent, repetitive action.
4. Fully ESD compliant for safe use on sensitive electronic components.
5. Anti-magnetic to prevent electro-magnetic damage.
6. Heat resistant up to 270°C for safe use.



### ESD Wire Stripper Pliers

Six pre-set blade pairs: 0.4, 0.5, 0.6, 0.8, 1.0, 1.3mm.  
IEC 61340. 5.1 & 5.2


Item No.				
T3894	3 / 8	0.4 - 1.3mm	152mm	6



### ESD Wire Stripping Pliers

Six pre-set blade pairs: 0.8, 1.0, 1.3, 1.6, 2.0, 2.6mm.  
IEC 61340. 5.1 & 5.2

Item No.				
T3895	3 / 8	0.8 - 2.6mm	152mm	6



## Carbofib ESD



### Carbofib ESD Fine Tweezers

Fine tips.  
IEC 61340. 5.1 & 5.2


Item No.		TYPE	
T2390	130mm	259CF	1



### Carbofib ESD Slim Tweezers


Fine, extra slim tips.  
IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2391	130mm	5CF	1



## Tweezers

1. Manufactured using high grade, stainless steel - acid and corrosion resistant.
2. Anti-magnetic to prevent electro-magnetic damage.
3. Precision welded joint for consistent, repetitive action.
4. Fine polished for a non-reflective matt finish.



### Carbofib ESD Round Tweezers

Round tips, 2mm wide.  
IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2392	130mm	249CF	1

## Precision Tweezers



### Fine Universal Tweezers

Fine, blunt tips, 2mm wide, finely milled inside. Polished and fine nickel plated.

Item No.			
T2301	115mm	C	1



### Black Fine Universal Tweezers

Fine, blunt tips, 2mm wide, finely milled inside. Polished and black coated.

Item No.			
T2302	115mm	C	1



### Blunt Universal Tweezers

Blunt tips, 3.5mm wide, finely milled inside. Polished and fine nickel plated.

Item No.			
T2307	145mm	C	1



**Universal Tweezers**

Blunt tips, 3.5mm wide, finely milled inside. Polished and black or PVC coated.

Item No.				
T2308	145mm	Black	C	1
T2308A	145mm	PVC	C	1



**Universal Cross-Cut Tweezers**

Blunt tips, 2mm wide, fine cross cut inside. Polished and fine nickel plated.

Item No.				
T2309	140mm		C	1



**Cross Pattern Tweezers**

Reverse action. Soldering tweezers with finger pads to protect against heat. Fine, bent tips, 2.5mm wide. Polished and fine nickel plated.

Item No.				
T2313A	160mm		C	1



**Tweezers - Guide Pin**

Fine, blunt tips, bent, finely milled inside. With guide pin. Polished and fine nickel plated.

Item No.				
T2314	150mm		C	1



**Black Tweezers - Guide Pin**

Fine, blunt tips, bent, finely milled inside. With guide pin. Polished and black coated.

Item No.				
T2315	150mm		C	1



**Fine Straight Tweezers**

Fine, straight tips.

Item No.				
T2316	105mm	SA (18/10)		1



**Bent Tweezers**

Fine, bent tips.

Item No.				
T2317	105mm	SA (18/10)		1



**Long Straight Tweezers**

Fine, straight extra long tips.

Item No.				
T2318	130mm	SA (18/10)		1



**Extra Long Tip Tweezers**

Fine, straight extra long tips.

Item No.				
T2319	120mm	S		1



**Radio Tweezers - Straight**

Fine, blunt tips, 2mm wide, straight. Finely milled inside. Polished and fine nickel plated.

Item No.				
T2327	155mm	C		1





**Radio Tweezers - Bent**

Fine, blunt tips, 2mm wide, bent. Finely milled inside. Polished and fine nickel plated.

Item No.	Length	Info	Unit
T2328	155mm	C	1



**Curved Precision Tweezers**

Fine tips, curved.

Item No.	Length	TYPE	Unit
T2339	110mm	7.SA	1



**Angled Tweezers**

Superfine tips, angled at 60°.

Item No.	Length	TYPE	Unit
T2330	110mm	5B.SA	1



**Sharp Precision Tweezers**

Fine, sharp tips, straight.

Item No.	Length	TYPE	Unit
T2340	110mm	3C.SA	1



**Offset & Angled Tweezers**

Superfine tips, offset and angled at 60°.

Item No.	Length	TYPE	Unit
T2331	115mm	5C.SA	1



**Superfine Straight Tweezers**

Superfine tips, straight.

Item No.	Length	TYPE	Unit
T2341	110mm	5B.SA	1



**Positioning Tweezers**

For SOT-packages, monolithic chip capacitors, etc.

Item No.	Length	TYPE	Unit
T2334	120mm	SM104.SA	1



**Fine Straight Tweezers**

Fine tips, straight.

Item No.	Length	TYPE	Unit
T2343	130mm	MM.SA	1



**Angled Positioning Tweezers**

Grooved tips, angled at 30°. For cylindrical devices up to 1mm Ø.

Item No.	Length	TYPE	Unit
T2336	120mm	SM115.SA	1



**Ceramic Straight Tweezers**

Fine, straight tips.

Item No.	Length	TYPE	Unit
T2345A	140mm	73 MZ SA	1



**Straight Fine Tip Tweezers**

Straight, fine tips.

Item No.		TYPE	
T2346	127mm	AA.SA	1



**Round Positioning Tweezers**

Tips round inside. For cylindrical devices up to 2mm Ø.

Item No.		TYPE	
T2354	115mm	578.SA	1



**Strong Flat Precision Tweezers**

Strong, thick, flat edges, straight.

Item No.		TYPE	
T2347	123mm	00.SA	1



**Bent Positioning Tweezers**

Fine, bent tips, fine cross-cut inside.

Item No.		TYPE	
T2359	150mm	22.SA	1



**Flat Sharp Precision Tweezers**

Flat, sharp, fine tips.

Item No.		TYPE	
T2348	122mm	2.SA	1



**Round Positioning Tweezers**

Flat, round tips, straight.


Item No.		TYPE	
T2360	120mm	2A.SA	1



**Reverse Cross Pattern Tweezers**

Reverse action. For SOT-packages, monolithic chip capacitors, etc.

Item No.		TYPE	
T2349	120mm	X104.SA	1



**Flat Tip Tweezers**

Spatulas. Square flat tips.

Item No.		TYPE	
T2364	105mm	127.SA	1



**Round Positioning Tweezers**

Tips round inside. For cylindrical devices up to 1mm Ø.

Item No.		TYPE	
T2351	115mm	582.SA	1




**Flat Blunt Precision Tweezers**

Flat, blunt tips, finely milled inside.

Item No.		TYPE	
T2381	120mm	OOD.SA	1

## Tweezers

1. Manufactured using high grade, stainless steel - acid and corrosion resistant.
2. ESD-safe, black epoxy coating with a surface resistance of  $10^5 - 10^6$ .
3. Anti-magnetic to prevent electro-magnetic damage.
4. Precision welded joint for consistent, repetitive action.
5. Fine polished, matt finish on the tips.



### Precision ESD Tweezers



#### ESD Precision Tweezers

Extra fine, sharp, straight tips.  
IEC 61340. 5.1 & 5.2

Item No.	Length	TYPE	Icon
T2340D	110mm	3C.SA ESD	1



#### ESD Precision Tweezers

Superfine tips, straight.  
IEC 61340. 5.1 & 5.2

Item No.	Length	TYPE	Icon
T2341D	110mm	5.SA ESD	1



#### ESD Precision Tweezers

Straight, fine tips.  
IEC 61340. 5.1 & 5.2

Item No.	Length	TYPE	Icon
T2346D	127mm	AA.SA ESD	1



#### ESD Precision Tweezers

Strong, thick, flat edges, straight.  
IEC 61340. 5.1 & 5.2

Item No.	Length	TYPE	Icon
T2347D	122mm	00.SA ESD	1



#### ESD Precision Tweezers

Flat, sharp, fine tips.  
IEC 61340. 5.1 & 5.2

Item No.	Length	TYPE	Icon
T2348D	120mm	2.SA ESD	1





**ESD Round Positioning Tweezers**

Flat, fine, round tips. For handling delicate or small components.

IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2360D	123mm	2A.SA ESD	1



**ESD Fine Precision Tweezers**

Slim, straight, fine tips.

IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2369D	120mm	1.SA ESD	1



**ESD Fine Curved Tweezers**

Extra fine tips, curved and strong.

IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2361D	120mm	7A.SA ESD	1



**ESD Curved Positioning Tweezers**

Flat, fine tips, curved. For handling delicate or small components. Tip angle facilitates wafer tray loading.

IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2370D	117mm	2AB.SA ESD	1



**ESD Smooth Tip Tweezers**

For positioning and soldering 1mm wide components. 45° tips.

IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2362D	120mm	12.SA ESD	1



**ESD Very Sharp Tweezers**

Very sharp, fine tips.

IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2379D	120mm	3.SA ESD	1



**ESD Positioning Tweezers**

Grooved tips for positioning and soldering 1mm wide components.

IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2363D	120mm	13.SA ESD	1



**ESD Extremely Fine Tweezers**

Extra fine, straight tips.

IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2388D	110mm	4A.SA ESD	1



**ESD Long Superfine Tweezers**

Slim, long, superfine tips. Provides extended reach and access in confined areas.

IEC 61340. 5.1 & 5.2

Item No.		TYPE	
T2368D	140mm	SS.SA ESD	1



**ESD Oblique Tweezers**

Oblique, extra fine tips. For improved visibility whilst working.

IEC 61340. 5.1 & 5.2


Item No.		TYPE	
T2389D	120mm	5A.SA ESD	1

# Screwdrivers

1. Ergonomic tri-lobe handle design for comfort and effective delivery of torque.
2. Fully ESD compliant for safe use on sensitive electronic components.
3. Toughened alloy steel blade for exceptional strength and durability.
4. Black anti-peel finish eliminates the risk of damage from flaking chrome.
5. Handle injection moulded directly to blade giving the ultimate bond for increased reliability and durability.
6. Precision machined tip for an exact screw fit and damage free screwdriving.



## Triton ESD



### ESD Screwdrivers - Slotted Parallel

DIN ISO 2380 , IEC 61340. 5.1 & 5.2

Item No.	Blade Width	Blade Length	Tip Width	Tip Length	Hex Size
T4725ESD 03	3mm (1/8")	75mm (3")	0.5mm (0.02")	70mm (2 3/4")	6
T4725ESD 04	3mm (1/8")	100mm (4")	0.5mm (0.02")	80mm (3 1/8")	6
T4725ESD 41	4mm (5/32")	100mm (4")	0.8mm (0.031")	90mm (3 1/2")	6
T4725ESD 05	5mm (3/16")	125mm (5")	0.8mm (0.031")	90mm (3 1/2")	6
T4725ESD 10	5mm (3/16")	250mm (10")	0.8mm (0.031")	90mm (3 1/2")	6



### ESD Screwdrivers - Pozidriv

DIN ISO 2380 , IEC 61340. 5.1 & 5.2

Item No.	Tip Type	Blade Width	Blade Length	Tip Length	Hex Size
T4723ESD 0	PZO	3.5mm (9/64")	80mm (3 1/8")	70mm (2 3/4")	6
T4723ESD 1	PZ1	5.0mm (3/16")	80mm (3 1/8")	90mm (3 1/2")	6
T4723ESD 2	PZ2	6.0mm (7/32")	100mm (4")	100mm (4")	6



### ESD Screwdrivers - Phillips

DIN ISO 2380 , IEC 61340. 5.1 & 5.2

Item No.	Tip Type	Blade Width	Blade Length	Tip Length	Hex Size
T4722ESD 0	PH0	3.5mm (9/64")	60mm (2 3/8")	70mm (2 3/4")	6
T4722ESD 1	PH1	5.0mm (3/16")	80mm (3 1/8")	90mm (3 1/2")	6
T4722ESD 13	PH1	5.0mm (3/16")	300mm (12")	90mm (3 1/2")	6
T4722ESD 2	PH2	6.0mm (7/32")	100mm (4")	100mm (4")	6
T4722ESD 23	PH2	6.0mm (7/32")	300mm (12")	100mm (4")	6



**ESD Screwdrivers - Torx Tamperproof**

IEC 61340. 5.1 & 5.2


Item No.					
T4718ESD 08	T 08	3.0mm (1/8")	70mm (2 3/4")	80mm (3 1/8")	6
T4718ESD 0820	T 08	3.0mm (1/8")	200mm (8")	80mm (3 1/8")	6
T4718ESD 09	T 09	3.0mm (1/8")	70mm (2 3/4")	80mm (3 1/8")	6
T4718ESD 10	T 10	3.0mm (1/8")	80mm (3 1/8")	90mm (3 1/2")	6
T4718ESD 1030	T 10	3.0mm (1/8")	300mm (12")	90mm (3 1/2")	6
T4718ESD 15	T 15	3.5mm (9/64")	80mm (3 1/8")	90mm (3 1/2")	6
T4718ESD 1530	T 15	3.5mm (9/64")	300mm (12")	90mm (3 1/2")	1
T4718ESD 20	T 20	4.0mm (5/32")	90mm (3 1/2")	90mm (3 1/2")	6



**ESD Bit Holder/Driver**

IEC 61340. 5.1 & 5.2

Item No.					
T4582ESD	C 6.3 (1/4")	11mm (7/16")	125mm (5")	100mm (4")	6



**ESD Screwdriver Set - Torx Tamperproof**

For Torx tamperproof screws. CONTENTS: T4718ESD T08, T09, T10, T15 & T20.

Item No.		
T4730ESD	Set of 5	3



**Triton ESD Screwdriver Set**

T4741ESD CONTENTS: T4725ESD 3 x 75, 3 x 100 & 5 x 135mm, T4723ESD PZ0 x 60, PZ1 x 80 & PZ2 x 100mm. T4741SESD CONTENTS: T4725ESD 3 x 75, 3 x 100, 5 x 125mm. T4722ESD PH0 x 60, PH1 x 80, PH2 x 100.

Item No.			
T4741ESD	Set of 6	Slotted & Pozidriv	3
T4741SESD	Set of 6	Slotted & Phillips	3



**ESD Screwdriver Set/6 - SL/PH/TX**

Long reach screwdrivers. CONTENTS: T4725ESD 5 x 250mm, T4722ESD PH1 x 300 & PH2 x 300mm, T4718ESD T08 x 200, T10 x 300 & T15 x 300mm.

Item No.		
T4797ESD	Set of 6	1



## Dissipative precision screwdrivers

1. Ergonomically designed handle with hollow rotating cap for ease of use and precise control.
2. Premium quality alloy steel blade for exceptional strength and durability.
3. Precision machined tip for an exact screw fit and damage free screwdriving.
4. Black anti-peel tips eliminate the risk of damage from flaking chrome.
5. Fully ESD compliant for safe use on sensitive electronic components.



### Xonic ESD



#### ESD Electronic Screwdrivers - Slotted

IEC 61340. 5.1 & 5.2

Item No.	Tip	Blade	Tip	Blade	Box
T4880XES08	0.8mm (1/32")	60mm (2 3/8")	0.20mm (0.008")	97mm (3 13/16")	30
T4880XES12	1.2mm (3/64")	60mm (2 3/8")	0.25mm (0.010")	97mm (3 13/16")	30
T4880XES15	1.5mm (1/16")	60mm (2 3/8")	0.30mm (0.012")	97mm (3 13/16")	30
T4880XES18	1.8mm (5/64")	60mm (2 3/8")	0.30mm (0.012")	97mm (3 13/16")	30
T4880XES256	2.5mm (3/32")	60mm (2 3/8")	0.40mm (0.016")	97mm (3 13/16")	30
T4880XES257	2.5mm (3/32")	75mm (3")	0.40mm (0.016")	97mm (3 13/16")	30
T4880XES310	3.0mm (1/8")	100mm (4")	0.50mm (0.020")	97mm (3 13/16")	20
T4880XES315	3.0mm (1/8")	150mm (6")	0.50mm (0.020")	97mm (3 13/16")	10
T4880XES410	4.0mm (5/32")	100mm (4")	0.60mm (0.024")	97mm (3 13/16")	20
T4880XES415	4.0mm (5/32")	150mm (6")	0.60mm (0.024")	97mm (3 13/16")	10



#### ESD Screwdrivers - Pozidriv

IEC 61340. 5.1 & 5.2

Item No.	Tip	Blade	Tip	Blade	Box
T4875X ESD	PZO 3.0mm (1/8")	60mm (2 3/8")	97mm (3 13/16")	30	
T4875X ESD 1	PZI 4.5mm (11/64")	80mm (3 1/8")	97mm (3 13/16")	30	



#### ESD Screwdriver - Phillips

IEC 61340. 5.1 & 5.2

Item No.	Tip	Blade	Tip	Blade	Box
T4882X000ES	PH000 2.5mm (3/32")	60mm (2 3/8")	97mm (3 13/16")	30	
T4882X00ESD	PH00 2.5mm (3/32")	60mm (2 3/8")	97mm (3 13/16")	30	
T4882X0 ESD	PH0 3.0mm (1/8")	60mm (2 3/8")	97mm (3 13/16")	30	
T4882X1 ESD	PH1 4.5mm (11/64")	80mm (3 1/8")	97mm (3 13/16")	30	



**ESD Screwdrivers - Torx**

IEC 61340. 5.1 & 5.2

Item No.					
T4877XESD04	T 04	2.5mm (3/32")	50mm (2")	97mm (3 13/16")	30
T4877XESD05	T 05	2.5mm (3/32")	50mm (2")	97mm (3 13/16")	30
T4877XESD06	T 06	3.5mm (9/64")	50mm (2")	97mm (3 13/16")	30
T4877XESD07	T 07	3.5mm (9/64")	50mm (2")	97mm (3 13/16")	30
T4877XESD08	T 08	3.5mm (9/64")	60mm (2 3/8")	97mm (3 13/16")	30



**Xonic Screwdrivers - Hex**

IEC 61340. 5.1 & 5.2

Item No.					
T4838XESD15	3.2mm (1/8")	50mm (2")	2.5mm (3/32")	97mm (3 13/16")	30
T4838XESD20	3.5mm (9/64")	50mm (2")	2.5mm (3/32")	97mm (3 13/16")	30
T4838XESD25	4.0mm (5/32")	60mm (2 3/8")	3.0mm (1/8")	97mm (3 13/16")	30
T4838XESD30	4.5mm (11/64")	60mm (2 3/8")	3.5mm (9/64")	97mm (3 13/16")	30



**Xonic Nut Spinner**

IEC 61340. 5.1 & 5.2

Item No.					
T4840XESD32	3.2mm (1/8")	60mm (2 3/8")	4mm (5/32")	97mm (3 13/16")	30
T4840XESD35	3.5mm (9/64")	60mm (2 3/8")	4mm (5/32")	97mm (3 13/16")	30
T4840XESD40	4.0mm (5/32")	60mm (2 3/8")	4mm (5/32")	97mm (3 13/16")	30
T4840XESD45	4.5mm (11/64")	60mm (2 3/8")	4mm (5/32")	97mm (3 13/16")	30
T4840XESD50	5.0mm (3/16")	60mm (2 3/8")	4mm (5/32")	97mm (3 13/16")	30
T4840XESD55	5.5mm (7/32")	60mm (2 3/8")	4mm (5/32")	97mm (3 13/16")	30



**Xonic Screwdriver Set/7**

Slotted and Phillips screws. CONTENTS: T4880XESD 2.5 x 75, 3 x 100, 3 x 150, 4 x 100 & 4 x 150mm, T4882XESD PH0 x 60 & PH1 x 80mm.

IEC 61340. 5.1 & 5.2

Item No.		
T4883XESD	Set of 7	1



**Xonic Screwdriver Set/4**


Slotted and Phillips screws. CONTENTS: T4880XESD 1.8 x 60, 3 x 100 & 4 x 150mm, T4882XESD PH0 x 60mm.

IEC 61340. 5.1 & 5.2

Item No.		
T4884X ESD	Set of 4	1

## Precision screwdrivers

1. Ergonomically designed handle with hollow rotating cap for ease of use and precise control.
2. Premium quality chrome vanadium steel blade for exceptional strength and durability.
3. Precision machined tip for an exact screw fit and damage free screwdriving.
4. Black anti-peel tips eliminates the risk of damage from flaking chrome.
5. Tip type colour coding for easy identification.



## Xonic Precision Screwdrivers



### Xonic Precision Screwdrivers - Slotted

Item No.					
T4880X 08	0.8mm (1/32")	60mm (2 3/8")	0.20mm (0.008")	97mm (3 13/16")	30
T4880X 12	1.2mm (3/64")	60mm (2 3/8")	0.20mm (0.008")	97mm (3 13/16")	30
T4880X 15	1.5mm (1/16")	60mm (2 3/8")	0.25mm (0.010")	97mm (3 13/16")	30
T4880X 18	1.8mm (5/64")	60mm (2 3/8")	0.30mm (0.012")	97mm (3 13/16")	30
T4880X 256	2.5mm (3/32")	60mm (2 3/8")	0.40mm (0.016")	97mm (3 13/16")	30
T4880X 257	2.5mm (3/32")	75mm (3")	0.40mm (0.016")	97mm (3 13/16")	30
T4880X 310	3.0mm (1/8")	100mm (4")	0.50mm (0.020")	97mm (3 13/16")	20
T4880X 315	3.0mm (1/8")	150mm (6")	0.50mm (0.020")	97mm (3 13/16")	10
T4880X 410	4.0mm (5/32")	100mm (4")	0.80mm (0.031")	97mm (3 13/16")	30
T4880X 415	4.0mm (5/32")	150mm (6")	0.80mm (0.031")	97mm (3 13/16")	10



### Xonic Precision Screwdrivers - Phillips

Item No.					
T4882X 000	PH000	2.5mm (3/32")	60mm (2 3/8")	97mm (3 13/16")	30
T4882X 00	PH00	2.5mm (3/32")	60mm (2 3/8")	97mm (3 13/16")	1
T4882X 0	PH0	3.0mm (1/8")	60mm (2 3/8")	97mm (3 13/16")	10
T4882X 1	PH1	4.5mm (11/64")	80mm (3 1/8")	97mm (3 13/16")	30





**Xonic Precision Screwdrivers - Torx**

Item No.	✦	∅	↔	↔	📦
T4877X 04	T 04	2.5mm (3/32")	50mm (2")	97mm (3 13/16")	30
T4877X 05	T 05	2.5mm (3/32")	50mm (2")	97mm (3 13/16")	30
T4877X 06	T 06	3.5mm (9/64")	50mm (2")	97mm (3 13/16")	30
T4877X 07	T 07	3.5mm (9/64")	50mm (2")	97mm (3 13/16")	30
T4877X 08	T 08	3.5mm (9/64")	60mm (2 3/8")	97mm (3 13/16")	30
T4877X 09	T 09	4.0mm (5/32")	60mm (2 3/8")	97mm (3 13/16")	30
T4877X 10	T 10	4.0mm (5/32")	80mm (3 1/8")	97mm (3 13/16")	30
T4877X 15	T 15	4.0mm (5/32")	80mm (3 1/8")	97mm (3 13/16")	30



**Xonic Screwdriver Set/4**

Slotted and Phillips screws. CONTENTS: T4880X 1.8 x 60, 3 x 100 & 4 x 150mm, T4882X PH0 x 60mm.

Item No.	i	📦
T4884X	Set of 4	1



**Xonic Screwdriver Set/5**

Slotted and Phillips screws. CONTENTS: T4880X 2.5 x 75, 3 x 100 & 4 x 100mm, T4882X PH00 x 60 & PH0 x 60mm.

Item No.	i	📦
T4880X/5	Set of 5	1



**Xonic Screwdriver Set - Hex**

Hexagon screws. CONTENTS: T4873X 0.7 x 50, 0.9 x 50, 1.3 x 50, 1.5 x 50, 2 x 50, 2.5 x 60 & 3 x 60mm.

Item No.	i	📦
T4874X	Set of 7	1



**Xonic Screwdriver Set/7**

Slotted and Phillips screws. CONTENTS: T4880X 2.5 x 75, 3 x 100, 3 x 150, 4 x 100 & 4 x 150mm, T4882X PH0 x 60 & PH1 x 80mm.

Item No.	i	📦
T4883X	Set of 7	1



**Xonic Screwdriver Set - Torx**

Torx screws. CONTENTS: T4877X T06, T07, T08, T09, T10, T15 & T20.

Item No.	i	📦
T4877PX	Set of 7	30

Precision Screwdrivers



VDE Screwdriver Set/7 - SL/PH

Designed to turn the smallest of screws with ease, the C.K VDE precision screwdriver combines the control of a rotating cap with the safety of VDE approval. Ergonomically designed handle with hollow rotating cap for ease of use & precise control. Premium quality chrome vanadium steel blade for exceptional strength & durability. Precision machined, magnetic tips for an exact screw fit & damage free screwdriving. VDE approved - individually tested to 10,000v for safe live working up to 1,000v. CONTENTS: Slotted sizes: 1.5, 1.8, 2.0, 2.5, 3.0 x 50mm, Phillips sizes: PH00, PH0 x 50mm.

Item No.	i	📦
T4897	Set of 7	24



Watchmakers Screwdriver Set/4 - SL

Slotted screws. CONTENTS: 1 x 15, 1.6 x 20, 2 x 22, 2.4 x 25mm.

Item No.	i	📦
T4852P	Set of 4	6



Watchmakers Screwdriver Set/6 - SL/PH

Slotted and Phillips screws. CONTENTS: 1 x 15, 1.6 x 20, 2 x 22, 2.4 x 25, PH00 x 25, PH0 x 25mm.

Item No.	i	📦
T4854P	Set of 6	6



Screwdriver Set/7 - SL/PH/TX

6 double ended blades. CONTENTS: Screwdriver handle, double ended blades, sizes: slotted 1.5mm x PH000, slotted 2.0mm x PH00, slotted 3.0 x PH0, slotted 4.0mm x PH1, TX05 x TX06 & TX07 x TX08.

Item No.	i	📦
T4896	Set of 7	6

Precision Ceramic Trimmers



Ceramic Trimmers - Slotted

Item No.	🌀	↔️	🌀	↔️	📦
T4845 09	0.9mm (.035")	15mm (5/8")	0.4mm (.016")	85mm (3 3/8")	10
T4845 13	1.3mm (.051")	15mm (5/8")	0.4mm (.016")	85mm (3 3/8")	10
T4845 18	1.8mm (.071")	15mm (5/8")	0.4mm (.016")	85mm (3 3/8")	10
T4845 26	2.6mm (.102")	15mm (5/8")	0.4mm (.016")	85mm (3 3/8")	10



Ceramic Trimmers - Phillips


Item No.	⊕	🌀	↔️	↔️	📦
T4847	PH 0	2.6mm (.102")	15mm (5/8")	85mm (3 3/8")	10
T4847 0	PH 0 spec	2.6mm (.102")	15mm (5/8")	85mm (3 3/8")	10



### Ceramic Trimmers - 4 in 1

4 ceramic blades in 1 tool. 2 reversible inserts with 2 ceramic blades each. Transparent protection caps. Antistatic handle. With protection cap fitted, the blade inserts can be used as mini-alignment tools.

Item No.					
T4856	0.9mm (.035")	PH 0 spec	1.8mm (.071")	PH 0	10
T4856A	0.9mm (.035")	PH 0 spec	1.8mm (.071")	2.6mm (.102")	10
Z4856 1					
Z4856 2					
Z4856 3					




### Plastic Trimmers



### Plastic Trimmer Set/7

Contents each 1 piece: Slotted with polycarbonate tip 0.5 x 1.2 / 0.5 x 1.5 / 0.7 x 2.4, Slotted with brass tip 0.5 x 1.0 / 0.5 x 2.0 / 0.7 x 1.5 / 0.7 x 2.5.

Item No.		
T4844	Set of 7	1



### Plastic Trimmer Set/10

Set of economy single ended trimming tools with 10 different heads for delicate trimming of electronic equipment. Manufactured from moulded/thermoplastic material. Contents of set, each 1 piece: 0.7 x 1.0mm square / 0.5 x 1.3mm and 0.8 x 2.3mm hexagon / Slotted: 0.7 x 2.0 / 0.7 x 2.4 / 0.7 x 1.0 / 0.8 x 1.3 / 0.8 x 1.8 / 0.7 x 2.4. and 1.3mm.

Item No.		
T4857	Set of 10	3

# precision

## Ceramic trimmers

1. Zirconia ceramic tips - safe trimming of highly sensitive electrical components, highly acid resistant (other than Hydrofluoric), solder repellent and electrically non-conductive.
2. Heat resistant up to 1000°C for safe use.
3. Non-magnetic to prevent electro-magnetic damage.





## Precision Wire Strippers



### Fibre Optic Stripper

For damage free wire preparation every time. Blades accurately ground and fully hardened for long life. 50mm scale with 1mm graduations and length stop. Compact design.

Item No.	Ø	📦
T3755 018	0.18mm	1
T3755 060	0.60mm	1



### Precision Wire Stripper

Compact precision wire strippers for repeatable, damage free stripping of PVC, Teflon & similar coated wire. Graduated depth stop for stripping to precise lengths. Specially hardened blades for outstanding long term performance. 50mm scale with 1mm graduations and length stop.


Item No.	Ø	📦
T3756 20	0.20mm	1
T3756 25	0.25mm	1
T3756 30	0.30mm	1
T3756 40	0.40mm	1
T3756 50	0.50mm	1
T3756 60	0.60mm	1
T3756 80	0.80mm	1
T3756 100	1.0mm	1



### Adjustable Precision Wire Stripper

Compact precision wire strippers for repeatable, damage free stripping of PVC, Teflon & similar coated wire. Graduated depth stop for stripping to precise lengths. Specially hardened blades for outstanding long term performance. Adjustable to strip 6 wire diameters.

Item No.	Ø	📦
330009	0.12, 0.16, 0.20, 0.25, 0.30, 0.40mm	1
330013	0.25, 0.30, 0.40, 0.50, 0.60, 0.80mm	1
330011	0.30, 0.40, 0.50, 0.60, 0.80, 1.0mm	1



### Strip Cut Wire Stripper

Easily adjustable to 6 wire diameters. Adjustable length stop with 15mm scale. Precision metal cutting and stripping blade, hardened. Integrated wire cutter for copper wires up to 0.8mm.

Item No.	Ø	📦
330012	0.25, 0.30, 0.40, 0.50, 0.60, 0.80mm	1



### ESD Precision Wire Stripper

Adjustable - damage free wire preparation every time. Fully ESD compliant for safe use on sensitive electronic components. Blades accurately ground and fully hardened for long life. 50mm scale with 1mm graduations and length stop. Adjustable to strip 6 wire diameters. Compact design. For solid and stranded wire with PVC, PTFE or similar insulation.

IEC 61340. 5.1 & 5.2

Item No.	Ø	📦
T3757ESD 1	0.12, 0.16, 0.20, 0.25, 0.30, 0.40mm	1
T3757ESD 2	0.25, 0.30, 0.40, 0.50, 0.60, 0.80mm	1
T3757ESD 3	0.30, 0.40, 0.50, 0.60, 0.80, 1.00mm	1



**ESD Wire Stripper Spares**

Set of replacement blades for C.K Precision Wire Strippers.

Item No.
Z3757 1
Z3757 2
Z3757 3



**PLCC Extractor**

Avoids the damage of PLCC components when extracting. Self opening for repetitive action. Hardened stainless steel sockets. Made from dissipative thermoplastic material. For all PLCC-components (20-124 pins).

Item No.	100mm (4")	
T2371		6

**Other**



**ESD Desoldering Tool**

High capacity pump with 14.5cm<sup>3</sup> volume. Body made from antistatic high quality glass fibre reinforced nylon. Heat resistant & conductive carbon fibre tip. Suction pressure can be increased or decreased by turning the spring around. IEC 61340. 5.1 & 5.2

Item No.	210mm (8 1/4")	
T6103A		1



**ESD Ball Pen**

Designed for ESD sensitive areas, and normal use. Writing color: Blue. DIN EN 61340 5.1 & 5.2

Item No.	
Z1123	1



**ESD Desoldering Tool Nozzle**

Spare nozzle for C.K desoldering pump T6103A. Nozzle made of Carbon. IEC 61340. 5.1 & 5.2

Item No.	
T6104A	1



**Magnetic Pickup Pointer & Pen**

Multi-use product for use in the workshop, office or home. The magnetic pick-up pointer extends to 630mm / 24.3/4". Unscrew the magnetic tip to reveal the pen which accommodates standard refills. With pocket clip.

Item No.
T1355







# Power Tool Accessories

<b>Masonry Drill Bits</b>	<b>106</b>
<b>Metal Drill Bits</b>	<b>108</b>
<b>Fast4 Fluted Bits</b>	<b>110</b>
<b>Wood Drill Bits</b>	<b>111</b>
<b>Multi-Material</b>	<b>113</b>
<b>ProCobalt Holesaws</b>	<b>114</b>
<b>Arbors &amp; Accessories</b>	<b>116</b>
<b>Blue Steel Impact Bits</b>	<b>118</b>
<b>Screwdriver Bits</b>	<b>121</b>
<b>Screwdriver Bit Holders</b>	<b>126</b>
<b>Multitool Blades</b>	<b>127</b>
<b>Jigsaw Blades</b>	<b>128</b>
<b>Reciprocating Blades</b>	<b>129</b>

## Masonry Drill Bits



### SDS+ Concrete Drill Bits

Tungsten carbide tipped with optimized geometry for drilling concrete and stone. Vacuum brazed tips for durability. Ground flutes designed for optimum debris removal. SDS+ shank.

Item No.	Ø	→	←	📦
T3120 0411	4mm	48mm	110mm	5
T3120 0511	5mm	48mm	110mm	5
T3120 0516	5mm	90mm	160mm	5
T3120 05511	5.5mm	48mm	110mm	5
T3120 05516	5.5mm	90mm	160mm	5
T3120 0611	6mm	48mm	110mm	5
T3120 0616	6mm	90mm	160mm	5
T3120 0621	6mm	140mm	210mm	5
T3120 06516	6.5mm	90mm	160mm	5
T3120 0711	7mm	48mm	110mm	5
T3120 0716	7mm	90mm	160mm	5
T3120 0816	8mm	90mm	160mm	5
T3120 0821	8mm	140mm	210mm	5
T3120 0826	8mm	185mm	260mm	5
T3120 0845	8mm	350mm	450mm	5
T3120 1016	10mm	90mm	160mm	5
T3120 1021	10mm	140mm	210mm	5
T3120 1026	10mm	185mm	260mm	5
T3120 1045	10mm	350mm	450mm	5
T3120 1215	12mm	90mm	160mm	5
T3120 1221	12mm	140mm	200mm	5
T3120 1225	12mm	180mm	260mm	5
T3120 1245	12mm	350mm	450mm	5
T3120 1425	14mm	180mm	260mm	5
T3120 1445	14mm	350mm	450mm	5
T3120 1630	16mm	250mm	310mm	5
T3120 1645	16mm	350mm	450mm	5
T3120 1830	18mm	250mm	310mm	5
T3120 1845	18mm	350mm	450mm	5
T3120 2030	20mm	250mm	310mm	5
T3120 2045	20mm	350mm	450mm	5
T3120 2545	25mm	350mm	450mm	5
T3120 12100	12mm	950mm	1000mm	5
T3120 16100	16mm	950mm	1000mm	5
T3120 20100	20mm	950mm	1000mm	5
T3120 25100	25mm	950mm	1000mm	5



### SDS Concrete Drill Bit Set/7

CONTENTS: 5 x 110mm / 6 x 110mm / 8 x 110mm / 6 x 150mm / 8 x 150mm / 10 x 150mm & 12 x 150mm.

#### Item No.

T3121



5



### SDS Flat Chisel Bits

SDS+ chisels. Hardened carbon steel for durability.

#### Item No.

T3146

T3147



20mm

40mm



250mm

250mm



6

6



### SDS Point Chisel Bit

SDS+ chisel. Hardened carbon steel for durability.

#### Item No.

T3145




Point



250mm



6



### SDS Masonry Drill Bit Set/14

Multiple quantities of most commonly used sizes. Drill bits supplied in roll up storage case offering a convenient long term storage solution. Tungsten carbide tipped for speed, performance and endurance. For rotary and percussion drills. CONTENTS: 5 x 110mm (x2); 5.5 x 110mm (x3); 6 x 110mm (x3); 5.5 x 160mm (x2); 6 x 160mm (x2); 7 x 160mm (x1); 8 x 160mm (x1).

#### Item No.

T3132



Set of 14



3



**SDS Masonry & Chisel Set/15**

Drill bits supplied in roll up storage case offering a convenient long term storage solution. Tungsten carbide tipped for speed, performance and endurance. For rotary and percussion drills. Contents of set, each 1 piece: 5 x 110mm / 5 x 160mm / 5.5 x 110mm / 5.5 x 160mm / 6 x 110mm / 6 x 160mm / 6 x 210mm / 6.5 x 160mm / 7 x 160mm / 8 x 160mm / 10 x 160mm & 12 x 160mm, Point chisel in 250mm / Flat chisel in 20 x 250mm and Scaling chisel in 40 x 250mm.

Item No.			
T3133	Set of 25		3



**Masonry Drill Bits**

Forged steel with tungsten carbide tip. Optimised design for fast and accurate drilling of concrete, stone & brick.

Item No.	Ø		
T3110 0475	4mm	75mm	10
T3110 0585	5mm	85mm	10
T3110 05150	5mm	150mm	10
T3110 05585	5.5mm	85mm	10
T3110 055150	5.5mm	150mm	10
T3110 06100	6mm	100mm	10
T3110 06150	6mm	150mm	10
T3110 065100	6.5mm	100mm	10
T3110 065150	6.5mm	150mm	10
T3110 07100	7mm	100mm	10
T3110 07150	7mm	150mm	10
T3110 08150	8mm	150mm	10
T3110 10150	10mm	150mm	10
T3110 12150	12mm	150mm	10
T3110 13150	13mm	150mm	10
T3110 14150	14mm	150mm	10
T3110 16150	16mm	150mm	10



**SDS Masonry & Chisel Sets CBOX**

Item No.	
T3130CBOX	



**Masonry Drill Bit Set/5**

Forged steel with tungsten carbide tip. Optimised design for fast and accurate drilling of concrete, stone & brick. CONTENTS: 1 of each size: 4, 5.5, 6.5, 7 & 8mm.



Item No.	
T3111	5





## Masonry Hex Drill Bit Set/5

Forged steel with tungsten carbide tip. Optimised design for fast and accurate drilling of concrete, stone & brick. With 4mm hexagonal shaft. CONTENTS: 1 of each size: 4, 5.5, 6.5, 7 & 8mm.

Item No.		
T3112	4mm	5



## Masonry Colour Drill Bit Sets


For rotary and percussion drills. Tungsten carbide tipped - for speed, performance and endurance. Colour coded sizes - for quick and convenient identification of the correct size drill for wall fixings. CONTENTS: 3 x 5mm, 3 x 6mm, 3 x 7mm.

Item No.
T3113
T3113CLIP



## Masonry Drill Bit Set/25

Multiple quantities of most commonly used sizes. Drill bits supplied in roll up storage case offering a convenient long term storage solution. Tungsten carbide tipped for speed, performance and endurance. For rotary and percussion drills. CONTENTS: 4 x 75mm (x3); 5.5 x 85mm (x5); 5.5 x 150mm (x5); 6 x 100mm (x5); 6 x 150mm (x3); 7 x 100mm (x2); 7 x 150mm (x2).

Item No.		
T3131	Set of 25	3

## Metal Drill Bits



## HSS Split Point Drill Bits

High speed steel. 135° split point design for non-wander starting. Flute ground for accurate results.

DIN338


Item No.					
T3100 01	1mm	12mm	34mm	Loose	10
T3100 015	1.5mm	18mm	40mm	Loose	10
T3100 02	2mm	24mm	49mm	Loose	10
T3100 025	2.5mm	30mm	57mm	Loose	10
T3100 03	3mm	33mm	61mm	Loose	10
T3100 035	3.5mm	39mm	70mm	Loose	10
T3100 04	4mm	43mm	75mm	Loose	10
T3100 045	4.5mm	47mm	80mm	Loose	10
T3100 05	5mm	52mm	86mm	Loose	10
T3100 055	5.5mm	57mm	93mm	Loose	10
T3100 06	6mm	57mm	93mm	Loose	10
T3100 065	6.5mm	63mm	101mm	Loose	10
T3100 07	7mm	69mm	109mm	Loose	10
T3100 08	8mm	75mm	117mm	Loose	10
T3100 09	9mm	81mm	125mm	Loose	10
T3100 10	10mm	87mm	133mm	Loose	10
T3100 11	11mm	94mm	142mm	Loose	10
T3100 12	12mm	101mm	151mm	Loose	10
T3100 13	13mm	101mm	151mm	Loose	10
T3100 045D	4.5mm	47mm	80mm	Single Pack	6
T3100 05D	5mm	52mm	86mm	Single Pack	6
T3100 055D	5.5mm	57mm	93mm	Single Pack	6
T3100 06D	6mm	57mm	93mm	Single Pack	6
T3100 065D	6.5mm	63mm	101mm	Single Pack	6
T3100 07D	7mm	69mm	109mm	Single Pack	6
T3100 08D	8mm	75mm	117mm	Single Pack	6
T3100 09D	9mm	81mm	125mm	Single Pack	6
T3100 10D	10mm	87mm	133mm	Single Pack	6
T3100 11D	11mm	94mm	142mm	Single Pack	6
T3100 12D	12mm	101mm	151mm	Single Pack	6
T3100 13D	13mm	101mm	151mm	Single Pack	6
T3100 01TD	1mm	12mm	34mm	Twin Pack	6
T3100 015TD	1.5mm	18mm	40mm	Twin Pack	6
T3100 02TD	2mm	24mm	49mm	Twin Pack	6
T3100 025TD	2.5mm	30mm	57mm	Twin Pack	6
T3100 03TD	3mm	33mm	61mm	Twin Pack	6
T3100 035TD	3.5mm	39mm	70mm	Twin Pack	6
T3100 04TD	4mm	43mm	75mm	Twin Pack	6



### Cobalt Split Point Drill Bit Set

Suitable for a range of materials including: steel, aluminium, wood, plastic, laminated sheet and particle board. CONTENTS: 2, 3, 4, 5, 6, 8mm shank. Material: M35, cobalt steel. DIN 338

Item No.	Icon
T3104	1



### HSS Split Point Drill Bit Set/6

High speed steel. 135° split point design for non-wander starting. Flute ground for accurate results. CONTENTS: 2, 3, 4, 5, 6 & 8mm. DIN 338

Item No.	Icon
T3101	3



### HSS Split Point Drill Bit Set/13

High speed steel. 135° split point design for non-wander starting. Flute ground for accurate results. CONTENTS: 1.5, 2, 2.5, 3, 3.2, 3.5, 4, 4.5, 4.8, 5, 5.5, 6 & 6.5mm. DIN 338

Item No.	Icon
T3102	3



### HSS Split Point Drill Bit Set/19

High speed steel. 135° split point design for non-wander starting. Flute ground for accurate results. CONTENTS: 1, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5 & 10mm. DIN 338

Item No.	Icon
T3103	1



### HSS Multi-Step Drills

Centres, drills and deburrs sheet metals in one operation. HSS, precision ground for accurate drilling. Dual flute construction for faster drilling & longer life. Three flats on drive shaft for secure drive in drill chucks.

Item No.	Icon
T3010 1	4, 6, 8, 10, 12, 14, 16, 18 & 20mm
T3008	6, 9, 12.3, 15.2, 18.6, 20.4, 22.5, 25.4, 28.3 & 30.5mm
T3011	6 8 10 12 14 16 18 20 22 24 26 28 30 32mm
T3012	12.5, 12.7, 15.2, 16.2, 18.6, 20.4, 22.5, 25.4, 28.3, 30.5 & 32.5mm



### High Speed Steel Cone Drills

Centres, drills and deburrs sheet metals in one operation. HSS, precision ground for accurate drilling. Dual flute construction for faster drilling & longer life. Three flats on drive shaft for secure drive in drill chucks.

Item No.	Icon
T3014	6 - 26mmØ
T3015	16 - 32mmØ



### TiN Coated Multi-Step Drill

Centres, drills and deburrs sheet metals in one operation. Titanium coated for longer life. HSS, precision ground for accurate drilling. Dual flute construction for faster drilling & longer life. Three flats on drive shaft for secure drive in drill chucks.

Item No.	Icon
T3013	6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 36, 28, 30 & 32mmØ

## Fluted bits

1. 4 bladed design:  
Offering 100% more cutting surface than a traditional flat bit for faster drilling.
2. Pilot screw point:  
Allows accurate positioning and pull through.
3. Optimized flute geometry:  
Waste is removed faster for a cleaner cut and finish.






## Fast4 Fluted Bits



### Fast4 Wood Drill Bits




Precision ground cutting edges with outer spur blades for a smoother cut & cleaner breakout. Clean hole results.

Item No.	Ø			
T2943-16	16mm	110mm	160mm	10
T2943-20	20mm	110mm	160mm	10
T2943-22	22mm	110mm	160mm	10
T2943-25	25mm	110mm	160mm	10
T2943-32	32mm	110mm	160mm	10
T2943S4				1



### Fast4 SDS+ Wood Drill Bits



Precision ground cutting edges with outer spur blades for a smoother cut & cleaner breakout. Clean hole results. SDS drive.

Item No.	Ø			
T2944-16	16mm	110mm	160mm	10
T2944-20	20mm	110mm	160mm	10
T2944-22	22mm	110mm	160mm	10
T2944-25	25mm	110mm	160mm	10
T2944-32	32mm	110mm	160mm	10



### Fast4Access Wood Drill Bits




50% shorter for better access. Precision ground cutting edges with outer spur blades for a smoother cut & cleaner breakout. Clean hole results.

Item No.	Ø		
T2945-16	16mm	50mm	80mm
T2945-20	20mm	50mm	80mm
T2945-22	22mm	50mm	80mm
T2945-25	25mm	50mm	80mm



### Fast4Nails Wood Drill Bits

Designed for use with Nail Embedded Timber; Chipboard, Blockboard, Particle board, Laminated sheet. HSS Bi-Metal construction for increased durability. Extended working life on nail embedded wood. 4 blades for faster drilling. 6.35 Hex Shank for convenience and ease of use.

Item Number	Ø			
T2946-16	16mm	60mm	120mm	90
T2946-20	20mm	60mm	120mm	70
T2946-22	22mm	60mm	120mm	70
T2946-25	25mm	60mm	120mm	70
T2946-32	32mm	60mm	120mm	50



Wood Drill Bits



Flat Wood Bits

HSS, hardened for long life performance. Brad pointed for accurate drill starts. Ground wing spur for clean hole cutting. Quick lock direct E6.3 drive.

Item No.	Ø			
T2942-06	6mm	130mm	160mm	5
T2942-08	8mm	130mm	160mm	5
T2942-10	10mm	130mm	160mm	5
T2942-12	12mm	130mm	160mm	5
T2942-13	13mm	130mm	160mm	5
T2942-14	14mm	130mm	160mm	5
T2942-16	16mm	130mm	160mm	5
T2942-20	20mm	130mm	160mm	5
T2942-22	22mm	130mm	160mm	5
T2942-25	25mm	130mm	160mm	5
T2942-28	28mm	130mm	160mm	5
T2942-32	32mm	130mm	160mm	5
T2942-38	38mm	130mm	160mm	5
T2942-12400	12mm	370mm	400mm	15
T2942-16400	16mm	370mm	400mm	15
T2942-20400	20mm	370mm	400mm	15
T2942-25400	25mm	370mm	400mm	5
T2942-32400	32mm	370mm	400mm	5



Heavy Duty Flat Wood Bits

For use on Nail Embedded Timber; Chipboard, Blockboard, Particle board, Laminated sheet. Heavy duty carbon steel construction for exceptional performance. Bevelled pilot-point reduces bit walk for faster drilling and clean holes. Impact ready hex shank with oversized shaft for greater strength and durability.

Item No.	Ø			
T2952-10	10mm	120mm	152mm	6
T2952-12	12mm	120mm	152mm	6
T2952-14	14mm	120mm	152mm	6
T2952-16	16mm	120mm	152mm	6
T2952-20	20mm	120mm	152mm	6
T2952-22	22mm	120mm	152mm	6
T2952-25	25mm	120mm	152mm	6
T2952-28	28mm	120mm	152mm	6
T2952-32	32mm	120mm	152mm	6
T2952-38	38mm	120mm	152mm	6



Flat Wood Bits Set

Professional quality HSS construction. Brad pointed for accurate drill starts. Ground wing spur for clean hole cutting. Quick lock direct E6.3 drive. CONTENTS: 6 x flat bits, sizes: 10, 13, 16, 20, 22 & 25mm.

Item No.	
T2942P	5



Flat Wood Bit Extension Drive

Extension drive shaft for flat bits with E6.3 drive.

Item No.		
T2940-2	300mm	30



Quick Release Extension Bar - 3 Pack

Quick release for a fast and convenient bit change. Gives greater access to awkward screws and drilling locations. Impact rated 6.35 hex shank for all common power tools. CrV (chrome vanadium) shaft for increased strength and durability. 3 different sizes for all applications.

Item Number		
T2940-3	60mm, 150mm & 300mm	30



Flat Bits - Long Stocked Display




CONTENTS: 3 x flat bits, sizes: 12 x 400mm, 16 x 400mm, 20 x 400mm, 4 x flat bits, sizes: 25 x 400mm, 2 x flat bits, size: 32 x 400mm.

Item No.	
T2942LS	1



## Auger Wood Bits - Short

HSS, hardened for long life performance. Spur lip for clean hole results. Screw tip for precise hole starts. Combination shank suitable for hand and power drills.

Item No.	Ø			
T3033 13	13mm	50mm	100mm	6
T3033 22	22mm	80mm	130mm	6



## Auger Wood Bits - Standard




HSS, hardened for long life performance. Spur ground external edge for clean hole cutting. Screw tip for precise hole starts. Combination shank suitable for hand & power drills.

Item No.	Ø			
T3031 06	6mm	90mm	160mm	6
T3031 08	8mm	100mm	170mm	6
T3031 10	10mm	120mm	190mm	6
T3031 13	13mm	120mm	190mm	6
T3031 16	16mm	130mm	200mm	6
T3031 20	20mm	140mm	210mm	6
T3031 22	22mm	140mm	210mm	6
T3031 25	25mm	140mm	210mm	6
T3031 30	30mm	140mm	210mm	6
T3031 32	32mm	140mm	210mm	6



## Auger Wood Bits - Long


HSS, hardened for long life performance. Spur ground external edge for clean hole cutting. Screw tip for precise hole starts. Combination shank suitable for hand & power drills.


Item No.	Ø			
T3034 10	10mm	220mm	300mm	6
T3034 13	13mm	220mm	300mm	6
T3034 16	16mm	220mm	300mm	6
T3034 20	20mm	220mm	300mm	6
T3034 22	22mm	220mm	300mm	6
T3034 25	25mm	220mm	300mm	6



## Wood Drill Bits


Chrome vanadium steel for long life performance. Brad pointed for accurate drill starts. Spur ground external edge for clean hole cutting.

Item No.	Ø			
T3035 03	3mm	33mm	61mm	10
T3035 04	4mm	43mm	75mm	10
T3035 05	5mm	52mm	86mm	5
T3035 06	6mm	60mm	97mm	5
T3035 08	8mm	75mm	117mm	5
T3035 10	10mm	87mm	133mm	5
T3035 12	12mm	96mm	151mm	5
T3035 13	13mm	96mm	151mm	5
T3035 14	14mm	97mm	151mm	5
T3035 16	16mm	100mm	160mm	3



## Wood Drill Bit Set/5

Chrome vanadium steel for long life performance. Brad pointed for accurate drill starts. Spur ground external edge for clean hole cutting. CONTENTS: 4, 5, 6, 8 & 10mm.

Item No.	
T3040	3



## Countersink Bit

HSS, hardened for long life performance. 1/2", 13 x 90°.

Item No.		
T2601S 5090	13 x 90°	6




**Glass/Tile Drill Bit Set**

Tungsten carbide tipped drill set for easy drilling of glass and ceramics. Titanium nitride coated for wear protection. CONTENTS: 4, 5, 6, 7, 10mm 1/4" quick change hex shank.

<b>Item No.</b>	
T3059	1

**Multi-Material**



**Universal Drill Bit Set**

Tungsten carbide tipped drills specially designed for drilling through concrete, brick, cement, stone, metal & ceramics. CONTENTS: 4, 5, 6, 8 & 10mm.

<b>Item No.</b>	
T3063	3



**Combination Drill Bit Set**

Masonry, Metal & Wood Drill Bit Set, 16 pieces. Contents each 1 piece: For Brick: 4, 5.5, 6.5, 7, 8mm, For Metal: 2, 3, 4, 5, 6, 8mm, For Wood: 4, 5, 6, 8, 10mm.


<b>Item No.</b>	
T3064B	10



**TiN Drill Saw - Twin Pack**

Titanium nitride coated HSS for strength and durability. Drills and cuts to create any size shape or hole. Self-starting tip. Cuts through wood/plastic up to 5mm, aluminium up to 4mm and metal up to 3mm thick. Pack includes 2 drill saws.

<b>Item No.</b>		
T3193T	6mm	3



**TiN Drill Bit Set/6**

135° Forged HSS steel. Precision ground for accurate drilling. Titanium nitride coated for extra wear protection. CONTENTS: 2, 3, 4, 5, 6, 8mm.

<b>Item No.</b>	
T3293	3



**TiN Drill Bit Set/19**

135° Forged HSS steel. Precision ground for accurate drilling. Titanium nitride coated for extra wear protection. CONTENTS: 1, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10mm.

<b>Item No.</b>	
T3291	3



## Holesaws

The ultimate in performance, reliability and output. One saw does it all. Cuts metal, wood, plasterboard and composites.

1. Vari-pitch teeth design optimised for a faster cut.
2. Location pins to avoid over tightening for easy removal.
3. Improved heat dissipation and slug removal access.



## ProCobalt Holesaws



### ProCobalt Holesaws

Premium grade 8% cobalt alloy steel construction for an extended working life. Excellent wear resistance even at high temperatures. For fast and clean cutting of metal, wood, aluminium, steel, cast iron, brass and plastics. Variable pitch teeth for rapid cutting action, efficient swarf removal and reduced vibration.

Item No.	Ø	Box
424001	16mm (5/32")	10
424002	19mm (3/4")	10
424003	20mm (25/32")	10
424005	22mm (7/8")	10
424006	25mm (1")	10
424007	29mm (1 1/8")	10
424008	32mm (1 1/4")	10
424010	38mm (1 1/2")	10
424011	40mm (1 5/16")	10
424012	41mm (1 5/8")	10
424013	43mm (1 11/16")	10
424014	44mm (1 3/4")	10
424015	48mm (1 7/8")	10
424016	51mm (2")	10
424017	54mm (2 1/8")	10
424018	57mm (2 1/4")	10
424019	60mm (2 3/8")	10
424020	64mm (2 1/2")	10
424021	65mm (2 9/16")	10
424022	67mm (2 5/8")	10
424023	68mm (2 11/16")	10
424024	70mm (2 3/4")	10
424025	73mm (2 7/8")	10
424026	76mm (3")	10
424027	79mm (3 1/8")	10
424028	83mm (3 1/4")	10
424029	86mm (3 3/8")	10
424030	89mm (3 1/2")	10
424031	92mm (3 5/8")	10
424032	95mm (3 3/4")	10
424033	102mm (4")	10
424034	105mm (4 1/8")	10
424035	111mm (4 3/8")	10
424036	114mm (4 1/2")	10
424050	127mm (5")	10
424060	152mm (6")	10



**Holesaw Kit - 6 Piece**

CONTENTS: 1 x holesaw, sizes: 40, 54, 65, 67 & 68mm. Quick release arbor 32 - 152mm (11mm shaft).

<b>Item No.</b>	
424044	10



**Electricians Hole Saw Kit - 9 Piece**

CONTENTS: 1 x holesaw, sizes: 16, 20, 25, 32, 38 & 51mm. Arbor 14 - 30mm (8mm shaft). Quick release arbor 32 - 114mm (11mm shaft). Hexagon key 4mm.

<b>Item No.</b>	
424045	10



**Holesaw Kit - 9 Piece**

CONTENTS: 1 x holesaw, sizes: 22, 29, 35, 44, 51 & 64mm. Arbor 14 - 30mm (8mm shaft). Locking arbor 32 - 152mm (11mm shaft). Hexagon key 4mm.

<b>Item No.</b>	
424043	10



**Holesaw Display - Stocked Stand**

CONTENTS: 1 x holesaw, sizes: 16, 19, 20, 22, 25, 29, 32, 38, 40, 44, 48, 51, 54, 57, 60, 64, 65, 67, 70, 73, 76, 79, 83, 89, 92, 95, 102, 105, 111 & 114mm. 1 x arbor 14-30mm (8mm shaft). 1 x arbor 14-30mm (11mm shaft). 1 x quick release arbor 32-114mm (11mm shaft). 1 x locking arbor 32-114mm (11mm shaft). 1 x SDS arbor 14-30mm. 1 x SDS quick release arbor 32-114mm. 1 x replacement pilot drill (for 424037, 424047 & 424048). 1 x replacement pilot drill (for 424038, 424039 & 424040). 1 x extension drive.

<b>Item No.</b>		
400002	Stock & stand	1



**Downlight Hole Saw Kit - 6 Piece**

CONTENTS: 1 x holesaw, sizes: 65, 70, 76 & 83mm. Quick release arbor 32 - 114mm (11mm shaft). Hexagon key 4mm.

<b>Item No.</b>	
424046	10



## Sheet Steel Holesaws

Tooth configuration optimised for the fast cutting of sheet steel. Cuts sheet steel faster than standard holesaws. 8 teeth per inch for a smoother cutting action. Cleaner holes with no burring. Premium grade 8% cobalt alloy steel construction for an extended working life. Slimline design reduces frictional heat build up and prevents tooth burn out compatible with impact drills. E6.3 drive system. Flared shoulders prevent overdrilling, avoids damaging inner components of electrical cabinets and junction boxes.

Item No.	Ø	
T3202 016	16mm	10
T3202 020	20mm	10
T3202 022	22mm	10
T3202 025	25mm	10
T3202 032	32mm	10
T3202 038	38mm	10
T3202 040	40mm	10



## Sheet Steel Holesaw Set/3

Tooth configuration optimised for the fast cutting of sheet steel. Cuts sheet steel faster than standard holesaws. 8 teeth per inch for a smoother cutting action. Cleaner holes with no burring. Premium grade 8% cobalt alloy steel construction for an extended working life. Slimline design reduces frictional heat build up and prevents tooth burn out. Compatible with impact drills. E6.3 drive system. Flared shoulders prevent overdrilling, avoids damaging inner components of electrical cabinets and junction boxes. CONTENTS: 20, 25 & 32mm.

Item No.		
T3213	Set of 3	3



## Sheet Steel Holesaw Display

CONTENTS: 2 x 16mm, 2 x 20mm, 2x 22mm, 2 x 25mm, 2 x 32mm & 2 x 28mm.

Item No.		
T3202R	Stock and backing card	1



## TCT Hole Saws

Tungsten Carbide Tip (TCT) for exceptional cutting performance across mild and stainless steel, cast iron and copper up to a 12mm thickness. 3-point variable cutting edge for maximum contact whilst minimising heat build-up. High tension spring for rapid slug ejection.

Item No.		Ø	
T3203 016	16mm	12mm	6
T3203 020	20mm	12mm	6
T3203 022	22mm	12mm	6
T3203 025	25mm	12mm	6
T3203 032	32mm	12mm	6
T3203 038	38mm	12mm	6
T3203 040	40mm	12mm	6

## Arbors & Accessories



## TCT HoleSaw Pilot Bit & Spring (3pc)

HSS pilot bit for C.K TCT hole saws. 6.0mm diameter.

Item No.		
T3218	6.0mm	6



## Pilot Drill Assembly

Replacement pilot drill for C.K Holesaws T3202.

Item No.	
T3212	20





### Hole Enlarging Adaptor

Allows nesting of one holesaw inside another for concentric enlarging of existing holes. Double threaded to accept any size of holesaw.

Item No.		
T3216		6



### Quick Change Arbor

Rapid Release System: Enables fast and tool free holesaw changeover. Universal Fitting: Compatible with most brands of holesaws. Suitable for holesaws from: 16 - 152mm.

Item No.		
T3224		Set
T3225		3 x <30mm adaptor
T3225 2		3 x >32mm adaptor



### Locking Holesaw Arbor

For use with holesaws from 32mm - 152mm. Supplied with replaceable 1/4" HSS pilot drill.

Item No.		
424040	11mm (7/16")	10



### Quick Release SDS+ Arbor

Quick-release mechanism for fast holesaw interchange. For use with holesaws from 32 - 152mm. Fixing pins are spring loaded for easy withdrawal making holesaw changes fast and efficient. SDS-Plus drive shaft. With replaceable 1/4" HSS pilot drill.

Item No.			
424048	11mm (7/16")	SDS-Plus	10



### Quick Release Arbor

Quick-release mechanism for fast holesaw interchange. For use with holesaws from 32 - 152mm. Fixing pins are spring loaded for easy withdrawal making holesaw changes fast and efficient. 11mm hexagonal drive shaft. With replaceable 1/4" HSS pilot drill.

Item No.		
424039	11mm (7/16")	10



### SDS+ Holesaw Arbor

For use with holesaws up to 30mm. Supplied with replaceable 1/4" HSS pilot drill. SDS Plus drive shaft.

Item No.			
424047	8mm (5/16")	SDS-Plus	10



### Holesaw Arbor

For use with holesaws up to 30mm. Supplied with replaceable 1/4" HSS pilot drill.

Item No.		
424037	8mm (5/16")	10
424038	11mm (7/16")	10



### Replacement Arbor Pilot Bit

Replacement HSS pilot drill bit for holesaw arbors.

Item No.		
424041	424037, 424047 & 424048	10
424042	424038, 424039, 424040, T3214 & T3224	10




### Holesaw Extension Bar

For use with all 11mm hexagonal shaft arbors.

Item No.			
424049	11mm (7/16")	300mm	10

## Impact screwdriver bits

1. Manufactured from specially formulated V8 steel alloy for extreme toughness.
2. Featuring torsion control technology to withstand the stresses of high torque applications.
3. C.K. Blue Steel Impact Bits provide a vastly extended working life.



Torsion Control  
Technology.




### Blue Steel Impact Bits







#### Blue Steel Impact Bits - PZ 25mm

Item No.				
T4560 PZ1	PZ1	25mm	Loose	10
T4560 PZ2	PZ2	25mm	Loose	10
T4560 PZ3	PZ3	25mm	Loose	10
T4560 PZ1D	PZ1	25mm	Triple Pack	20
T4560 PZ2D	PZ2	25mm	Triple Pack	20
T4560 PZ3D	PZ3	25mm	Triple Pack	20




#### Blue Steel Impact Bits - PZ 50mm

Item No.				
T4560 PZ1L	PZ1	50mm	Loose	10
T4560 PZ2L	PZ2	50mm	Loose	10
T4560 PZ1LD	PZ1	50mm	Triple Pack	20
T4560 PZ2LD	PZ2	50mm	Triple Pack	20
T4560 PZ3LD	PZ3	50mm	Triple Pack	20



**Blue Steel Impact Bits - PH 25mm**

Item No.				
T4560 PH1	PH1	25mm	Loose	10
T4560 PH2	PH2	25mm	Loose	10
T4560 PH3	PH3	25mm	Loose	10
T4560 PH2D	PH2	25mm	Triple Pack	20
T4560 PH2D15	PH2	25mm	Set of 15	



**Blue Steel Impact Bits - PH 50mm**

Item No.				
T4560 PH2L	PH2	50mm	Loose	10
T4560 PH2LD	PH2	50mm	Triple Pack	20
T4560 PH2LD10	PH3	50mm	Set of 10	



**Blue Steel Impact Bits - SL 25mm**

Item No.				
T4560 SL45	4.5mm	25mm	Loose	10
T4560 SL55	5.5mm	25mm	Loose	10
T4560 SL65	6.5mm	25mm	Loose	10



**Blue Steel Impact Bits - TX 25mm**

Item No.				
T4560 TX05	TX05	25mm	Loose	10
T4560 TX06	TX06	25mm	Loose	10
T4560 TX07	TX07	25mm	Loose	10
T4560 TX08	TX08	25mm	Loose	10
T4560 TX09	TX09	25mm	Loose	10
T4560 TX10	TX10	25mm	Loose	10
T4560 TX15	TX15	25mm	Loose	10
T4560 TX20	TX20	25mm	Loose	10
T4560 TX25	TX25	25mm	Loose	10
T4560 TX27	TX27	25mm	Loose	10
T4560 TX30	TX30	25mm	Loose	10
T4560 TX40	TX40	25mm	Loose	10
T4560 TX30D15	TX30	25mm	Set of 15	



**Blue Steel Impact Bits - TX Tamperproof**

Item No.				
T4560 TXTP10	TX10	25mm	Loose	10
T4560 TXTP15	TX15	25mm	Loose	10
T4560 TXTP20	TX20	25mm	Loose	10
T4560 TXTP25	TX25	25mm	Loose	10
T4560 TXTP30	TX30	25mm	Loose	10





## Blue Steel Impact Bits - Hex

Item No.	⊙	↔	i	📦
T4560 HEX25	2.5mm	25mm	Loose	10
T4560 HEX30	3.0mm	25mm	Loose	10
T4560 HEX40	4.0mm	25mm	Loose	10
T4560 HEX50	5.0mm	25mm	Loose	10
T4560 HEX60	6.0mm	25mm	Loose	10



## Blue Steel Impact Bits CBOX

Item No.	↔	i	📦
T4560 PZ2D15CS	W:220 x H:880 x D:115mm	Must be ordered in multiples of 12	12



## Blue Steel Impact Bits - Robertson

Item No.	⊙	↔	i	📦
T4560 ROB1	ROB1	25mm	Loose	10
T4560 ROB2	ROB2	25mm	Loose	10
T4560 ROB3	ROB3	25mm	Loose	10



## Blue Steel Impact Bits Set/10 - PZ/PH

Item No.	i	↔	📦
T4510	Set of 10	25mm	20



## Blue Steel Impact Bits Trade Pack

Item No.	⊙	↔	i	📦
T4560 PZ2D15	PZ2	25mm	Set of 15	12
T4560 PZ3D15	PZ3	25mm	Set of 15	
T4560 PZ2LD10	PZ2	50mm	Set of 10	12
T4560 PZ3LD10	PZ3	50mm	Set of 10	



## Blue Steel Impact Bits Set/6 - PZ

Item No.	i	↔	📦
T4511	Set of 6	50mm	20



**Blue Steel Impact Bits Set/6 - PH**

Item No.	i	↔	📦
T4512	Set of 6	50mm	20



**Blue Steel Impact Bits Set/6 - TX**

Item No.	i	↔	📦
T4513	Set of 6	50mm	20

**Screwdriver Bits**



**Roofing Bolt Driver**

Unique 4 blade design with optimised geometry for a perfect fit on roofing bolts. Stronghold magnet securely retains bolt for quicker alignment and fix. Impact rated S2 Steel with 6.35mm Hex Shank.

Item No.	↔	📦
T4561	75mm	6



**S2 Steel Modulo Bits**

Premium quality chrome vanadium steel for exceptional strength & durability. Precision machined tip for an exact screw fit & damage free screwdriving. Drive: E6.3.

Item No.	+	↔	i	📦
T4545 1	MOD 1	50mm	Loose	20
T4545 2	MOD 2	50mm	Loose	20
422001	MOD 1 & 2	50mm	Card/2	10



**Screwdriver Bits - PZ Long**

Premium quality chrome vanadium steel. Precision machined for high performance screwdriving. Featuring grip tip anti cam out ribs - designed to positively engage with the screw head and reduce the risk of slip and cam out.

Item No.	↔	+	i	📦
T4556 1	50mm	PZ1	Loose	10
T4556-1T	50mm	PZ1	Card/2	25



**Screwdriver Bits - PH Long**

Premium quality chrome vanadium steel. Precision machined for high performance screwdriving. Featuring grip tip anti cam out ribs - designed to positively engage with the screw head and reduce the risk of slip and cam out.

Item No.	↔	+	i	📦
T4555 2	50mm	PH2	Loose	10



**Screwdriver Bits - Slotted**

Premium quality chrome vanadium steel. Precision machined for high performance screwdriving. Featuring grip tip anti cam out ribs - designed to positively engage with the screw head and reduce the risk of slip and cam out.

Item No.	↔	○	i	📦
T4550-0645T	25mm	0.6 x 4.5mm	Card/2	25
T4550 0855	25mm	0.8 x 5.5mm	Loose	10
T4550-0855T	25mm	0.8 x 5.5mm	Card/2	25
T4550-1055T	25mm	1.0 x 5.5mm	Card/2	25
T4550-1265T	25mm	1.2 x 6.5mm	Card/2	25



## Screwdriver Bits - Torx

Premium quality chrome vanadium steel. Precision machined for high performance screwdriving.

Item No.	Length	Tip	Info	Box
T4557 05	25mm	TX05	Loose	10
T4557 07	25mm	TX07	Loose	10
T4557 08	25mm	TX08	Loose	10
T4557 09	25mm	TX09	Loose	10
T4557 40	25mm	TX40	Loose	10
T4557-05T	25mm	TX05	Card/2	25
T4557-06T	25mm	TX06	Card/2	25
T4557-07T	25mm	TX07	Card/2	25
T4557-08T	25mm	TX08	Card/2	25
T4557-09T	25mm	TX09	Card/2	25
T4557-10T	25mm	TX10	Card/2	25
T4557-15T	25mm	TX15	Card/2	25
T4557T 15	25mm	TX15	Tamperproof - Loose	10
T4557T 20	25mm	TX20	Tamperproof - Loose	10
T4557T 30	25mm	TX30	Tamperproof - Loose	10
T4557T-15T	25mm	TX15	Tamperproof - Card/2	25



## Screwdriver Bits - Hex

Premium quality chrome vanadium steel. Precision machined for high performance screwdriving.

Item No.	Length	Tip	Info	Box
T4554-3T	25mm	3.0mm	Card/2	25
T4554-4T	25mm	4.0mm	Card/2	25
T4554-5T	25mm	5.0mm	Card/2	25
T4554-6T	25mm	6.0mm	Card/2	25



## TiN Screwdriver Bits - PZ Long

Premium quality chrome vanadium steel, titanium nitride coated for the ultimate wear resistance. Precision machined for high performance screwdriving. Featuring grip tip anti cam out ribs - designed to positively engage with the screw head and reduce the risk of slip and cam out.

Item No.	Length	Tip	Info	Box
T4556TIN-1T	50mm	PZ1	Card/2	20
T4556TIN-2T	50mm	PZ2	Card/2	20



## TiN Screwdriver Bits - PH Long

Premium quality chrome vanadium steel, titanium nitride coated for the ultimate wear resistance. Precision machined for high performance screwdriving. Featuring grip tip anti cam out ribs - designed to positively engage with the screw head and reduce the risk of slip and cam out.

Item No.	Length	Tip	Info	Box
T4555TIN 1T	50mm	PH1	Card/2	20



## TiN Double Ended Bits - PH/Slotted

Premium quality chrome vanadium steel, titanium nitride coated for the ultimate wear resistance. Precision machined for high performance screwdriving. Featuring grip tip anti cam out ribs - designed to positively engage with the screw head and reduce the risk of slip and cam out.

Item No.	Length	Tip 1	Tip 2	Info	Box
T4580TIN-1T	50mm	PH1	4mm	Card/2	20
T4580TIN-2T	50mm	PH2	7mm	Card/2	20



## TiN Screwdriver Bits - Torx

Premium quality chrome vanadium steel, titanium nitride coated for the ultimate wear resistance. Precision machined tip for an exact screw fit & damage free screwdriving.

Item No.	Tip	Length	Info	Box
T4557TIN 10	TX10	25mm	Loose	300
T4557TIN 15	TX15	25mm	Loose	300
T4557TIN 20	TX20	25mm	Loose	300
T4557TIN 25	TX25	25mm	Loose	300
T4557TIN 30	TX30	25mm	Loose	300
T4557TIN 40	TX40	25mm	Loose	300
T4557TIN-10T	TX10	25mm	Card/2	20
T4557TIN-15T	TX15	25mm	Card/2	20
T4557TIN-40T	TX40	25mm	Card/2	20





**Screwdriver Bit Clip Set/7 - PZ**

Premium quality S2 alloy steel for exceptional strength & durability. Precision machined tip for an exact fit & damage free screwing. CONTENTS: 1 x PZ1 / 4 x PZ2 / 1 x PZ3 / 1 x bit holder.

<b>Item No.</b>	<b>i</b>		
T4517	Set of 7	25mm	12



**Screwdriver Bit Clip Set/31**

Premium quality S2 alloy steel for exceptional strength & durability. Precision machined tip for an exact fit & damage free screwing. CONTENTS: 1xPZ1 / 4xPZ2 / 1xPZ3 2xTX10 / 4xTX15 / 4xTX20 / 2xTX25 / 2xTX30 / 1xTX40 1xPH1 / 2xPH2 1xSL4.0mm / 1xSL5.5mm / 1xSL6.5mm 1x hex 4.0mm / 1x hex 5.0mm / 1x hex 6.0mm 1 x bit holder.

<b>Item No.</b>	<b>i</b>		
T4502	Set of 31	25mm	6



**Screwdriver Bit Clip Set/7 - PH**

Premium quality S2 alloy steel for exceptional strength & durability. Precision machined tip for an exact fit & damage free screwing. CONTENTS: 1 x PH1 / 4 x PH2 / 1 x PH3 / 1 x bit holder.

<b>Item No.</b>	<b>i</b>		
T4518	Set of 7	25mm	12



**Screwdriver Bit Box Set/7**

Made from high quality chrome vanadium steel. Hardened and tempered for long performance. Precision machined tips for an exact screw fit & damage free screwdriving. CONTENTS: Screwdriver bit holder; Bits: Slotted, sizes: 5.5 & 6.5mm; Pozidriv, sizes: 1 & 2; Phillips, sizes: 1 & 2.

<b>Item No.</b>	<b>i</b>		
T4583C	Set of 7	25mm	5



**Screwdriver Bit Clip Set/7 - TX**

Premium quality S2 alloy steel for exceptional strength & durability. Precision machined tip for an exact fit & damage free screwing. CONTENTS: TX10, TX15, TX20, TX25, TX30, TX40 & bit holder.

<b>Item No.</b>	<b>i</b>		
T4501	Set of 7	25mm	12



**TiN Screwdriver Bit Set/7 - PZ**

Premium quality chrome vanadium steel, titanium nitride coated for the ultimate wear resistance. Precision machined tip for an exact screw fit & damage free screwdriving. CONTENTS: 1 x Bit holder, Bits: 1 x PZ 1 and PZ 3, 4 x PZ 2.

<b>Item No.</b>	<b>i</b>		
T4569TINC	Set of 7	25mm	20



## Screwdriver Bits Set/8 - PZ/PH

Bits made from special S2 alloy steel. Precision machined tips for an exact screw fit & damage free screwdriving. CONTENTS: Pozidriv, sizes: 0, 1, 2 & 3; Phillips, sizes: 0, 1, 2 & 3.


<b>Item No.</b>	
T4522	6



## Screwdriver Bits Set/8 - Hex

Bits made from special S2 alloy steel. Precision machined tips for an exact screw fit & damage free screwdriving. CONTENTS: 1.5, 2, 2.5, 3, 4, 5, 5.5 & 6mm.

<b>Item No.</b>	
T4524	6



## Screwdriver Bits Set/8 - Slotted

Bits made from special S2 alloy steel. Precision machined tips for an exact screw fit & damage free screwdriving. CONTENTS: 3, 4, 4.5, 5, 5.5, 6, 7, 8 & 9mm.

<b>Item No.</b>	
T4521	6



## Screwdriver Bits Set/8 - Hex Tamperproof

Bits made from special S2 alloy steel. Precision machined tips for an exact screw fit & damage free screwdriving. CONTENTS: 2, 2.5, 3, 4, 5, 5.5, 6 & 7mm.

<b>Item No.</b>	
T4528	6



## Screwdriver Bits Set/8 - Torx

Bits made from special S2 alloy steel. Precision machined tips for an exact screw fit & damage free screwdriving. CONTENTS: TX 8, 10, 15, 20, 25, 27, 30 & 40.

<b>Item No.</b>	
T4523	6



## Screwdriver Bits Set/8 - Torx Tamperproof

Bits made from special S2 alloy steel. Precision machined tips for an exact screw fit & damage free screwdriving. CONTENTS: TX 8, 10, 15, 20, 25, 27, 30 & 40.

<b>Item No.</b>	
T4527	6



## Screwdriver Bits Set/33 - Mixed

Bits made from special S2 alloy steel. Precision machined tips for an exact screw fit & damage free screwdriving. CONTENTS: Screwdriver bit holder, bits, slotted, sizes: 3, 4, 4.5, 5, 5.5, 6, 7, 8 & 9mm; Pozidriv, sizes: 0, 1, 2 & 3; Phillips, sizes: 0, 1, 2, & 3; TX, sizes: 8, 10, 15, 20, 25, 27, 30 & 40; Hexagon, sizes: 1.5, 2, 2.5, 3, 4, 5, 5.5 & 6mm.

<b>Item No.</b>	
T4520	6



### Screwdriver Bits Set/10 - Long

Bits made from special S2 alloy steel. Precision machined tips for an exact screw fit & damage free screwdriving. CONTENTS: Slotted: 4, 5 & 7mm; Pozidriv: 1, 2 & 3; Phillips: 1, 2 & 3; TX: 15 & 20.

Item No.		
T4525	100mm	6



### Damaged Screw Removers

Designed for the fast removal of damaged non hardened screws. Hexagon shaft for use with reversible drill. Pack CONTENTS: two sizes for screws 6 - 10 & 12 - 14mm.


Item No.		
422003		12
T3060-CLIP	Clipstrip x 6	1
T3060-CBOX	Counterbox x 12	1



### Screwdriver Bits Set/41

Premium quality S2 alloy steel for exceptional strength & durability. Precision machined tip for an exact fit & damage free screwing. CONTENTS: 2 x PH1, 4 x PH2, 2 x PH3, 4 x PZ1, 8 x PZ2, 4 x PZ3; 2 x 4.0mm, 2 x 5.5mm, 2 x 6.0mm, 2 x 8.0mm (slotted); 1 x TX15, 1 x TX20, 1 x TX25, 1 x TX30; 1 x 3.0mm, 1 x 4.0mm, 1 x 5.0mm, 1 x 6.0mm (hexagon); 1 x bit holder.

Item No.			
T4509	Set of 41	25mm	6



### Screw Extractor Set/5

Hardened chrome vanadium steel. Left hand threaded for extracting broken studs and screws.

Item No.	
T3062 01	5



### Security Bits Set/41

Premium quality S2 alloy steel for exceptional strength & durability. Precision machined tip for an exact fit & damage free screwing. In metal box for convenience. CONTENTS: Phillips: 1 x PH0 / 1 x PH1 / 3 x PH2 / 1 x PH, Pozidriv: 1 x PZ0 / 1 x PZ1 / 1 x PZ2 / 1 x PZ, Slotted: 1 x 4.0mm / 1 x 5.0mm / 1 x 6.0mm / 1 x 8.0mm, Multitooth: 1 x size 4 / 1 x size 5 / 1 x size 6 / 1 x size 8, Spanner: 1 x size 4 / 1 x size 6 / 1 x size 8 / 1 x size 10, Torque-Set: 1 x size 6 / 1 x size 8 / 1 x size 10, Tamper-TX: 1 x TX8 / 1 x TX10 / 1 x TX15 / 1 x TX20 / 1 x TX25 / 1 x TX27 / 1 x TX30 / 1 x TX40, Tri-Wing: 1 x size 1 / 1 x size 2 / 1 x size 3 / 1 x size, 1 x bit holder.

Item No.			
T4508	Set of 41	25mm	6




### Screwdriver Bits CBOX - PZ

Premium quality chrome vanadium steel, titanium nitride coated for the ultimate wear resistance. Precision machined for high performance screwdriving. Featuring grip tip anti cam out ribs - designed to positively engage with the screw head and reduce the risk of slip and cam out.

Item No.			
T4562-2CB	25mm	PZ2	1





## TiN Screwdriver Bits CBOX - PZ

Premium quality chrome vanadium steel, titanium nitride coated for the ultimate wear resistance. Precision machined for high performance screwdriving. Featuring grip tip anti cam out ribs - designed to positively engage with the screw head and reduce the risk of slip and cam out.

Item No.			
T4562TIN-215	25mm	PZ2	1
T4562TIN-2CB	25mm	PZ2	1

## Screwdriver Bit Holders




### Nut Driver - Magnetic

For fast and effective driving of hex head screw fixings. Forged alloy steel for strength and durability. Colour coded for convenience.

DIN 3126 E6.3 & ISO 1173

Item No.			
T4598	8mm	Loose	10
T4598C 08	8mm	Carded	10



### Magnetic Bit Holders

Strong & corrosion resistant stainless steel sleeve. Magnetic base and c-ring securely retains the bit in place.

DIN 3126 E6.3 & ISO 1173

Item No.		
T4570	60mm	10
T4570 100	100mm	10
T4570 200	200mm	10



### SDS+ Bit Holder

Stainless steel - strong & corrosion resistant. Magnetic base for bit retention. SDS Plus drive.

DIN 7427

Item No.		
T4564SDSC	74mm	10



### Locking Bit Holder

Locking mechanism securely retains bit in place. Quick release mechanism allows fast & convenient bit changes.

DIN 3126 E6.3 & ISO 1173

Item No.		
T4564D	60mm	10



### Screw Grip Magnetic Bit Holder

Magnetic base retains bit in place. Magnetic collar holds the screw in place.

DIN 3126 E6.3 & ISO 1173

Item No.		
T4567D	70mm	10



### Pivot Joint Bit Holder

Magnetic base securely retains the bit in place. Pivoting head for when straight line access isn't possible. Lockable collar for use as a straight line bit holder. E6.3 drive.

Item No.		
T4504	100mm	25



**Keyless Chuck Adaptor**

1/4" hexagon to 3 jaw chuck converter. E6.3 drive. Keyless chuck. Fits up to 6mm drill bits.

<b>Item No.</b>		
T2463	6mm	6



**Quick Change Chuck System**

Bits made from special S2 alloy steel. Precision machined tips for an exact screw fit & damage free screwdriving. CONTENTS: Screwdriver bit holder, Quick change chuck, Slotted, sizes: 4, 5, 6, & 7mm; Pozidriv, sizes: 1, 2 & 3; Phillips, sizes: 1, 2 & 3; TX, sizes: 10, 15, 20, 25, 30 & 40; Hexagon, sizes: 3, 4, 5, & 6mm. 2 x drill/driver bits, sizes: 2.5mm x Pozidriv1 & 3.0mm x Pozidriv1 x drill/driver bit, size: 4.0mm x Pozidriv.

<b>Item No.</b>	
T4519	6



**Magnetic Nut Drivers Set/7**

For fast and effective driving of hex head screw fixings. Forged alloy steel for strength and durability. Colour coded for convenience. CONTENTS: 7 / 8 / 10 / 11 / 13mm - 1/4" & 3/8". DIN 3126 E6.3 and ISO 1173

<b>Item No.</b>		
T4514	Set of 7	14

**Multitool Blades**



**Multitool Blade - Box Cutter**

Optimized curved teeth design for efficient cutting action. Integrated double-socket guide for quick alignment and cut. HCS construction for strength and durability. Universal quick change fitment covers most brands of oscillating tool (not compatible with Starlock). Multi-material: for use on plasterboard, wood and plastic.

<b>Item No.</b>	
T0880	75 x 75 x 32mm
T0880CBOX	



**Multitool Blade - Carbide**

Carbide Construction for extreme cutting performance. Cuts ferrous metals, hardened screws, bolts, nails, and abrasive materials. Universal quick change fitment covers most brands of oscillating tool (not compatible with Starlock).

<b>Item No.</b>		
T0877	34 x 40mm	10



**Multitool Blade - Scraper**


Stainless steel construction for durability and easy cleaning. Removes grout glue, paint, tile and wall adhesives with ease. Universal quick change fitment covers most brands of oscillating tool (not compatible with Starlock).

<b>Item No.</b>		
T0878	52 x 38mm	10



## Multitool Blade - 2 Piece Set


Strong and durable multitools to be used with a range of materials including; thin steel, wood, wood with nails, plastics and non ferrous metals.

Item Number		
T0875	34 x 40mm	1
T0876	28.5 x 57mm	1



## Multitool Blade - 5 Piece Set

Strong and durable multitools to be used with a range of materials including; thin steel, wood, wood with nails, plastics and non ferrous metals. CONTENTS: 2 x 34mm x 40 wood HCS, 1 x 34mm x 40 BIM, 1 x 80mm diameter BIM, 1 x 65mm x 42 wood BIM M2 (Japanese teeth).

Item No.	
T0870	1

## Jigsaw Blades



### Straight Cut Blade - Metal

Thin metal, straight cuts.

Item No.				BOSCH	
T0865A	50mm	2.5mm	1.5 - 3mm	T118A	5



### Coarse Cut Blade - Wood




Wood, fast coarse cuts.

Item No.				BOSCH	
T0865B	75mm	2.5mm	5 - 60mm	T111C	5



### Fine Cut Blade - Wood

Wood, precise cuts.

Item No.				BOSCH	
T0865C	75mm	2.5mm	4 - 30mm	T101B	5



### Straight Cut Blade - Thick Metal

Thicker metal, straight cuts.

Item No.				BOSCH	
T0865H	50mm	1.2mm	3 - 60mm	T118B	5



### Fast Cut Blade - Wood

Wood, fast clean cuts.

Item No.				BOSCH	
T0865L	75mm	4mm	6 - 60mm	T101D	5





**Fast Fine Cut Blade - Wood**

Wood, fast extra clean cuts.

Item No.				
T0865P	95mm	4mm	8 - 75mm	5



**Fine Cut Blade - Metal**

Metal & sandwich materials.

Item No.				BOSCH	
T0865Y	110mm	1.2mm	1.5 - 3mm	T318A	5



**Down Cut Blade - Laminate**

Wood laminates, down cut.

Item No.				BOSCH	
T0865R	75mm	2.5mm	4 - 30mm	T101BR	5



**Curved Cut Blade - Wood**

Wood, extra clean curved cuts.


Item No.				BOSCH	
T0865T	75mm	2.5mm	4 - 30mm	T244D	5



**Straight Cut Blade - Universal**

Universal. For straight cuts in soft & hardwood, wood with nails, steel, aluminium, laminate, plastics and particle board.

Item No.				
T0865W	110mm	1.8-2.5mm	3 - 100mm	5





**Double Cut Blade - Wood**

Wood, fast double cut.

Item No.				
T0865X	75mm	2.0mm	3 - 60mm	5

**Reciprocating Blades**



**Reciprocating Saw Blades**

Multi-purpose reciprocating saw blades cut metal, wood, plastic and plasterboard. Universal fitting - Compatible with T0820 and all reciprocating saws.

Item No.		tpi
T0821	150mm	6
T0822	150mm	18
T0823	150mm	24





# Building & Decorating

<b>Bricklaying</b>	<b>132</b>
<b>Plastering</b>	<b>133</b>
<b>Trowels</b>	<b>134</b>
<b>Tiling &amp; Glazing</b>	<b>136</b>
<b>Paddles &amp; Mixers</b>	<b>137</b>
<b>Scrapers &amp; Filling Knives</b>	<b>137</b>
<b>Plumbing</b>	<b>138</b>
<b>Glue Guns</b>	<b>138</b>
<b>Staple Guns</b>	<b>139</b>
<b>Bradawls</b>	<b>139</b>



## Bricklaying



### Broad Heel Brick Trowel - Soft Grip

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Patented soft grip handle with finger guard for comfort & control.

<b>Item No.</b>		
T529510	255mm (10")	3



### Philadelphia Brick Trowel - Wood Handle

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Traditional wooden handle.

<b>Item No.</b>		
T527111	275mm (11")	1



### Philadelphia Brick Trowel - Soft Grip

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Patented soft grip handle with finger guard for comfort & control.

<b>Item No.</b>		
T529311	280mm (11")	3



### Philadelphia Brick Trowel - Stainless Steel

Stainless steel blade for corrosion protection & low maintenance. Heavy duty tang welded to blade for strength & durability. Patented soft grip handle with finger guard for comfort & control.

<b>Item No.</b>		
T524111	280mm (11")	3



### Broad Heel Brick Trowel - Wood Handle

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Traditional wooden handle.

<b>Item No.</b>		
T527010	250mm (10")	6
T527011	275mm (11")	3



### Brick Jointer

Fully hardened & tempered carbon steel for wear resistance.



<b>Item No.</b>		
T5198	13 x 16mm (1/2 x 5/8")	12

Plastering



**Finishing Trowel - Soft Grip**

High carbon steel blade, hardened & tempered for the optimum balance of strength & flexibility. Welded & riveted tang to blade joint for outstanding durability. Soft grip handle for comfort & control.

Item No.		
T5298	280 x 120mm (11 x 4 3/4")	6



**Plasterers Hawk**


Lightweight aluminium blade with grooved, non-slip surface.

Item No.		
T5069	300 x 300mm (12 x 12")	3



**Finishing Trowel - Wood Handle**




High carbon steel blade, hardened & tempered for the optimum balance of strength & flexibility. Welded & riveted tang to blade joint for outstanding durability. Traditional wooden handle.

Item No.		
T5068	280 x 120mm (11 x 4 3/4")	6



**Leaf & Square Tool**



Solid forged steel blade, hardened, tempered & ground for the optimum balance of flexibility & strength.

Item No.			
T5091 50	200mm (8")	12mm (1/2")	3



**Skimmer Floats**




Lightweight, moulded foam polymer with fine chequered working face - durable & non-warping.

Item No.		
T5172	280 x 140mm	1
T5172 18	320 x 180mm	1



**Trowel & Square Tools**

Solid forged steel blade, hardened, tempered & ground for the optimum balance of flexibility & strength.

Item No.			
T5093 50	265mm (10 1/2")	12mm (1/2")	3
T5093 62	265mm (10 1/2")	16mm (5/8")	3
T5093 75	265mm (10 1/2")	19mm (3/4")	3

## Trowels



### Pointing Trowel - Soft Grip

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Patented soft grip handle with finger guard for comfort & control.

Item No.		
T529606	150mm (6")	3



### Gauging Trowel - Soft Grip

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Patented soft grip handle with finger guard for comfort & control.

Item No.		
T529207	180mm (7")	6



### Finger Trowel - Soft Grip

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Patented soft grip handle with finger guard for comfort & control.

Item No.		
T529750	175 x 13mm (7 x 1/2")	3



### Pointing Trowels - Wood Handle

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Traditional wooden handle.

Item No.		
T5060 4	100mm (4")	3
T5060 5	125mm (5")	3
T5060 6	150mm (6")	6



### Gauging Trowel - Wood Handle

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Traditional wooden handle.

Item No.		
T527207	175mm (7")	3




### Finger Trowels - Wood Handle

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Traditional wooden handle.

Item No.			
T5073 1	175mm (7")	13mm (1/2")	3
T5073 37	175mm (7")	10mm (3/8")	3
T5073 50	175mm (7")	13mm (1/2")	3
T5073 62	175mm (7")	16mm (5/8")	3
T5073 75	175mm (7")	19mm (3/4")	3
T5073 99	175mm (7")	25mm (1")	3





**Margin Trowel**

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Traditional wooden handle.

<b>Item No.</b>		
T5273	125mm (5")	3



**Harling Trowel**

Heavy gauge steel blade with tang welded to blade for strength & durability. Traditional wooden handle.

<b>Item No.</b>		
T5097	165 x 165mm (6 1/2 x 6 1/2")	2



**Flooring Trowel**

High carbon steel blade. Hardened & tempered for the optimum balance of strength & flexibility. Welded & riveted tang to blade joint for outstanding durability. Traditional wooden handle.

<b>Item No.</b>		
T5264	405 x 115mm (16 x 4 1/2")	3



**Pointing Trowel - Stainless Steel**

Stainless steel blade for corrosion protection & low maintenance. Heavy duty tang welded to blade for strength & durability. Patented soft grip handle with finger guard for comfort & control.

<b>Item No.</b>		
T524306	150mm (6")	6



**Edging Trowel**

High carbon steel blade. Hardened & taper ground for the optimum balance of strength & flexibility. Heavy duty tang welded to blade for strength & durability. Traditional wooden handle.

<b>Item No.</b>		
T5274	280 x 115mm (11 x 4 1/2")	3



**Gauging Trowel - Stainless Steel**

Stainless steel blade for corrosion protection & low maintenance. Heavy duty tang welded to blade for strength & durability. Patented soft grip handle with finger guard for comfort & control.

<b>Item No.</b>		
T524207	175mm (7")	3

## Tiling & Glazing



### Tile Scriber

Tungsten carbide tipped, suitable for tiles, metal and glass. Pocket clip.

**Item No.**



T1531

12



### Adhesive Trowels

Polished carbon steel blade. Comfortable soft grip handle.

**Item No.**

T5170 1

T5170 2



### Grouting Sponge

Lightweight, polymer handle bonded to a sponge pad - suitable for washing down grout.

**Item No.**



T5173

280 x 140mm (11 x 5 1/2")

1



### Grouting Float

Lightweight, polymer handle bonded to a dense rubber pad - suitable for grout application.

**Item No.**



T5174

280 x 140mm (11 x 5 1/2")

1



### Glass Cutter


High quality with 6 premium quality tungsten carbide blades in turret head. Oiled felt washer for constant lubrication. Heavy nickel plated head for protection.

**Item No.**



T5087

6



### Suction Lifter - 60kg

Lever action, double suction cup designed to lift up to 60Kg. Heavy duty construction for strength & durability.

**Item No.**



T5082

320mm (12 3/4")

60kg


1

**Paddles & Mixers**



**Power Paint Mixer**

Nickel plated steel construction for strength & easy cleaning. Suitable for use with electric drills at speeds between 200 - 700rpm.



Item No.		
T1881	420mm (16 1/2")	2
T1882	620mm (25")	2

**Scrapers & Filling Knives**



**Scrapers / Filling Knives**



Tapered ground spring steel blade for strength & flexibility. Plastic wipe clean handles with hanging hole for convenient storage.

Item No.		
T5070A 040	40mm (1 1/2")	6
T5070A 050	50mm (2")	6
T5070A 070	70mm (2 3/4")	6
T5070A 100	100mm (4")	6



**Scrapers**



High quality, taper ground spring steel blade for strength. Walnut handle.

Item No.		
T5075 1	25mm (1")	3
T5075 2	50mm (2")	3
T5075 3	75mm (3")	3
T5075 4	100mm (4")	3



**Filling Knife**


High quality, thin, taper ground spring steel blade for the optimum balance of strength & flexibility required for filling. Rosewood handle.

Item No.		
T5077 3	75mm (3")	6



**Putty Knife**

High quality spring steel blade for strength & flexibility. Clip point profile for smoothing & shaping putty. Rosewood handle.

Item No.	
T5076	1



## Plumbing



### Basin Wrench

Adjustable, telescopic wrench with sliding T handle for confined & long reach access. Spring loaded, self adjusting jaws maintain an automatic grip. 180° swivelling head for clockwise or anti-clockwise action. Hardened steel jaws for durability.

Item No.		
T4311	275 - 460mm	6



### Immersion Heater Spanner

One piece steel construction for strength & durability. Zinc plated for corrosion protection. PVC handle for comfort and grip.

Item No.		
T4347	85mm	6



### Stillson Wrench

High quality drop forged steel construction with hardened & tempered jaws for strength & durability. Patented head design for high torque performance. Non slip, durable paint finish for grip and control.

Item No.			
T3735 300	300mm (12")	38mm	8
T3735 350	350mm (14")	55mm	8
T3735 450	450mm (18")	55mm	8
T3735 600	600mm (24")	70mm	4

## Glue Guns



### Glue Gun

Premium quality with high energy heater for fast heating & improved glue flow. Heat insulated nozzle for safety. Integral wire stand for convenience. Glue output of up to 21g/min for fast application. Supplied with two 100 x 11mm general purpose glue sticks.

LDV, RoHS, WEEE

Item No.		
T6215	UK 3 pin plug	6
T6215A	Euro 2 pin plug	6




### Glue Gun Kit

Premium quality with high energy heater for fast heating & improved glue flow. Heat insulated nozzle for safety. Integral wire stand. Glue output of up to 21g/min for fast application. CONTENTS: Glue gun, 12 x glue sticks, size: 200mm.

LDV, RoHS, WEEE

Item No.		
T6216	Euro 2 pin plug	1



**Glue Sticks**

10g Glue Sticks. Diameter: 11mm. Colour: transparent.

Item No.			
T6218 06	100mm	x 6	6
T6218 25	100mm	x 25	6
T6219 025	200mm	x 25	1
T6219 125	200mm	x 125	1



**Staples - Square**

High quality steel staples, galvanised for corrosion protection - to suit C.K 496001 heavy duty staple gun.

Item No.		
496002	10.5 x 8mm	10
496003	10.5 x 10mm	10
496004	10.5 x 12mm	10
496005	10.5 x 14mm	10

**Staple Guns**



**Staple & Nail Gun**

Heavy duty, tough cast aluminium body for strength & durability. Bi-material ergonomic handle for comfort & reduced fatigue. Unique staple loading & clearing mechanism for fast & convenient use. Handle safety locking system prevents accidental operation. Fires staples 6-14mm (interchangeable with Arrow T50 or Rapid 140 6-14mm) & nails (brads) 18 gauge 16mm. Supplied with 200 x 8mm staples.

Item No.	
496001	3


**Bradawls**



**Bradawl - Square**

Hardened steel square spike bradawl with lacquered beech handle and solid brass ferrule.

Item No.			
T4831 2	100mm (4")	85mm (3 1/4")	6



**Bradawl - Round**

Nickel plated hardened steel blade for a long life. Shatterproof ball ended acetate handle for comfort and safety.

Item No.				
T4835	6mm (1/4")	100mm (4")	85mm (3 1/4")	6







# Striking Tools

<b>Hammers</b>	<b>142</b>
<b>Wrecking Tools</b>	<b>144</b>
<b>Chisels</b>	<b>144</b>
<b>Punches</b>	<b>145</b>



## Hammers



### Claw Hammers - Anti-Vibration One Piece

Single piece drop forged high carbon steel head & shaft - hardened & tempered for superior strength & durability. Balanced weight design with energy saving claw geometry for improved performance. Contoured anti-vibe shock absorbing grip system to protect against injury through shock. Polished & lacquered to protect against corrosion.

Item No.		
357001	454g (16oz)	6
357002	568g (20oz)	6



### Engineers Hammer - French Pattern

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Black lacquered to protect against corrosion. Traditional ash shaft for strength.

Item No.		
356002	300g (10 1/2oz)	12
356003	400g (14oz)	12



### Pin Hammer

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Black lacquered to protect against corrosion. Tough hickory shaft for durability. Cross pein for easy starting of small nails & pins.

Item No.		
T4203	114g (4oz)	3



### Electricians Hammer - French Pattern

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Black lacquered to protect against corrosion. Traditional ash shaft for strength.

Item No.		
356001	200g (7oz)	12



### Engineers Hammer - German Pattern

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Black lacquered to protect against corrosion. Traditional ash shaft for strength.

Item No.		
T4227A 0100	100g (3 1/2oz)	12
T4227A 0200	200g (7oz)	12
T4227A 0300	300g (10 1/2oz)	12
T4227A 0500	500g (17 1/2oz)	12
T4227A 1000	1000g (35oz)	6



### Claw Hammers - Anti-Vibration Fibreglass

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Tough fibreglass shaft for strength. Contoured anti-vibe shock absorbing grip system to protect against injury from transmitted shock. Polished and lacquered to protect against corrosion.

Item No.		
357003	454g (16oz)	6
357004	568g (20oz)	6



**Claw Hammers - Hi-Vis**

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Tubular steel shaft - strong & lightweight. Hi-vis handle for increased visibility in low light conditions. Black lacquered to protect against corrosion.

Item No.		
T4229 08	227g (8oz)	6
T4229 16	454g (16oz)	6
T4229 20	568g (20oz)	6



**Club Hammer - Anti-Vibration One Piece**

Single piece drop forged high carbon steel head & shaft - hardened & tempered for superior strength and durability. Contoured anti-vibe shock absorbing grip system to protect against injury from transmitted shock. Polished and lacquered to protect against corrosion.

Item No.		
357005	1361g (3lb)	2



**Club Hammers**

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Black lacquered to protect against corrosion. Tough hickory shaft to withstand high impact applications.

Item No.		
T4219 40	1135g (2 ½lb)	2
T4219 64	1816g (4lb)	2
T4219A 10	1000g (2 ¼lb)	6
T4219A 15	1500g (3 ½lb)	6



**Brick Hammers**

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Accurately ground chisel end for clean cutting. Tubular steel shaft - strong & lightweight.

Item No.		
T4232 16	454g (16oz)	4
T4232 20	568g (20oz)	4



**Mortar Pick**

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Tubular steel shaft - strong & lightweight.

Item No.		
T4234	Chisel and point	6



**Ball Pein Hammer**

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Black lacquered to protect against corrosion. Tough hickory shaft for durability. Ball pein for setting rivets.

Item No.		
T4208H 16	454g (1lb)	3



**Joiners Hammer**

Drop forged high carbon steel head - hardened & tempered for superior strength and durability. Black lacquered to protect against corrosion. Tough hickory shaft for durability. Cross pein for easy starting of small nails & pins.

Item No.		
T4204 08	227g (8oz)	3

## Wrecking Tools



### Japanese Prybar

Hot forged from carbon steel alloy, hardened for strength and durability. 46mm wide tip for precise removal with minimal damage. Flat heel for striking with a hammer.

Item No.	Length
T4312	10"



### Prybar, Nail Puller & Scraper

Forged spring steel for strength and durability. Specially contoured & notched for efficient nail pulling and prying. Sharp angle ground ends for effective chiselling & scraping.

Item No.	Length	Weight
T4310	380mm (15")	6

## Chisels



### Slaters Ripper

Single piece forged spring steel construction for strength & durability. Slim blade design with double sided hooked blades for fast & effective nail cutting.

Item No.	Weight
T5180	1



### Brick Bolster Chisels with Grip

Hand guard for increased comfort & protection from overstrike.  
BS 3066

Item No.	Length	Width	Weight
T3087S 3	230mm (9")	75mm (3")	10
T3087S 4	230mm (9")	100mm (4")	10



### Brick Bolster Chisels

Octagonal shank brick bolster with precision ground cutting edges. Specifically designed for cutting bricks and composite blocks. Powder coated for corrosion protection.  
BS 3066

Item No.	Length	Width	Weight
T3087 3	230mm (9")	75mm (3")	10
T3087 4	230mm (9")	100mm (4")	10



### Electricians Bolster with Grip

Hand guard for increased comfort & protection from overstrike.  
BS 3066

Item No.	Length	Width	Weight
T3086S	225mm (8 3/4")	55mm (2 1/4")	10



### Electricians Bolster Chisel

Octagonal shank electrician's bolster with precision ground cutting edges for long term performance. Ideal for splitting and lifting floorboards, cutting plaster and chasing. Powder coated for corrosion protection.  
BS 3066

Item No.	Length	Width	Weight
T3086	225mm (8 3/4")	55mm (2 1/4")	10





## Plugging Chisel

Angled & grooved cutting edge for the effective removal of mortar & cement.

BS 3066

Item No.			
T3088	250mm (10")	25mm (1")	10



## Cold Chisels

Chisel for cutting small section steel, can also be used on brick and concrete. Hardened steel with powder coating for corrosion protection. Hexagon shaft.

BS 3066

Item No.			
T3383 06	150mm (6")	12mm (1/2")	10
T3383 07	180mm (7")	16mm (5/8")	10
T3383 08	200mm (8")	19mm (3/4")	10
T3383 10	250mm (10")	19mm (3/4")	10
T3383 18	460mm (18")	19mm (3/4")	10
T3383 101	250mm (10")	25mm (1")	10
T3383 12	300mm (12")	25mm (1")	10




## Scutch Chisels

High quality carbon steel, hardened & tempered for strength & durability. Replaceable chisel bits.

BS 3066

Item No.		
406001	25mm (1")	3
406002	38mm (1 1/2")	3



## Scutch Chisel - Spare Bits

10 spare comb bits for scutch chisels.

Item No.			
T4211/1	25mm (1")	Scutch combs	10
T4211/2	25mm (1")	Scutch drives	10
T4211/3	38mm (1 1/2")	Scutch combs	10
T4211/4	38mm (1 1/2")	Scutch drives	10




## Bolster Chisels - Stocked CDU

CONTENTS: 7 x plugging chisels, 7 x electrician's bolster chisels, 6 x bolster chisels, sizes: 75 & 100mm, 3 x bolster chisels with grip, size: 100mm.

Item No.		
T3090LS	Stock & stand	1

## Punches



## Plasterboard Punch

Stepped, special alloy shaft for punching 5, 6 & 7mm wall plug holes - no drilling, no mess. Cone point for punching, scribing and marking plasterboard. Shatterproof acetate handle with a strike-through cap - withstands hammer blows.

Item No.			
T4837	98mm	100mm	6



## Centre Punches

High quality chrome vanadium steel hardened for durability.

Item No.		
T3319	150mm (6")	6
T3326	120mm (4 3/4")	6



## Pin Punches

High quality chrome molybdenum steel hardened for durability. DIN 645

Item No.			
T3328 05	150mm (6")	2mm (5/64")	6
T3328 06	150mm (6")	2.5mm (3/32")	6
T3328 08	150mm (6")	3mm (1/8")	6
T3328 10	150mm (6")	4mm (5/32")	6
T3328 12	150mm (6")	5mm (3/16")	6
T3328 14	150mm (6")	5.5mm (7/32")	6
T3328 16	150mm (6")	6mm (1/4")	6
T3328 20	150mm (6")	8mm (5/16")	6
T3328 24	150mm (6")	10mm (3/8")	6
T3328S	2, 2.5, 3, 4, 5 & 6mm		3



# Sawing, Cutting & Filing

<b>Wood Saws</b>	<b>148</b>
<b>Hacksaws</b>	<b>149</b>
<b>Multisaws</b>	<b>150</b>
<b>Plasterboard Saws</b>	<b>150</b>
<b>Trimming Knives</b>	<b>151</b>
<b>Files &amp; Rasps</b>	<b>152</b>
<b>Wood Chisels</b>	<b>155</b>



## Wood saws

1. The Sabretooth saw range offers the comfort, speed and durability typically only associated with premium priced saws.
2. Featuring triple ground 'turbo cut' hard point teeth for effective cutting of timber, chipboard, plywood and plastics.







## Wood Saws



### Sabretooth Trade Universal Wood Saw





Universal tooth pitch for a wide range of materials. Offset teeth for reduced friction & greater waste removal. 0.85mm premium grade CK5 steel blade for maximum power transfer. 45 & 90° angle guides for ease of marking out. Dual component cushion grip handle for comfort and control. Stay sharp, hard point teeth for an extended working life.

Item No.				
T0840 20	20"	7 TPI / 8 PPI	Supplied in a counterbox when ordered in 10's	10
T0840 22	22"	7 TPI / 8 PPI	Supplied in a counterbox when ordered in 10's	10



### Sabretooth Trade Fine Cut Wood Saw




Universal tooth pitch for a wide range of materials. Offset teeth for reduced friction & greater waste removal. 0.85mm premium grade CK5 steel blade for maximum power transfer. 45 & 90° angle guides for ease of marking out. Dual component cushion grip handle for comfort and control. Stay sharp, hard point teeth for an extended working life.

Item No.				
T0940 22	22"	9 TPI / 10 PPI	Supplied in a counterbox when ordered in 10's	10



### Sabretooth Wood Saw

Triple edge, ultra sharp diamond ground teeth that cut on both the push and the pull. Up to 41% fewer strokes, saving time and effort. Easy start tooth configuration for clean and accurate cut starts. Induction hardened teeth for outstanding wear resistance. Rigid 1mm thick blade made from premium quality alloy steel for non flex and perfect straight cuts. Ergonomic handle design featuring a soft grip insert for comfort and control plus 45/90° marking bevels.

Item No.			
481001	22"	7TPI / 8PPI 1st fix	10
481002	22"	11TPI / 12PPI 2nd fix	10

## Hacksaws



### Heavy Duty Ripping Saw

Optimized design to easily access nails underneath slates and tiles. Less damage to roof coverings and joinery. 14 TPI precision power blade for exceptional durability and cutting performance. Ergonomic handle for comfortable one-handed use. Reversible blade for extended working life.

Item No.	Length	tpi	Icon
T0817	600mm (24")	14 TPI	5



### Quick Change Hacksaw

Quick release mechanism for rapid blade change. Ergonomic front and rear soft grip handles for extra comfort. Supplied with a 300mm (12") 24TPI Bi-metal blade. Balanced and durable heavy duty frame. Additional 55° blade fixed mounting pins for flush cutting.

Item No.	Length	tpi	Icon
T0815	300mm (12")	24 TPI	5



### Technicians Hacksaw

High tension blade mechanism for rapid cutting. Ergonomically designed soft grip handles for extra comfort. Supplied with a 300mm (12") 24TPI Bi-metal blade. Balanced and durable, coated aluminium frame with blade storage. Additional 55° blade fixed mounting pins for flush cutting.


Item No.	Length	tpi	Icon
T0816	300mm (12")	24 TPI	5



### Heavy Duty Quick Change Hacksaw

Heavy duty premium quality hacksaw with rubber grips for comfort & control. Quick release blade change mechanism for convenience. High leverage blade tensioning system for straighter cuts. Spare blade storage in back frame for convenience. 45 & 90° blade positions.

Item No.	Length	tpi	Icon
T0814	300mm (12")	24	3



### Heavy Duty Hacksaw

Heavy duty, box section steel frame with aluminium handle for strength & durability. High leverage blade tensioning system for straighter cuts. Spare blade storage in back frame for convenience. 45 & 90° blade positions.

Item No.	Length	tpi	Icon
T0905	300mm (12")	24	3



### Hacksaw Blades

Shatterproof HSS Bi-metal construction.


Item No.	Length	tpi	i	Icon
T0932R 1218	300mm (12")	18 tpi	Pack of 3	12
T0931R 12	300mm (12")	24 tpi	Pack of 3	12
T0934R 1232	300mm (12")	32 tpi	Pack of 3	12
T0932 12	300mm (12")	18 tpi	Pack of 25	10
T0933 12	300mm (12")	24 tpi	Pack of 25	10
T0934 12	300mm (12")	32 tpi	Pack of 25	10



### Mini Saw

Handy for cutting metal and plastic in restricted spaces. Die-cast metal frame.

Item No.	Length	Icon
T0833	320mm (12")	6



## Mini Hacksaw

Cast aluminium frame for strength. Broad handle for comfort. Adjustable blade for angled cutting. Special screw tensioner for fast & simple blade fitting.

Item No.	150mm (6")	6
T0836A		



## Mini Hacksaw & Mitre Box

Cast aluminium frame for strength. Broad handle for comfort. Adjustable blade for angled cutting. Special screw tensioner for fast & simple blade fitting. Supplied with lightweight 3 angle mitre box.


Item No.	150mm (6")	5
T0837		



## Junior Hacksaw

Non protruding blade fixing for safety.

Item No.	150mm (6")	6
T0834		



## Junior Hacksaw Blades

Pack of 10 blades of 150mm length.

Item No.	150mm (6")	x 10	10
T0835			

## Multisaws



## Multi-Saw

Multi-purpose saw cuts metal, wood, plastic and plasterboard. Quick release mechanism for rapid blade change. Universal fitting – Compatible with all standard hacksaw, jigsaw and reciprocating blades. Durable, ergonomic grip for comfort, control and confidence when cutting.

Item No.	150mm	tpi
T0820		6, 18, 24

## Plasterboard Saws



## Sabretooth 2-Sided Plasterboard Saw

For fast, clean cutting of plasterboard, wood and plastic. Double-sided 1.5mm SK5 Premium Steel Blade for greater versatility. Fast cut 7TPI blade with triple ground teeth for effortless performance. Fine cut 12TPI blade for cleaner, intricate cuts on finished walls or surfaces. Cushion grip handle with anti-slip horns for increased comfort, control & safety. Rigid scabbard with belt mount for convenient, safe storage that prolongs blade life.

Item No.	120mm	tpi	5
T0838		7 / 12 TPI	



## Sabretooth Plasterboard Saw

For fast cutting of plasterboard, wood and plastic. Triple ground 'turbo cut' teeth for improved cutting performance. Rigid 1.5mm premium grade SK5 steel blade. Cushion grip handle with anti-slip horns for increased comfort, control & safety. Supplied with a protective tooth guard for safe storage.

Item No.	150mm	6
T0832		





## Plasterboard Saw

Induction hardened coarse ground cutting teeth & pointed blade for fast cutting of holes in plasterboard for sockets & conduits. (Also known as a dry wall saw).

Item No.		
T0831	150mm (6")	6

## Trimming Knives



## Multifunction Knife

Easy fit blade holder mechanism enables blade changes in under 3 seconds. Ergonomic, anodised aluminium handle, strong, lightweight & comfortable in use. Quick release, push button locking mechanism for single handed operation. Thumb ledge for greater control and firmer cutting action.

Item No.	
T0955	6



## Folding Utility Knife

Ergonomic, anodised aluminium handle, strong, lightweight & comfortable in use. Precision engineered, stainless steel blade holder reduces blade wobble during straight line cuts. Quick release, push button locking mechanism for single handed operation. Easy fit blade holder mechanism enables blade changes in less than 3 seconds. Thumb ledge for greater control and firmer cutting action.

Item No.	
T0954	6
T0954CBOX10	



## Soft Grip Trimming Knives

Robust, die cast aluminium housing - strong and lightweight. Safety interlocking design to prevent the blade slipping through the body joint. Ergonomically designed, soft grip handle for increased comfort and control. Magnetic blade retainer and captive body screw for quick and easy blade changes. Retractable blade for safe storage. String/wire cutting notch for convenience. Internal 5 blade storage compartment.

Item No.	
T0957-1	6
T0957-2	6



## Trimming Knives

Robust, die cast aluminium housing - both strong and lightweight. Safety interlocking joint to prevent the blade slipping through the body joint. Magnetic blade retainer & captive body screw for quick & easy blade changes. Retractable blade for safe storage. String/wire cutting notch for convenience. Internal 5 blade storage compartment.

Item No.	
T0956-1	6
T0956-2	6



## Safety Trimming Knife

Auto retracting blade for safety in use & storage. Robust, die cast aluminium housing both strong and lightweight. Safety interlocking joint to prevent the blade slipping through the body joint.

Item No.	
T0969	6



## Snap Off Trimming Knife

Heavy duty plastic body with soft grip handle for comfort & control. Push button blade positioning with locking system for control & safety. Integrated blade snapper for safe blade segment removal. Supplied with 4 blades stored in the handle for convenience.

Item No.		
T0958		12



## Spare Snap Off Blades

Heavy duty segmented blades (8 segments) supplied in a spring loaded blade dispenser for safety & convenient storage.


Item No.		
T0971-10		12



## Snap Off Trimming Knife - 9mm

Lightweight and tough ABS handle grips. Stainless steel body with internal storage for up to two spare blades. Integrated blade snapper and pocket-clip. Retractable blade with push-button positioning for control and safety.

Item No.		
T0951	Supplied with one blade. Spare blades available: Item No. T0953	12
T0951-CLIP		



## Spare 9mm Trimming Knife Blades

Pack CONTENTS: 10 x 9mm blades. 12 segments per blade. Razor sharp blades - handle with care.

Item No.		
T0953-10	Compatible with T0951	25

## Files & Rasps



## Flat Bastard Engineers File

One safe edge.

Item No.			
T0080B 10	250mm (10")	Flat	3



## Spare Trimming Knife Blades

Heavy duty blades supplied in a spring loaded blade dispenser for safety & convenient storage.

Item No.		
T0959-10	x 10	12
T0959-50	x 50	12
T0959-100	x 100	12



## Engineers Files

One safe edge.

Item No.			
T0080 6	150mm (6")	Flat 2nd Cut	3
T0080 8	200mm (8")	Flat 2nd Cut	3
T0080 10	250mm (10")	Flat 2nd Cut	3



**Flat Smooth Engineers Files**

One safe edge.

Item No.			
T0080S 6	150mm (6")	Flat Smooth Cut	3
T0080S 8	200mm (8")	Flat Smooth Cut	3



**File/Rasp**

1 side bastard rasp. 1 side bastard cut.

Item No.			
T0106 06	150mm (6")	Flat Rasp	3
T0106 08	200mm (8")	Flat Rasp	3



**Half Round Engineers Files**

Tapered towards the point.

Item No.			
T0082 6	150mm (6")	Half Round 2nd Cut	3
T0082 8	200mm (8")	Half Round 2nd Cut	3
T0082 10	250mm (10")	Half Round 2nd Cut	3



**Wood Rasps**

Tapered towards the point.

Item No.			
T0107 06	150mm (6")	Half Round Rasp	3
T0107 08	200mm (8")	Half Round Rasp	3



**Round Engineers Files**

Tapered towards the point.

Item No.			
T0083 6	150mm (6")	Round 2nd Cut	3
T0083 8	200mm (8")	Round 2nd Cut	3
T0083 10	250mm (10")	Round 2nd Cut	3



**Chainsaw Files**

Second cut.

Item No.			
T0079 1	175mm (7")	4mm (5/32")	3
T0079 2	175mm (7")	5mm (3/16")	6
T0079 3	175mm (7")	5.5mm (7/32")	6





## Saw File

Tapered towards the point.

Item No.	←→	i	📦
T0074 6	150mm (6")	Triangular	3



## Slim Saw File

Tapered towards the point.

Item No.	←→	i	📦
T0073 6	150mm (6")	Triangular	3



## Extra Slim Saw File

Tapered towards the point.

Item No.	←→	i	📦
T0072 5	125mm (5")	Triangular	6



## Mills Saw File

Flat profile. Single cut.

Item No.	←→	i	📦
T0075 10	250mm (10")	Flat	3



## Warding Files

Manufactured from special file steel. Precise cut. Second cut. Wooden handle.


Item No.	←→	i	📦
T0120 1	100mm (4")	Flat 2nd Cut, Square	6
T0120 2	100mm (4")	Flat 2nd Cut, Tapered	6
T0120 3	100mm (4")	Half Round 2nd Cut, Rasp	6
T0120 4	100mm (4")	Round 2nd Cut	6
T0120 5	100mm (4")	Square 2nd Cut	6
T0120 6	100mm (4")	Triangular 2nd Cut	6
T0120P	100mm (4")	Set of 6 - Flat, Flat Tapered, Half Round, Round, Square & Triangular.	3



## Warding File Set




4 piece set with wooden handles. Manufactured from special file steel. Second cut. CONTENTS: triangular, flat, round and flat tapered.

Item No.	←→	i	📦
T0119	100mm (4")	Set of 4 - Triangular, Flat, Round & Flat Tapered.	3



## Needle File Set



Manufactured from special file steel. CONTENTS: triangular, square, flat, tapered flat, half round & round.

Item No.			
T0124P	100mm (4")	Set of 6 - Triangular, Square, Flat, Tapered Flat, Half Round & Round	3



## Wood Chisel Set



Supplied with silicone carbide sharpening stone & protective storage case. CONTENTS: 1 x wood chisel, sizes: 6, 13, 19, & 25mm. Sharpening stone.

Item No.		
T1180	Set of 5	3



## Sharpening Stone

Double sided medium/fine silicon carbide sharpening stone, ideal for sharpening chisels, scissors, shears, etc.



Item No.		
T1126	200 x 50mm	1

## Wood Chisels



## Wood Chisels



Finest chrome vanadium steel, full length hardened & tempered for long life performance. Shatterproof acetate handle for safety. Replaceable blade cover for protection & safety.

Item No.		
T1178 025	6mm (1/4")	3
T1178 037	10mm (3/8")	3
T1178 050	13mm (1/2")	3
T1178 062	16mm (5/8")	3
T1178 075	19mm (3/4")	3
T1178 087	22mm (7/8")	3
T1178 100	25mm (1")	3
T1178 125	32mm (1 1/4")	3
T1178 150	38mm (1 1/2")	3



## Wood Chisel Stand

CONTENTS: 3 x wood chisels, sizes: 6, 10, 13, 16, 19, 22, 25, 32 & 38mm. Sharpening stone.

Item No.		
T1179LS	Stock & stand	1







# Automotive & Engineering

<b>Sure-Drive</b>	<b>159</b>
<b>Spanners</b>	<b>162</b>
<b>Rescue Sets</b>	<b>164</b>
<b>Wrenches</b>	<b>164</b>
<b>Hexagon Keys</b>	<b>165</b>
<b>Tap &amp; Die</b>	<b>166</b>
<b>Inspection Mirrors</b>	<b>167</b>
<b>Wire Brushes</b>	<b>167</b>
<b>Grease Guns</b>	<b>167</b>
<b>Funnels</b>	<b>167</b>



# SURE DRIVE

## Sockets, spanners & wrenches

1. Heavy duty chrome vanadium construction for superior strength and durability.
2. Reversible, 45 tooth ratchet mechanism for a finer working arc (8° arc).
3. Ball bearing locking system with push button release mechanism for quick inter-change of sockets.
4. Dual component, non slip grip for added comfort & control.
5. Forged chrome vanadium steel for superior strength and durability.
6. Non slip, satin chrome plated for resistance to rust and peeling.
7. C.K 'Sure-Drive' system applies torque to the flat of the nut rather than the corners to avoid rounding off.



Sure-Drive



Bi-Hex Sockets - 1/2" Drive

Item No.		
T4690M 10	10mm	5
T4690M 11	11mm	5
T4690M 12	12mm	5
T4690M 13	13mm	5
T4690M 14	14mm	5
T4690M 15	15mm	5
T4690M 16	16mm	5
T4690M 17	17mm	5
T4690M 18	18mm	5
T4690M 19	19mm	5
T4690M 20	20mm	5
T4690M 21	21mm	5
T4690M 22	22mm	5
T4690M 23	23mm	5
T4690M 24	24mm	5
T4690M 27	27mm	5
T4690M 30	30mm	5
T4690M 32	32mm	5



Torque Wrench - 1/2" Drive

Micrometer sleeve for accurate torque setting. 1/2" ratchet, reversible, in Nm and Mkg calibrated with their corresponding markings. Individually calibrated and supplied with a certificate of calibration. Supplied in a protective storage case complete with 120mm extension drive & 3/8" square drive adaptor.

DIN 3122, ISO 6789

Item No.			
T4463	490mm (18")	42 - 210Nm / 30 - 154lb/ft	12



45 Tooth Ratchet Handle - 1/2" Drive

Reversible, 45 tooth ratchet mechanism for a finer working arc (8° arc). Ball bearing locking system with push button release mechanism for quick inter-change of sockets.

Item No.		
T4691	260mm (10")	5



Flexible Handle - 1/2" Drive

Pivoted drive for angled access in tight spaces.

Item No.		
T4692	430mm (17")	5



24 Tooth Ratchet Handle - 1/2" Drive

Reversible, 24 tooth ratchet mechanism for high torque applications. Heavy duty chrome vanadium construction for superior strength & durability. Ball bearing locking system with push button release mechanism for quick inter-change of sockets. Drive: 1/2".

Item No.		
T4603	270mm	3
T4603 1		1



Sliding T-Handle - 1/2" Drive

Forged chrome vanadium steel. Drive: 1/2".

Item No.		
T4695	250mm (10")	5





### Long Extension - 1/2" Drive

Forged chrome vanadium steel. Drive: 1/2".

<b>Item No.</b>		
T4693	250mm (10")	5



### Short Extension - 1/2" Drive

Forged chrome vanadium steel. Drive: 1/2".

<b>Item No.</b>		
T4694	125mm (5")	5



### Universal Joint - 1/2" Drive

Forged chrome vanadium steel. Drive: 1/2".

<b>Item No.</b>	
T4696	5



### Socket Accessory Stand

<b>Item No.</b>
T4645S



### Coloured 3/8" Socket & Spanner Set

12 piece professional colour coded socket and spanner set - 72 tooth ratchet wrench. High torque 12 point sure drive sockets. Apply torque to the flat of the nut rather than the corners to avoid rounding off. Forged chrome vanadium steel for superior strength & durability.

<b>Item No.</b>	
T4659	10



### Coloured 1/4" Socket Set/17

17 piece professional colour coded socket set - 72 tooth ratchet wrench. High torque 12 point sure drive sockets. Apply torque to the flat of the nut rather than the corners to avoid rounding off. Forged chrome vanadium steel for superior strength & durability.

<b>Item No.</b>	
T4658	20



### Socket Set/22 - 1/2" Drive

Heavy duty chrome vanadium construction for superior strength and durability. Reversible, 72-teeth ratchet mechanism for fine adjustment in confined spaces. Ball bearing locking system with push-button release mechanism for quick interchange of sockets. Dual component, non-slip grip for added comfort and control. Hex and Bi-Hex design to accommodate a range of fasteners and bolts. Rust-resistant satin chrome finish. C.K Sure-Drive system applies torque to the flat of the nut rather than the corners to avoid rounding-off.

<b>Item No.</b>
T4662



**Socket Set/23 - 3/8" Drive**

Heavy duty chrome vanadium construction for superior strength and durability. Reversible, 72-teeth ratchet mechanism for fine adjustment in confined spaces. Ball bearing locking system with push-button release mechanism for quick interchange of sockets. Dual component, non-slip grip for added comfort and control. Hex and Bi-Hex design to accommodate a range of fasteners and bolts. Rust-resistant satin chrome finish. C.K Sure-Drive system applies torque to the flat of the nut rather than the corners to avoid rounding-off.

**Item No.**

T4661



**Socket Set/36 - 1/4" Drive**

Heavy duty chrome vanadium construction for superior strength and durability. Reversible, 72-teeth ratchet mechanism for fine adjustment in confined spaces. Ball bearing locking system with push-button release mechanism for quick interchange of sockets. Dual component, non-slip grip for added comfort and control. Hex and Bi-Hex design to accommodate a range of fasteners and bolts. Rust-resistant satin chrome finish. C.K Sure-Drive system applies torque to the flat of the nut rather than the corners to avoid rounding-off.

**Item No.**

T4660



**Pocket Socket Set - 1/4" Drive**

Forged chrome vanadium steel for superior strength & durability. C.K Sure-Drive system applies torque to the flat of the nut rather than the corners to avoid rounding off.

**Item No.**

T4654



3



**Socket Set/23 - 3/8" Drive**

Metric socket set, forged from chrome vanadium steel. All contents have a non-slip satin chrome finish giving maximum resistance to rust and peeling. C.K Sure-Drive system exerts torque through the flats of the socket rather than the corners, thus eliminating "rounding off" at high torque. Ratchet with comfortable two compound handle.

**Item No.**

T4656



2



**Socket Set/39 - 1/4" Drive**

Metric socket set, forged from chrome vanadium steel. All contents have a non-slip satin chrome finish giving maximum resistance to rust and peeling. C.K Sure-Drive system exerts torque through the flats of the socket rather than the corners, thus eliminating "rounding off" at high torque. Ratchet with comfortable two compound handle.

**Item No.**

T4655



3

## Spanners



### Combination Spanners

Drop forged chrome vanadium steel, hardened & tempered for strength & durability. Heavy duty chrome plated for corrosion resistance. 12° offset bi-hex ring for access.

DIN 3113

Item No.				
T4343M 06	100mm	6mm	Loose	10
T4343M 06H	100mm	6mm	On hanger	6
T4343M 07	110mm	7mm	Loose	10
T4343M 07H	110mm	7mm	On hanger	6
T4343M 08	120mm	8mm	Loose	10
T4343M 08H	120mm	8mm	On hanger	6
T4343M 09	130mm	9mm	Loose	10
T4343M 09H	130mm	9mm	On hanger	6
T4343M 10	140mm	10mm	Loose	10
T4343M 10H	140mm	10mm	On hanger	3
T4343M 11	150mm	11mm	Loose	10
T4343M 11H	150mm	11mm	On hanger	3
T4343M 12	160mm	12mm	Loose	10
T4343M 12H	160mm	12mm	On hanger	3
T4343M 13	170mm	13mm	Loose	10
T4343M 13H	170mm	13mm	On hanger	3
T4343M 14	180mm	14mm	Loose	10
T4343M 14H	180mm	14mm	On hanger	6
T4343M 15	190mm	15mm	Loose	10
T4343M 15H	190mm	15mm	On hanger	6
T4343M 16	200mm	16mm	Loose	10
T4343M 16H	200mm	16mm	On hanger	6
T4343M 17	210mm	17mm	Loose	10
T4343M 17H	210mm	17mm	On hanger	3
T4343M 18	220mm	18mm	Loose	10
T4343M 18H	220mm	18mm	On hanger	1
T4343M 19	230mm	19mm	Loose	10
T4343M 19H	230mm	19mm	On hanger	1
T4343M 20	240mm	20mm	Loose	5
T4343M 20H	240mm	20mm	On hanger	1
T4343M 21	250mm	21mm	Loose	5
T4343M 21H	250mm	21mm	On hanger	1
T4343M 22	260mm	22mm	Loose	5
T4343M 22H	260mm	22mm	On hanger	1
T4343M 24	280mm	24mm	Loose	5
T4343M 24H	280mm	24mm	On hanger	1
T4343M 27	310mm	27mm	Loose	5
T4343M 27H	310mm	27mm	On hanger	1
T4343M 30	340mm	30mm	Loose	5
T4343M 30H	340mm	30mm	On hanger	1
T4343M 32	360mm	32mm	Loose	5
T4343M 32H	360mm	32mm	On hanger	1





**Combination Spanner Set/10**

10 piece set supplied in a wall mounting rack for convenient storage. Drop forged chrome vanadium steel, hardened & tempered for strength & durability. Heavy duty chrome plated for corrosion resistance. 12° offset bi-hex ring. CONTENTS: 8, 9, 10, 11, 12, 13, 14, 15, 17, & 19mm. DIN 3113

<b>Item No.</b>	
T4343M/10ST	3



**Combination Spanner Set/12**

12 piece set supplied in a wall mounting rack for convenient storage. Drop forged chrome vanadium steel, hardened & tempered for strength & durability. Heavy duty chrome plated for corrosion resistance. 12° offset bi-hex ring. CONTENTS: 8, 9, 10, 11, 12, 13, 14, 15, 17, 19, 21 & 22mm. DIN 3113

<b>Item No.</b>	
T4343M/12ST	1



**Speed Spanners Set/6**

Drop forged chrome vanadium steel, hardened & tempered for strength & durability. Colour coded for quick selection of the correct size. Innovative ratchet action style jaw for use in tight places. 12° offset bi-hex ring for access. Supplied in a wall mounting rack for convenient storage. CONTENTS: 10, 12, 13, 14, 15 & 17mm.

<b>Item No.</b>	
T4345/6ST	5



**Metric Ratchet Spanner Set/7**

7 piece set supplied in a wall mounting rack for convenient storage. Drop forged chrome vanadium steel, hardened & tempered for strength & durability. Heavy duty chrome plated for corrosion resistance. CONTENTS: 8, 10, 12, 13, 15, 17 & 19mm. DIN 3113

<b>Item No.</b>	
T4344M7ST	5



**Colour Coded Spanner Set/12**

Drop forged chrome vanadium steel, hardened & tempered for strength & durability. Colour coded for quick selection of the correct size. CONTENTS: 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 17 & 19mm.

<b>Item No.</b>		
T4346M12ST	Set of 12	10



## Rescue sets

Patented extractor inserts for ring spanners & sockets. Securely grips all round and works on fasteners with up to 85% damaged or worn corners.



Patented extractor hex key set removes damaged hex fasteners with up to 100% rounded heads. Multi-purpose design, installs new fasteners.



## Rescue Sets



### Damaged Nut Extractor Set

Adaptors for fixings sized 8, 9, 10, 11, 12, 13, 14, 15, 16 and 17mm. Works on a range of fasteners: 6 point, 12 point, Hex and Spline. Adapts just two socket/ring spanner sizes to fit 10 different fasteners (sizes 8-17mm). 8-12mm Inserts suit 14mm wrench / 12-17mm Inserts suit 19mm wrench. Unique Flange design to prevent fall through.

#### Item No.

T4360



### Damaged Hex Bolt Rescue Set

Ball-ended for use at an angle of up to 25 degrees where access is restricted. Sizes: 1.5, 2, 2.5, 3, 4, 5, 6, 8 and 10mm. Folding carry clip for convenience.

#### Item No.

T4440M

## Wrenches



### Adjustable Wrenches - Sure-Drive

C.K Sure-Drive jaws which apply torque to the flat of the nut rather than the corners to avoid rounding off. Forged chrome vanadium for strength & durability. Matt chrome plated for corrosion protection. Extra capacity jaws - up to 18% wider than standard patterns. Metric & imperial graduations for accurate jaw pre-setting. Soft grip handle for comfort & control.

Item No.			
T4365 150	150mm (6")	24mm	3
T4365 200	200mm (8")	29mm	3
T4365 250	250mm (10")	33mm	3
T4365 300	300mm (12")	38mm	3



## Adjustable Wrenches - Wide Jaw

Forged chrome vanadium for strength & durability. Extra capacity jaws - up to 26% wider than standard patterns. Precision ground, fully polished jaws for secure nut engagement. Metric graduations for accurate jaw pre-setting.

Item No.			
T4366 150	150mm (6")	24mm	6
T4366 200	200mm (8")	29mm	6
T4366 250	250mm (10")	33mm	6
T4366 300	300mm (12")	38mm	6
T4366 375	375mm (15")	51mm	5
T4366 450	450mm (18")	60mm	5



## Self Grip Wrench - Concave Jaws

Forged chrome vanadium jaws for strength & durability. Concave jaws ideal for gripping round profile. Integral wire cutting blades. Epoxy coated for corrosion protection. Quick release lever.

Item No.			
T3630 10	250mm (10")	50mm	5



## Self Grip Wrench - V-Jaws

Forged chrome vanadium jaws for strength & durability. Combination straight & curved jaws ideal for gripping round, flat & square profile. Epoxy coated for corrosion protection. Quick release lever.

Item No.			
T3638 07	180mm (7")	25mm	6
T3638 10	250mm (10")	35mm	6



## Self Grip Wrench - Straight Jaws

Forged chrome vanadium jaws for strength & durability. Flat jaws ideal for gripping flat profile. Epoxy coated for corrosion protection. Quick release lever.

Item No.			
T3641	250mm (10")	40mm	5

## Hexagon Keys



## Hexagon Keys - Metric

Chrome vanadium steel. Hardened and tempered for strength and durability. ISO 2936

Item No.				
T4411 007	0.7mm	32mm	6mm	12
T4411 009	0.9mm	32mm	10mm	12
T4411 01	1.0mm	32mm	10mm	12
T4411 012	1.2mm	38mm	10mm	12
T4411 0127	1.27mm	40mm	12mm	12
T4411 015	1.5mm	45mm	14mm	12
T4411 02	2.0mm	50mm	16mm	12
T4411 025	2.5mm	56mm	18mm	12
T4411 03	3.0mm	63mm	20mm	12
T4411 035	3.5mm	67mm	23mm	12
T4411 04	4.0mm	71mm	25mm	12
T4411 045	4.5mm	75mm	26mm	12
T4411 05	5.0mm	80mm	28mm	12
T4411 055	5.5mm	85mm	30mm	12
T4411 06	6.0mm	90mm	32mm	12
T4411 07	7.00mm	95mm	34mm	12
T4411 08	8.0mm	100mm	36mm	12
T4411 09	9.0mm	105mm	38mm	12
T4411 10	10.0mm	112mm	40mm	12
T4411 11	11.0mm	118mm	43mm	12
T4411 12	12.0mm	125mm	45mm	6
T4411 13	13.0mm	133mm	50mm	6
T4411 14	14.0mm	140mm	56mm	3
T4411 15	15.0mm	147mm	58mm	3
T4411 16	16.0mm	154mm	60mm	3
T4411 17	17.0mm	160mm	63mm	3
T4411 18	18.0mm	170mm	65mm	3
T4411 19	19.0mm	180mm	70mm	3
T4411 20	20.0mm	187mm	73mm	3
T4411 22	22.0mm	200mm	80mm	3





## Hexagon Key Folding Set/8

Professional quality fully hardened chrome vanadium steel blades. Dual component holder for convenient storage.

<b>Item No.</b>	
T4406	6



## Coloured Hex Key Set/9

Premium quality S2 steel blades, tempered and hardened for exceptional strength & durability. Screws can be tightened or loosened at angles up to 25°. CONTENTS: 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10mm.

<b>Item No.</b>	
T4449	3



## Hexagon Key Clip Set/9

Chrome vanadium steel, hardened & tempered for strength & durability. Ball ended for use at an angle of up to 25° where access is restricted. Supplied in a storage holder.

<b>Item No.</b>		
T4444I	Imperial AF $\frac{5}{64}$ , $\frac{3}{32}$ , $\frac{1}{8}$ , $\frac{5}{32}$ , $\frac{3}{16}$ , $\frac{7}{32}$ , $\frac{1}{4}$ , $\frac{5}{16}$ , $\frac{3}{8}$ "	6



## Hexagon Key TX Tamperproof Set

Professional quality fully hardened chrome vanadium steel blades. Dual component holder for convenient storage. CONTENTS: T8, T9, T10, T15, T20, T25, T27, T30, T40.

<b>Item No.</b>	
T4409	3




## Hexagon Key Clip Set/10

Chrome vanadium steel, hardened & tempered for strength & durability. Ball ended for use at an angle of up to 25° where access is restricted. Supplied in a storage holder.

<b>Item No.</b>		
T4443M	Metric 1.5, 2, 2.5, 3, 4, 5, 6, 7, 8, 10mm	6

## Tap & Die



## Tap & Die Set/21 - Metric

High carbon steel, hardened & tempered for strength and durability. Precision machined to produce accurate thread forms. CONTENTS: Tap & dies, sizes: 3 x 0.5, 4 x 0.7, 5 x 0.8, 6 x 1.0, 7 x 1.0, 8 x 1.25, 10 x 1.5, 12 x 1.75mm & 1/8" NPT. Tap wrench. Die stock. Screwdriver.

<b>Item No.</b>	
T4032	10

Inspection Mirrors



Inspection Mirrors - Telescopic

Telescopic shaft. Stainless steel. Swivel head. Pocket clip.

Item No.	↔	∅	📦
T5913 32	180 - 520mm	32mm	6
T5912 38	125 - 685mm	38mm	6
T5912 55	125 - 560mm	55mm	6



Inspection Mirror - Extra Long

Telescopic shaft. Stainless steel. Swivel head. Comfort handle.

Item No.	↔	∅	📦
T5914 55	250 - 780mm	55mm	6

Wire Brushes



Wire Brush

Hardened & tempered steel wire bristles, set in 4 rows for professional results.

Item No.	i	📦
T6238 4	4 Rows	12

Grease Guns



Grease Gun and Accessories

Heavy duty construction grease gun with pressure head. Multiple loading: cartridge, grease gun filler or bulk. Precision machined piston and pump cylinder. Air release valve. Wide safety knurls for a sure grip. Supplied complete with angled delivery tube and 4 jaw hydraulic coupler. Delivery pressure 400/5800 psi.

Item No.	↔	📏	i	📦
T6270	500cm <sup>3</sup>	66g		10
T6270 2	300mm	32g	Flexible Hose	10
T6270 3	450mm	84g	Flexible Hose	6
T6270 4			Coupler	6
T6270 5			Grease Cartridge	36

Funnels



Metal Funnel

Bright tin plated funnel. Flexible detachable metal hose. With plastic spout and brass filter.

Item No.	↔	📦
T6274 2	3.2ltr / 300mm∅	6



Plastic Funnel

Polythene funnel with flexible, detachable metal hose, plastic spout and brass filter.

Item No.	↔	📦
T6275 1	3.2ltr / 160mm∅	10







# Marking & Measuring

<b>Tape Measures</b>	<b>170</b>
<b>Spirit Levels</b>	<b>171</b>
<b>Rules</b>	<b>172</b>
<b>Chalk Lines &amp; Accessories</b>	<b>172</b>
<b>Joiners Bevels &amp; Squares</b>	<b>173</b>
<b>Combination Squares</b>	<b>174</b>
<b>Vernier Calipers</b>	<b>175</b>
<b>Feeler Gauges</b>	<b>175</b>
<b>Pens &amp; Pencils</b>	<b>175</b>
<b>Pocket Balances</b>	<b>175</b>



## XT & AT tapes

Professional quality tape measures featuring advanced tape technology to cater for the most demanding requirements.

1. Nylon coated blade for superior wear resistance.
2. Rubber casing for a strong grip and impact protection.
3. Double sided blade markings for regular, overhead and vertical measuring.

XT tape - Manual blade lock, powerful, non-slip.  
AT tape - Automatic blade locking mechanism.



## Tape Measures



### XT Tape Measures

Express blade brake - instant locking. Dual function end hook - top and bottom hooks for convenience. Shock absorbing device at the blade retraction hole. Metal belt clip.

2014/22/EC Class 2

Item No.	↔	i	i	↑	👜	📦
T3448 16	5m / 16ft	Metric / Imperial	2.3m Stand Out	25mm	305g	6
T3448 25	7.5m / 25ft	Metric / Imperial	2.8m Stand Out	27mm	470g	6
T3448M 5	5m	Metric	2.3m Stand Out	25mm	305g	
T3448M 8	8m	Metric	2.8m Stand Out	27mm	490g	



### AT Auto Lock Tape Measure

Automatic blade locking mechanism. Shock absorbing device at the blade retraction hole. Metal belt clip.

2014/22/EC Class 2

Item No.	↔	i	i	↑	👜	📦
T3447 16	5m / 16ft	Metric / Imperial	2.3m Stand Out	25mm	285g	6



## Softech Tape Measures

Tough ABS plastic body for damage protection. Full lock & pause buttons for control. Belt clip for convenience. Nylon coated blade - superior abrasion resistance & durability. 400mm joist centre markings for fast marking out. True zero hook for accurate external & internal measurements. Integral recoil damper for hook damage protection.

2014/22/EC Class 2

Item No.			
T3442 10	3m / 10ft	Metric / Imperial	
T3442 16	5m / 16ft	Metric / Imperial	
T3442 25	7.5m / 25ft	Metric / Imperial	
T3442M 3	3m	Metric	
T3442M 5	5m	Metric	
T3442M 8	8m	Metric	6




## Surveyors Tapes

Tough ABS plastic body for damage protection. Integral ground spike & fold out blade hook for secure anchoring. Soft grip handle for comfortable carrying. Fold out winding handle for rapid rewind & safe storage. Glassfibre reinforced tape - strong & stretch resistant. Double sided metric/imperial graduations.

20144/22/EC Class 3

Item No.			
T3565 100	30m (100ft)	13mm (1/2")	3
T3565 165	50m (165ft)	13mm (1/2")	3
T3565 330	100m (330ft)	13mm (1/2")	3

## Spirit Levels




## Fibreglass Measuring Tape

Tough ABS plastic body for damage protection. Fold out blade hook for secure anchoring. Hand strap for convenient carrying. Fold out winding handle for rapid rewind & safe storage. Glassfibre reinforced tape - strong & stretch resistant. Double sided metric/imperial graduations.

20144/22/EC Class 3

Item No.			
T3561 100	30m (100ft)	13mm (1/2")	3



## Steel Measuring Tape

Tough steel case for damage protection. Fold out blade hook for secure anchoring. Hand strap for convenient carrying. Fold out winding handle for rapid rewind & safe storage. Glassfibre reinforced tape - strong & stretch resistant. Nylon coated steel tape - extremely strong & stretch resistant. Double sided metric/imperial graduations.

20144/22/EC Class 3


Item No.			
T3563 100	30m (100ft)	13mm (1/2")	3



## Box Section Spirit Levels

Powder coated, box section aluminium - strong, light & durable. Shockproof, unbreakable vials, guaranteed leakproof for three years. Luminous horizontal vial for low light conditions. Precision manufactured, accurate to +/- 0.5mm per metre. Metric measurement graduations for convenience.

Item No.			
T3494 16	400mm (16")	2 vial with rule	30
T3494 24	600mm (24")	2 vial with rule	30
T3494 32	800mm (32")	3 vial with rule	30
T3494 40	1000mm (40")	3 vial with rule	30
T3494 48	1200mm (48")	3 vial	10
T3494 70	1800mm (70")	3 vial	10



## Pocket Level

Tough ABS plastic body for damage protection. V-groove base for pipework. Magnetic base for steelwork. Patented detachable mini level with magnetic base, ideal for setting pattress boxes. Also features string slots for use as line level. 1 vertical & 1 horizontal vial.

Item No.		
T3482	210mm (8 1/4")	5



## Rules



### Straight Edge Rule

Anodised aluminium construction with a strong plastic handle - lightweight, easy clean. Metric graduations. Ideal for cutting, measuring and marking out.

Item No.		
T3531 100	100mm (4")	1



### Folding Rule

Made of high-quality beech wood. Joints riveted, brass coated springs. High accuracy. Section Thickness: 3mm. Section Height: 16mm.

20144/22/EC Class 3

Item No.		
T3514	2000mm (6ft)	1



### Steel Rules

Stainless steel for corrosion protection. Permanent indented markings for wear resistance. Fine graduations for accurate measurements.

Item No.			
T3530 06	150mm (6")	18mm	6
T3530 12	300mm (12")	25mm	6

## Chalk Lines & Accessories



### Heavy Duty Chalk Line Reel Set

Die cast aluminium construction. Strong & lightweight. Fold away winding handle for convenient storage. Self chalking line with end attachment hook. Supplied with 60g of blue chalk.

Item No.	
T3520B	30m (100ft)



### Chalk Line Reel and Chalk

Tough plastic construction - strong & lightweight. Fold away winding handle for convenient storage. Self chalking line with end attachment hook for ease of use. Supplied with 60g of blue chalk.

Item No.		
T3522	30m (100ft)	6



### Chalk Line - Cotton

Strong & absorbent cotton for effective retention of marking chalk.

Item No.		
T3517	18m (60ft)	12



## Chalk Line - Braided Nylon

Braided nylon construction - extra strong & durable.

Item No.		
T3519	18m (60ft)	12



## Plumb Bob

Conical, fully polished bob complete with screwed brass cord fitting.

Item No.	
T3492 11	3



## Chalk Powder

High density chalk for clear marking results. Plastic refill container with re-sealable dispenser cap.

Item No.			
T3521B 100	Blue	100g (4oz)	6
T3521R 100	Red	100g (4oz)	6

## Joiners Bevels & Squares



### Joiners Square - Rosewood

Hardened & tempered blued steel blade for corrosion resistance. Blade secured with three brass rivets & brass inside face for long term accuracy. Hard rosewood stock.

Item No.		
T3540 09	225mm (9")	3
T3540 12	300mm (12")	3



### Sliding Bevel - Rosewood

Hardened & tempered blued steel blade for corrosion resistance. Quick lock lever for convenient adjustment. Hard rosewood stock.

Item No.		
T3541 9	225mm (9")	4



### Marking Gauge - Rosewood

Screw pin adjustment for accurate & consistent setting of mortice & tenon joints. Heavy brass inlays on marking faces for protection. Hard rosewood body.

Item No.		
T3543	190mm (7 1/2")	1



## Joiners Square - Beech

Hardened & tempered blued steel blade for corrosion resistance. Blade secured with three brass rivets & brass inside face for long term accuracy. Beech stock.

<b>Item No.</b>		
T3533 09	225mm (9")	3



## Sliding Bevel - Beech

Hardened & tempered blued steel blade for corrosion resistance. Beechwood stock.

<b>Item No.</b>		
T3537 09	230mm (9")	3




## Marking Gauge - Beech

Thumbscrew adjustment for accurate & consistent marking. Brass inlays on marking faces for protection. Beechwood body.

<b>Item No.</b>		
T3542A	240mm (9 1/2")	3

## Combination Squares



## Combination Square - 3 in 1

Heavy duty, 3 in 1 construction for a complete marking & measuring solution. Stainless steel rule for corrosion protection. Permanent indented markings for wear resistance.


<b>Item No.</b>		
T3579	300mm (12")	1



## Heavy Duty Combination Square

Heavy duty construction for strength & durability. Stainless steel rule for corrosion protection. Permanent indented markings for wear resistance.

<b>Item No.</b>		
T3581	300mm (12")	3




## Combination Square

Stainless steel rule for corrosion protection. Permanent indented markings for wear resistance.

<b>Item No.</b>		
T3582	210mm (8 1/4")	3



Vernier Calipers



Vernier Caliper

Roller adjustment along metric & imperial graduated rule for convenience. Nickel plated for corrosion protection.

Item No.		
T3451	125mm (5")	6

Feeler Gauges



Feeler Gauges

Blades permanently etched with its size for long term use. BS EN 957:2008 part 2 and DIN 2275:2014 grade 2

Item No.			
T3527 413	100mm (4")	Imperial	3
T3527M 413	100mm (4")	Metric	3

Pens & Pencils



Carpenters Pencil

Traditional rectangular leaded carpenters pencil. For noting of dimensions etc.

Item No.		
T1125 24	240mm	25



Professional Marker Pen

Quick drying ink - dries within 5 seconds on most surfaces, eliminating smudges. Waterproof - for writing in wet, greasy and gritty conditions. 1mm Bullet Nib - fine bullet nib design for access to tight spots, imprinting a 1mm line. Premium quality acrylic nib - non-toxic, low odour, job site ready. Permanent - indelible ink for writing permanently or semi-permanently on a wide variety of surfaces.

Item No.				
T1130-TUB	13.5mm	1mm	< 5 seconds	50

Pocket Balances



Pocket Balances

Brassed scale, black lacquered body, tinned hook & ring for corrosion resistance. Calibrated in 1lb/0.5kg divisions.

Item No.		
T6202 025	12.5kg (25lb)	12
T6202 032	15kg (32lb)	12
T6202 044	20kg (44lb)	12
T6202 050	23kg (50lb)	6
T6202 066	30kg (66lb)	6
T6202 088	40kg (88lb)	6
T6202 112	50kg (112lb)	6







# Water Systems

**Hose Connectors**

**178**

**Hose Accessories**

**180**

**Hose Pipes**

**181**






## Water systems

The range of C.K. hose connectors is precision engineered to be long lasting and leak free. The fittings are solid brass, so are much more hard wearing than plastic systems and are rust resistant. They are compatible with all popular makes of hoses of both 1/2" and 3/4" bores.

1. Solid brass - tough and corrosion resistant.
2. Ball bearing locking - secure and hard wearing.
3. Threaded clamp for a secure fit to hosepipe.



## Hose Connectors



### Hose Connectors - Male

Simple and user friendly fitting.

Item No.	Ø	
G7904	1/2"	6
G7934	3/4"	6



### Hose Repairers

Secure screw down hose connector for permanently joining two hoses or re-joining a hose when a damaged section has been cut out.

Item No.	Ø	
G7924	1/2"	6
G7932	3/4"	6



### Hose Connector Display

CONTENTS: 12 x hose connectors: female (1/2"), 6 x hose connectors: male (1/2"), male & female, double male, triple male & water stop (1/2"), 6 x tap connectors: threaded female (1/2"), threaded female (5/8") & threaded female (3/4"), 3 x tap connectors: threaded male (1/2"), threaded male (3/4"), two-way (3/4"), push-on (standard bore) & push-on (large bore), 6 x hose repairers (1/2"), 6 x adjustable spray guns, 6 x adjustable spray nozzles.


Item No.		
G7900ALS	Stock & stand	1



**Hose Connectors - Female**

Used at both ends of a hose pipe.

Item No.	Ø	
G7903	1/2"	6
G7933	3/4"	6



**Hose Connectors**

Ideal to extend hose pipes.


Item No.	Ø	
G7907	1/2"	6
G7907Y	1/2"	6



**Hose Connector - Male & Female**

Suitable for extension / reduction of hose length.

Item No.	Ø	
G7905	1/2"	6



**Hose Connector - Water Stop**

Automatic water cut off feature allows the interchange of accessories such as sprinklers, nozzles, spray guns, etc.

Item No.	Ø	
G7913	1/2"	6



**Tap Connectors - Threaded Female**

Tap connector for threaded taps. Screwed onto the tap, the connector provides a quick coupling to the system.

Item No.	Ø	
G7915 50	1/2"	6
G7915 62	5/8"	6
G7915 75	3/4"	6



**Tap Connectors - Threaded Male**

Ideal for converting a female threaded tap or other equipment such as jet washers to connect to a female hose coupling.

Item No.	Ø	
G7916 50	1/2"	6
G7916 75	3/4"	6



### Tap Connector - 2 Way

For 3/4" external-threaded taps. Two outlets each featuring a cut off valve that can be individually closed.


Item No.	Ø	Icon
G7918	3/4"	6



### Adjustable Spray Gun

Comfortable ergonomic design with lockable on/off trigger and precise easy to use spray to jet adjustment.

Item No.	Icon
G7943	3



### Tap Connectors - Push-On

Tightens to smooth bore taps by screw clip (not suitable for high water pressures).

Item No.	i	Icon
G7919	Standard bore (10 - 20mm)	3
G7928	Large bore (20 - 30mm)	3



### Spare O-Rings

Brass Interlock O-Rings.

Item No.	i	Icon
G7980	Packet of 20	6

## Hose Accessories



### Adjustable Spray Nozzle

Adjustable spray fitting with male end. Simple turn adjustment varies flow from "off" through spray to hard jet.

Item No.	Icon
G7912	6



### Rose Spray

Diffuses water through hundreds of holes to provide a gentle spray pattern, suitable for delicate plants. 36" long reach arm, lightweight design and comfort grip ensures ease of use in all watering situations. On/off volume control.

Item No.	Icon
G7945	900mm (36") 1






## Lawn Sprinkler - Oscillating

Covers 200m<sup>2</sup> at a 5 bar pressure. Adjustable to 4 modes of spread: full, right, left or centre. With internal filter.

Item No.		
G7756BI		1



## Lawn Sprinklers - Pulse Jet

Covers 450m<sup>2</sup> at a minimum pressure of 1.2 bar. Adjustable watering arc for full circle or partial segment coverage.

Item No.		
G7752BI		
G7755BI		3



## Pro-Flex Hose Pipes - 3/4"

High quality, triple layered, polyester reinforced for extra strength & resistance to twisting and stretching. Abrasion resistant PVC outer layer for long life. UV stable. Burst pressure 35 bar.

Item No.			
G7626 15	15m	19mm (3/4")	10
G7626 30	30m	19mm (3/4")	5
G7626 50	50m	19mm (3/4")	3

## Hose Pipes



## Pro-Flex Hose Pipes - 1/2"

Highly flexible hose pipe 1/2" / 13mm. Premium quality, triple layered, polyester reinforced for extra strength & resistance to twisting and stretching. Heavy duty, abrasion resistant PVC outer layer for superior elasticity at low temperatures. UV stable. Burst pressure 35 bar.

Item No.			
G7625 15	15m	13mm (1/2")	10
G7625 30	30m	13mm (1/2")	5
G7625 50	50m	13mm (1/2")	3
G7625 75	75m	13mm (1/2")	2



## Multi-Flex Hose Pipes - 1/2"

High quality 1/2" hose pipe, triple layered, polyester reinforced for extra strength & resistance to twisting and stretching. Abrasion resistant PVC outer layer for long life. UV stable. Burst pressure 28 bar.

Item No.			
G7621 15	15m	13mm (1/2")	10
G7621 30	30m	13mm (1/2")	5
G7621 50	50m	13mm (1/2")	3







# Lighting

**Inspection Lights**

**184**

**Site Lights**

**186**

**Head Torches**

**187**





## Inspection lights

High performance COB-LED with additional torch light.  
4 Lighting modes: standard, red, torch, tip.

1. Battery life indicator.
2. Charge time: 4hrs.
3. Integrated rechargeable 3.7V 2600mAh Li-Ion battery.
4. Integrated magnet.
5. Clamp and hanging hook.



## Inspection Lights



### C.K. MINI LED Inspection Light

Compact Inspection light with dual function LED. Lightweight pocket friendly design with clip. Tactile on/off mode switch. CKlearView LED for accurate colour rendering. 120lm main light. 80lm torch light. 3.7V 750mAh Li-ion battery for up to 4.5 hours runtime. USB-C rechargeable in 1.5 hours (cable included).

Item No.	i	📦
T9426USB	150lm	5



### C.K. MIDI LED Inspection Light

High powered Inspection light with dual function LED. IK07 moulded design for exceptional durability. Tactile on/off mode switch. CKlearView LED for accurate colour rendering. 400lm main light with eco mode (250lm). 100lm torch light. Flexible 180° folding design with magnetic base. Retractable 360° rotating hook. IP54 rated against dust and water ingress. 3.7V 2600mAh Li-ion battery for up to 5.0 hours runtime. Battery level indicator. USB-C rechargeable in 3.5 hours (cable included).

Item No.	i	📦
T9427USB	400lm	8



### C.K. MAXI LED Inspection Light

High Powered Inspection light with dual function LED. IK07 moulded design for exceptional durability. Tactile on/off mode switch. CKlearView LED for accurate colour rendering. 700lm dimmable main light with eco mode (175lm). 150lm torch light. Flexible 180° folding design with magnetic base. Retractable 360° rotating hook. IP65 rated against dust and water ingress. 3.7V 2600mAh Li-ion battery for up to 8.0 hours runtime. Battery level indicator. USB-C rechargeable in 3.5 hours (cable included).

Item No.	i	📦
T9428USB	700lm	5



**Neck Light - 300lm**

Versatile LED neck light with adjustable brightness. Ergonomic design for comfortable all day use. Individual light control via independent on/off switches. CKlearView LED for accurate colour rendering. Max. 300lm with dimmer function. Flexible antenna for optimum light orientation. Magnetised and threaded base gives a choice of mounting options. USB-C rechargeable with battery charge indicator (cable included).

Item No.	i	☐
T9429USB	300lm	5



**Mini Inspection Light - USB**

High performance 240 lumen COB-LED. 2 Lighting modes: high, dimmed. Battery indicator light. Battery life: up to 2.5 hrs. Charge time: 2.5 hrs. Integrated rechargeable 3.7V 600mAh Li-Ion battery. Integrated pocket clip and magnetic base. Supplied with type C USB charger cable (UK mains plug not included).

CE UKCA

Item No.	↔	☐
T9423USB	89H x 21W x 12D (mm)	12
T9423USBCBOX		



**Compact Inspection Light - USB**

T4924USB: 240 lumen COB-LED. Battery life: standard/red up to 2.5hrs, torch up to 4hrs, tip up to 14 hrs. Charge time: 4hrs. Supplied with type C USB charger cable (UK mains plug not included).

T9425USB: 400 lumen COB-LED. Battery life: standard/red up to 3hrs, torch up to 5hrs, tip up to 17hrs. Charge time: 4hrs. Supplied with type C USB charger cable (UK mains plug not included).

CE UKCA

Item No.	↔	☐
T9424USB	130H x 27W x 41D (mm)	12
T9425USB	158H x 31W x 66D (mm)	12



**Pocket Inspection Light - 120Lm**

Super bright COB-LED. Wide flood beam. End torch light. Magnetic pocket clip. 4 lighting modes: High, dimmed, flash, torch. Water & dirt resistant, tested to IP54. Battery life: up to 6 hours. Battery: 3 x AAA (Not supplied).

EMC, RoHS, WEEE, IP54

Item No.	↔	i	☐
T9420	162 x 26mm	150Lm	3
T9420CBOX			12



**Pocket Inspection Light - 240Lm**

Super bright COB LEDs producing 240 lumens. Wide flood beam. End torch light. Swivelling magnetic base. Water & dirt resistant, tested to IP54. Integrated hanging hook and belt clip. 3 x lighting modes: High, dimmed, torch. Battery life: up to 10hrs. Battery life indicator. Supplied with USB cable and 3-pin wall plug.

EMC, RoHS, WEEE, IP54

Item No.	i	☐
T9421R	240Lm	3



**Pocket Inspection Light - 420Lm**

Super bright COB LEDs producing 420 lumens. Wide flood beam. End torch light. Swivelling magnetic base and magnetic back plate. Water & dirt resistant, tested to IP54. Integrated hanging hooks. 3 x lighting modes: High, dimmed, torch. Battery life: up to 10hrs. Battery life indicator. Supplied with USB cable and 3-pin wall plug.

EMC, RoHS, WEEE

Item No.	i	☐
T9422R	420Lm	3



**LED Pocket Inspection Light CBOX**

12pcs in a box . 8 Super bright LEDs. Wide flood beam. 180° rotating magnetic pocket clip. Water & dirt resistant, tested to IP64. Battery life: 8 hrs. Battery: 3 x AAA (Not supplied).

EMC, RoHS, WEEE

Item No.	↔
T9410CBOX	160 x 26mm



## Corded Inspection Lamps

Heavy duty steel cage & glass for damage protection. Rubber grip for safe handling. Suspension hook. 5m cable for long reach access. Max 60W 240V. Bulb not included. 2-pole Euro Plug.

LDV, EMS, RoHS, WEEE

Item No.	i	📦
T5901A	Euro 2 pin plug	1



## 10W Rechargeable Site Light

High Power COB LED. 700 Lumens /colour temp 6500 Kelvin. 2 Lighting modes: High, Dimmed. Battery life: High: 2.5hrs, Dimmed: 4hrs. 3 hours approximate charge time. 360° adjustable head directs the light where you need it. Impact resistant, tested to IK05. Water & dirt resistant, tested to IP65. Including rechargeable 3.7V 2200mAh Li-Ion battery.

EMC, RoHS, WEEE

Item No.	📦
T9735USB	1

## Site Lights



## COB Power Tool Battery Site Lights

High powered site light with adjustable LED. Heavy duty IK08 rated design for increased impact resistance. Tactile on/off switch with +/- brightness function. CKlearView LED for accurate colour rendering. 4 x selectable power output (5000, 3750, 2500 and 1250lm). Integrated pivot stand to adjust working angle. IP65 rated against dust and water ingress. Threaded base for tripod mounting. Battery level indicator. Compatible with standard 18V power tool batteries using the included adaptors (eg. Bosch, Dewalt, Makita, Metabo and Milwaukee).

Item No.	i	📦
T9740	5000lm	2
T9741	10000lm	2



## 15W Rechargeable Flood Light

15W Rechargeable LED Flood Light 1300 Lumens High Power LED light source. Can be used as a free standing floodlight or clamped on using the strong integral clamp. 120° wide flood beam angle. 4.5 hours approximate charge time. Battery life: High Power up to 2.5 hours. Low Power up to 7.5 hours. 360° swivel head directs the light where you need it. IP54 Rated: Water & dirt resistant.

LDV, EMC, RoHS, WEEE

Item No.	📏	i	📦
T9715R	190 x 140 x 260mm	1300Lm	8

## 10W Flood Light Mains Charger

High performance 600 lumen Epistar COB LED. Power: 10W. Wide 120° flood beam. Magnetic base. Vertical and horizontal rotation. Water & dirt resistant. Battery life: 3 hours.

LDV, EMC, RoHS, WEEE

Item No.	📏	📦
T9710RMC	147 x 168 x 240mm	1



## 24W Bluetooth Flood Light

LED rechargeable outdoor floodlight with 3 adjustable light panels containing 24 high power SMD LEDs. The floodlight is designed to promote user convenience and interactivity, with a Bluetooth switch control and accompanying app allowing the lights to be controlled from a mobile phone. The product features a USB output port for charging devices, along with a battery charge indicator.

CE certified

Item No.
T9724R





Head Torches



Wide Field Headlight

The C.K T9630 USB head light is ideal for the end user working in dark & confined spaces where quality of light is important. COB LED Technology. 400 Lumens, 5,700K and CRI 80. 4 mode operation: Spot Light / Wide Field / Full Beam / Dipped Beam. Rear Flashing Red Light. Up to 6 Hours Runtime. Charge Time: 3 hours. IP-54 Rated. IK-07 Impact Rated. Charging Indicator Light.

EMC, RoHS, WEEE, IP54

Item No.

T9630USB



Head Torch with Motion Sensor

T9613: High Power Cree LED. 220 Lumens. 7 Lighting modes: High, Dimmed, Red, COB, COB & Main, COB & Low Light, COB & Red Beam. Battery life: High: 4hrs, Low: 9hrs, Red beam: 5hrs, COB: 9hrs, Main & COB: 135 minutes. Sensor mode switching ability. Adjustable head lamp swivels through 80°. Impact resistant, tested to IK05. Water & dirt resistant, tested to IPX4. Maximum range: 90m. Battery 3 x AAA (Not supplied). T9613USB: High Power Cree LED. 270 Lumens. 7 Lighting modes: High, Dimmed, Red, COB, COB & Main, COB & Low Light, COB & Red Beam. Battery life: High: 4hrs, Low: 9hrs, Red beam: 6hrs, COB: 9hrs, Main & COB: 135 minutes. Sensor mode switching ability. Adjustable head lamp swivels through 80°. Impact resistant, tested to IK05. Water & dirt resistant, tested to IPX4. Maximum range: 90m. Including high performance 3.7V 1800mAh Lithium-Ion rechargeable battery, USB cable.

EMC, RoHS, WEEE, IPX4

Item No.

T9613



1

T9613USB

1



Head Torch with Rear Red Light

High Power 150 Lumen Cree XP-G LED. 3 Lighting modes: high, dimmed, red. Rear red LED safety light. Adjustable head lamp swivels though 80°. Water & dirt resistant, tested to IPX0. Detachable over-head elasticated strap. Battery life: high - 6hrs, dimmed - 12hrs. Battery 3 x AAA (Not supplied).

EMC, RoHS, WEEE, IP54

Item No.

T9612



150Lm



3



Beanie Hat - USB Rechargeable

Stylish Beanie hat with integrated USB rechargeable 80 Lumen head torch.

EMC, RoHS, WEEE

Item No.

T9608BHR



10



LED Head Torch USB - Twin Pack

SMD LED Technology. 80 Lumens. Light modes: High / Medium / Low. Runtime: High: 2 hours, Medium: 3 hours, Low: 4 hours. Charge Time: 3.5 hours. Impact resistance: 1m. Maximum Range Distance: 10m. Battery: 3.7V 300mAh Li-ion.

EMC, RoHS, WEEE

Item No.

T9608R2



1