

Cable markers CLI TM 10-33

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



CLI TM is the right sleeve for large conductor cross-sections. The sleeve's transparent pocket protects the inlay tags against environmental influences. Cable ties are used to fix the transparent CLI TM sleeve in place. Marking is carried out with TM-I 18 for CLI TM 10/33 or ESG 9/17 for CLI TM20/33. Both inlay tags are designed in the proven MultiCard format and can be comfortably labelled with SMark laser, PrintJet, plotter or MC-Mobilo. The CLI F 2/17,5 tag is suitable for CLI TM 20/66.

- Secure attachment with cable ties
- Professional labelling thanks to Weidmüller's marking devices for MultiCards

General ordering data

Type	CLI TM 10-33
Order No.	1763270000
Version	Cable markers, 33 x 6 mm, PVC, Colour: Transparent
GTIN (EAN)	4032248050239
Qty.	100 pc(s).

Cable markers CLI TM 10-33

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	33 mm	Width	6 mm
Height	5 mm	Depth	5 mm
Net weight	0.2 g		

General data

Colour	Transparent	Material	PVC
Operating temperature range, max.	60 °C	Operating temperature range, min.	-30 °C
Recommended industries	Process, Machinery	Type of printing	blank
UL 94 flammability rating	V-0		

Conductor and cable markers

Conductor O.D., max.	317 mm	Conductor O.D., min.	10 mm
Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²
Halogen	Yes		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform