

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2153481115](#)
Status: **Active**
Overview: Off-the-Shelf Pre-Crimped Leads
Description: Pre-Crimped Lead Squba 3.6 Male-to-Pigtail, Tin (Sn) Plating, 450.00mm Length, 18 AWG, Black

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	215348
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Squba-to-Pigtail
Overview	<u>Off-the-Shelf Pre-Crimped Leads</u>
Product Name	Squba
UPC	195842349902

Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Male-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Resin	Modified Polystyrene
Net Weight	4.359/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	3.60mm
Plating min - Mating	2.540µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.90mm-2.40mm
Wire Size AWG	18
Wire/Cable Type	UL 11028

Electrical

Current - Maximum per Contact	11.5A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Sales Drawing	2153481111-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[215348 Series](#)