

Product data sheet

Characteristics

NSYEB1510D6

Earth braids section 10mm², length 150mm, eyelet hole 6,4mm. Packaging unit: 10.



Main

Range	Spacial
Anwendung	Multi-purpose
Product or component type	Earthing braid
Device composition	1 braid
Quantity per set	Set of 10

Complementary

Material	Tinned copper
Fixing mode	Nut and washer - on earth connection location
Length	150 mm
Width	17 mm
Nominal cross section	10 mm ²
Diameter	6.5 mm

Packing Units

Package 1 Weight	0.018 kg
------------------	----------

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Contractual warranty

Warranty	18 months
----------	-----------
