

RtecX1 SP+N RCBOs


RtecX1 features live disconnect, single pole switching and dual pole sensing with solid neutral. Functional earth connection is required to ensure correct operation in case of neutral failure.



RtecX1 RCBO Technical Specification:

Rated Current	6, 10, 16, 20, 25, 32, 40A
Rated Voltage (U _n)	110Vac - 230Vac
Number of Poles	2 or 4
Electrical Life	4000 Switching Operations
Rated Residual Operating Current (I _n)	4000 Switching Operations
Rated Short Circuit Capacity (I _{nc})	10kA
Overload tripping	Trip Curves Type B and C

RtecX1 Ordering Scheme:



NOTE: Techna's RtecX1 fits in DtecOP Distribution Boards. For more information please see page 40.