


Note:
 RoHS 2.0 AND REACH Compliant
 Test:
 Grade Designation: Each to Reference



Type	Multi-Mode
Insertion Loss	≤ 0.2dB
Return Loss	≤ 60dB
Test Wavelength	1310nm

MATERIAL LIST:

NO.	SPECIFICATION STANDARD	QT' Y	REMARK	ITEM NO.	DESC.
⑥	Fiber Optical Cable Yellow OS2 G657. A2 9/125um Duplex ø3.0*6.0mm LSZH	L		21.15.9500	ROLINE FO Jumper Cable LSH-LSH, APC, Duplex, 9/125um, OS2, 0.5m
⑤	Black Heat Shrink Tube	2pcs		21.15.9501	ROLINE FO Jumper Cable LSH-LSH, APC, Duplex, 9/125um, OS2, 1m
④	Ring 1, 2	4pcs		21.15.9502	ROLINE FO Jumper Cable LSH-LSH, APC, Duplex, 9/125um, OS2, 2m
③	LSH 3.0 Boot Green	4pcs		21.15.9503	ROLINE FO Jumper Cable LSH-LSH, APC, Duplex, 9/125um, OS2, 3m
②	LSH Connector Green	4pcs		21.15.9505	ROLINE FO Jumper Cable LSH-LSH, APC, Duplex, 9/125um, OS2, 5m
①	LSH Metal Dust Cap	2pcs		21.15.9506	ROLINE FO Jumper Cable LSH-LSH, APC, Duplex, 9/125um, OS2, 7.5m
				21.15.9507	ROLINE FO Jumper Cable LSH-LSH, APC, Duplex, 9/125um, OS2, 10m
BY	CHK	NEW	2018-05-07		
		REVISION RECORD MODIFICATIONS	DATE		

