



Overview

Lead time	Usually Ships within 4 Weeks
-----------	------------------------------

Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Power range	150 W
Input voltage	110...250 V AC 50/60 Hz

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...158 °F (-40...70 °C)
IP degree of protection	IP20
Product certifications	VDE UL
Material	Body extruded aluminium
Height	11.22 in (285 mm)
Width	80 mm
Depth	2.76 in (70 mm)
Condition of use	Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed
Fixing mode	By clips
Mounting support	35 mm DIN rail

Ordering and shipping details

GTIN	03606480152221
Nbr. of units in pkg.	1
Package weight(Lbs)	28.32 oz (803 g)

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.76 in (7 cm)
Package 1 width	3.15 in (8 cm)
Package 1 Length	11.22 in (28.5 cm)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------