

iiyama TH5563MIS-B1AG Signage-Display Digital Signage Flachbildschirm 139,7 cm (55") LED 450 cd/m² Full HD Schwarz Touchscreen

Marke : iiyama

Artikel-Code: TH5563MIS-B1AG

Produktname : TH5563MIS-B1AG



iiyama TH5563MIS-B1AG. Produktdesign: Digital Signage Flachbildschirm. Bildschirmdiagonale: 139,7 cm (55"), Bildschirmtechnologie: LED, Display-Auflösung: 1920 x 1080 Pixel, Helligkeit: 450 cd/m², HD-Typ: Full HD, Touchscreen. Produktfarbe: Schwarz



Bildschirm

Bildschirmdiagonale *	139,7 cm (55")
Bildschirmtechnologie *	LED
Display-Auflösung *	1920 x 1080 Pixel
Helligkeit *	450 cd/m ²
HD-Typ *	Full HD
Touchscreen *	✓
Natives Seitenverhältnis	16:9
Reaktionszeit	12 ms
Kontrastverhältnis	1300:1
Bildwinkel, horizontal	178°
Bildwinkel, vertikal	178°
Anzahl der Farben des Displays	1,073 Milliarden Farben
Pixel Abstand	0,63 x 0,63 mm
Aktiver Displaybereich (B x H)	680,4 x 1209,6 mm
Bildschirmdiagonale (cm)	140 cm
Horizontaler Scanbereich	30 - 75 kHz
Vertikaler Scanbereich	50 - 75 Hz

Anschlüsse und Schnittstellen

Anzahl HDMI-Anschlüsse *	1
Anzahl HDMI-Eingangsschnittstellen	1
DVI Anschluss *	✓
Anzahl DVI-D-Anschlüsse	1
VGA (D-Sub)-Eingangsanschlüsse	1
USB Anschluss *	✓
USB-Version	2.0
Ethernet/LAN *	✗
Komponenteneingang Video (YPbPr/YCbCr)	1
Komponentenausgang Video (YPbPr/YCbCr)	1
Audioeingang (L, R)	2
Audio (L,R) Out	1
PC Audio-Eingang	✓
RS232	✓
RS-232C	✓
Infrarotport	✓

Audio

Eingebaute Lautsprecher *	✓
Anzahl eingebauter Lautsprecher	2
RMS-Leistung	24 W

Design

Produktdesign *	Digital Signage Flachbildschirm
Ausrichtung	Horizontal/Vertikal
Produktfarbe *	Schwarz
VESA-Halterung *	✓
Panel-Montage-Schnittstelle	400 x 200 mm

Leistungen

TV Tuner integriert	✗
Bild-in-Bild	✓
On-Screen-Display (OSD)	✓
Anzahl OSD-Sprachen	7
Menüsprachen	Deutsch, Niederländisch, Englisch, Spanisch, Französisch, Polnisch, Russisch
HDCP	✓

Energie

Stromverbrauch (Standardbetrieb) *	136 W
Stromverbrauch (Standby) *	0,5 W
AC Eingangsspannung	100 - 240 V
AC Eingangsfrequenz	50 - 60 Hz

Computersystem

Computersystem *	✗
------------------	---

Gewicht und Abmessungen

Breite	1273 mm
Tiefe	96 mm
Höhe	743,5 mm
Gewicht	45 kg

Lieferumfang

Fernbedienung enthalten	✓
Mitgelieferte Kabel	AC, VGA

Zertifikate

Zertifizierung CE, TÜV-Bauart, CB

Sonstige Funktionen

S-Video-Ausgang	✓
Audio-System	stereo
Schnellstartübersicht	✓
Separate H/V-Sync	✓

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 09-APR-2024. Prints or copies of Information are only valid on the printed Publication date