


Electrical Test:

1. 100%Test (Open , short , miss wire)
2. Contact Resistance: 3 ohm(max).
3. Insulation Resistance: DC 300V/10ms, 10M ohm(MIN)

接线PIN位



9	A6-0000099	DisplayPort M TRANSPARENT dust cover	2	pcs							
8	A5-R047001	45P PVC ROHS	12	g							
7	A5-R047011	TRANSPARENT PE	5	g							
6	A6-R104405	DisplayPort Port M Shell Plated Nickel AFTER	2	pcs							
5	A6-R104406	DisplayPort Port M Shell Plated Nickel Before	2	pcs							
4	A6-R104407	DisplayPort Port M ABS shell down	2	pcs							
3	A6-R104408	DisplayPort Port M ABS shell up	2	pcs							
2	A2-R028354	DisplayPort M BLACK INSULATION, Shell Plated nickel, PIN 5u"	2	pcs							
1	A0010303-00251	DP1.4~[28AWG(7/0.127TC)+EAM]*5P+28AWG(7/0.127TC)*4C+AEB(16/10/0.12AL 85%)OD:7.3MM~ Black~mark:DisplayPort Cable E342987 兄 AWM STYLE 20276 80°C 30V VW-1	0.5	m							
NO	ITEM	DESCRIPTION	Q'TY	UNIT							
					REV.	ECN NO.	DESCRIPTION	DATE	NAME		
						TOLERANCE					
						INCHES	M/M				
						.X	.015	.30			
						.XX	.010	.10	TITLE:		
						.XXX	.005	.05	Display Port 1.4 M TO M 28AWG		
					DRAWN BY	王志斌		CUSTOMER :		Element14	
					CHECK BY			CUSTOMER P/N:		PSG91493	
					APPD BY			SCALE	NONE	DRAWING NO:	REV A1
								UNIT	MM		
								DATE	2018.08.29	C04180-00283	1/1