


Common Mode Choke

TCK-138


Order Code	TCK-138	
Inductance (each winding)	16.1 μH ±25% (at 100 kHz / 1 V)	
Impedance (DCR)	11 mΩ max.	
Rated Current	1.44 A max.	
Rated Voltage	500 VDC max. (between windings)	
Operating Temperature	-40°C to +105°C	



Impedance Curve



Outline Dimensions



Dimensions [mm]	
Α	6.5 ±0.3
В	6.0 ±0.2
С	4.5 max.
D	4.3
E	7.7
F	0.91
G	3.0



Specifications can be changed without notice.