

## Circular cutter, type 00

for diameter range from 30-200 mm

### Application:


For drilling holes in the diameter range from 30 to 200 mm up to a max. material thickness of 30 mm in steel, non-ferrous metals, seals, rubber, leather and similar materials.

### Execution:

- steel circular cutter with cutter holder and cutter, HSS, type 422

### Advantage:

- universal use for a multitude of materials
- possible to create cost-effective holes in a large diameter range
- excellent cutting properties and high degree of cutting precision



<b>Art. no.</b>	<b>11350 141</b>
<b>Brand</b>	GFS
<b>Manufacturer Part Number</b>	21 011 003
<b>Type</b>	Type 00 with cutter, type 422 HSSE
<b>Suitable for min. diameter</b>	30 mm
<b>Morse taper size</b>	MK 3
<b>Gross Weight</b>	0.927 kg
<b>Product Group</b>	119