

Nuts

For T-grooves




Application:

For clamping in T-grooves.

Version:

- Ref. no. 010- 130 tempered, strength class 10
- Ref. no. 220- 310 tempered, strength class 10, long form



Art. no.	26195 100
Type	standard
Nominal dimension of groove	24 mm
Slot nut width	23.7 mm
Thread dimension	M22
Length	40 mm
Height	32 mm
Slot nut height	16 mm
DIN	508

EAN-Code

4020772080099