

## Adjustable crocodile clamp

With counter-holder



### Application:


The crocodile is used with all clamping tasks where clamping is achieved using T-grooves and tapped holes.

### Execution:

- Tempered and galvanised
- Variable and quick adjustment
- The captive thrust piece and counter-holder are connected to the adjustable clamp (cannot be lost).
- Particularly suitable for use on injection moulding machines and presses
- Accessories facilitate variable adjustment of the clamping height
- Infinitely variable adjustment of clamping height

### Advantage:

- Captive thrust piece connected to the adjustable clamp (cannot be lost), crocodile can therefore be used quickly and flexibly
- Heights are quickly overcome and packing the underside of the adjustable clamp does not present a problem
- Accessories facilitate variable adjustment of the clamping height



<b>Art. no.</b>	<b>26224 010</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	79756
<b>Size</b>	1
<b>Suitable T-groove width</b>	10 mm, 12 mm, 14 mm
<b>Tension force</b>	30 kN
<b>Min./max. adjustment range</b>	0-55 mm
<b>Length</b>	115 mm
<b>Width</b>	44 mm
<b>Height</b>	27 mm
<b>Thickness</b>	17 mm
<b>Bore diameter</b>	13 mm
<b>Gross Weight</b>	0.655 kg
<b>Product Group</b>	260

### EAN

4020772079758