

Micrometer

Adjustable anvil

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:


- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces
- Spindle travel 50 mm

Advantage:

- Sturdy, robust and lightweight construction for large measurement ranges

Delivery:

Includes box, two setting standards



| | |
|---|------------------|
| Art. no. | 32016 129 |
| Brand | MITUTOYO |
| Manufacturer Part Number | 105-419 |
| Min./max. length measuring range | 1200-1400 mm |
| Vernier scale | 0.01 mm |
| Measuring surface diameter | 8 mm |
| Measuring spindle increments | 0.5 mm |
| Spindle clamping | Yes |
| Error limit | 25 µm |
| Display | Nonius |
| Min./max. measurement force | 5-10 N |
| Calibration Group | D |
| Gross Weight | 15.770 kg |
| Product Group | 3MA |

EAN

4946368007670