

Hardness reference plates, HV test procedure - macro

Includes DAkkS certificate

ATORN[®]

Application

For indirect and periodic checking of functionality and measurement inaccuracy of hardness testers in line with the HV test method.

Version

- Fine-grained, homogeneous steel
- DAkkS certificate

Art. No.	42367 266
Hardness test method	Vickers
Testing method	HV 10
Hardness value	540
Form	Triangular
Dimension hardness comparison plate	70 x 70 x 70 x 6 mm
Surface	Polished
ISO	DIN EN ISO 6507-3
Material	Steel



EAN-Code

4050293719130