

META CLIP boltless rack with shelves

Load capacity per bay 100/230 kg, zinc plated



Application:

Universal rack system for all storage applications, quick setup or conversion through simple plugging of the shelves, can be assembled without tools.

Execution:

- Double-row boltless rack with pre-assembled frame = clinched frame
- Both rows securely connected on the back
- Shelves height-adjustable, spacing 25 mm
- Shelves with a 50 mm hole grid to accommodate accessories
- Basic rack planning dimensions: Nominal length + 56 mm, 2 x nominal depth + 75 mm

Advantage:

- Quick plug-in assembly without tools
- Stable and reliable
- Different versions available



Art. no.	50167 719
Brand	META
Manufacturer Part Number	20070754
Height	2500 mm
Length	1356 mm
Depth	836 mm
Nominal length	1300 mm
Nominal depth	800 mm
Design	Double-sided
Type of assembly	To insert
Surface	Zinc plated
ESD-capable	No
Design of the frame	Pre-assembled
Grid dimension	25 mm
Number of shelves	5 PCS
Load-carrying capacity per shelf	230 kg
Load-carrying capacity per field	2350 kg
Number of frame	2 PCS
Number of lines	2 PCS
Quality label	RAL-RG 6 14/ 1
Made in	Germany
Material	Steel
Gross Weight	134.080 kg
Product Group	508

EAN

40262 12 102383