


TRMS DIGITAL MULTIMETER 2000Vdc

DMM4500PV



- Multimeter suitable for industrial, HVAC and solar applications
- TRMS measurements
- 6000 counts display
- 2000 V DC / 1500 V AC
- 10 A AC/DC capability
- Resistance, diode, capacitance and frequency measurements
- Temperature measurement (°C/°F)
- Non-contact voltage detection
- Low-pass filter function
- Low impedance mode
- Automatic range
- Data logging
- Bluetooth connectivity with "KPS Link" application
- CAT IV 600V/CAT III 1000V safety standards



DMM4500PV

TRMS DIGITAL MULTIMETER 2000Vdc

Información General	
Display	6000 counts
Auto Power Off	✓
Backlight	✓
Bargraph	✓
Relative measurements	✓
HOLD	✓
HFR (low pass filter)	✓
Continuity and diode test	✓
Auto-range	✓
MIX/MAX	✓
ZERO	✓
Non-contact Voltage detection	✓
Connectivity	Bluetooth
Datalogging	4000
Dimensions	74x156x44mm
Torch	✓
Weight	250g
Batteries	NEDA 15A/IEC LR6, 2*1,5V
Standars	EC 61010-1, IEC/EN61010-2-033
Safety rating	CAT IV 600V, CAT III 1000V
Accesories included	Test leads, PV test leads, thermocouple, batteries, user manual

DMM4500PV

TRMS DIGITAL MULTIMETER 2000Vdc

Specifications	
TRMS	✓
DC Voltage (mV)	600mV
DC Voltage (V)	1000V
PV Voltage (Vdc)	2000V
AC Voltage (V)	1000V
PV Voltage (Vac)	1500V
DC current	10A
AC current	10A
Frequency	100kHz
Resistance	40MΩ
Diode	1,5V
Capacitance	10mF
Temperature	-40°C - 400°C

Product Code Information	
SKU	KPSDMM4500PVCBINT
EAN code	8435394784724
UPC code	810053676639
Uds/box	15