# LAD6K10B

# CONTACTOR MECH. LATCH CONTACT BLOCK IEC





#### Main

Range	TeSys
Product or component type	Mechanical latch block
Product compatibility	LC1D09D38 LC1D40AD65A LC1DT20DT40 LC1DT60ADT80A TeSys D control relays
[Uc] control circuit voltage	24 V AC 50/60 Hz 24 V DC

### Complementary

Mounting location	Front side	
Tripping control	Electrical Manual	
[Ui] rated insulation voltage	690 V - conforming to IEC 60947-5-1	
Power required in VA	25 for AC circuit	
Power required in W	30 W for DC circuit	
Mechanical durability	500000 cycles	
Operating rate	1200 cyc/h	
On-load factor	10 %	
Product weight	0.07 kg	

#### **Environment**

		(
product certifications	CSA UL	
IP degree of protection	IP2x conforming to VDE 0106	
protective treatment	TH conforming to IEC 60068	
ambient air temperature for operation	-2555 °C	
ambient air temperature for storage	-4080 °C	

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0629 - Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations