

**2755 / 2755B / GH275
GH435 / GH755
GH810 (-6 to -10)**

**Nipples without
wire trap**

**Nippel ohne
Ausreiß-
sicherung**


**Nipples sans
gorge pour
nappes**

**Nipples senza
protezione da
strappo**

**Manguitos
roscados sin
seguro de
arranque**

2755(B) / GH275 / GH435 / GH810 (-6 to -10)

GH755



DS

**DKO Female Swivel, Heavy Duty
Dichtkopf DKOS, schwere Baureihe
DKO série S
Femmina girevole DKOS, serie pesante
Hembra loca DKOS, serie pesada**

Part Number Skive Steel	Part Number Skive Stainless Steel	Part Number TTC Steel	Part Number TTC Stainless Steel	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E mm	K Ø mm	HEX [1]	HEX [2]
41.721-12-6*	41.721-12-6BA*	1T8DS6**	1T8DS6BA**	M20x1,5		12	10	-6	58,2	28,7		6,5		24	
41.721-14-6				M22x1,5		14	10	-6	61,2	28,0		6,5		27	
41.721-16-8*	41.721-16-8BA*	1T12DS8**	1T12DS8BA**	M24x1,5		16	12	-8	65,0	32,0		9,0		30	
41.721-16-10*		1T12DS10**		M24x1,5		16	16	-10	68,5	31,9		11,0		30	27
41.721-20-10* ***		1T16DS10**	1T16DS10BA**	M30x2,0		20	16	-10	73,3	36,7		12,0		36	
41.721-25-12* ***	41.721-25-12BA*	1T20DS12**	1T20DS12BA**	M36x2,0		25	19	-12	77,5	40,5		15,0		46	
41.721-30-16* ***		1T25DS16**	1T25DS16BA**	M42x2,0		30	25	-16	83,3	42,8		20,0		50	

*** With VITON O-Ring, add "VI"

*** Mit VITON O-Ring, füge "VI" hinzu



*** Avec VITON O-Ring, ajouter "VI"

*** Con VITON O-Ring, apportare "VI"

*** Con VITON O-Ring, agregar "VI"

2755(B) / GH275 / GH435 / GH810 (-6 to -10)

GH755



DSA

**DKO Female Swivel, Heavy Duty, 45° Elbow
Dichtkopf DKOS, schwere Baureihe, 45° Krümmer
DKO série S coude 45°
Femmina girevole DKOS a 45°, serie pesante
Hembra loca DKOS acodado a 45°, serie pesada**

Part Number Skive Steel	Part Number Skive Stainless Steel	Part Number TTC Steel	Part Number TTC Stainless Steel	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E mm	K Ø mm	HEX [1]	HEX [2]
41.839-12-6*	41.839-12-6BA*	1T8DSA6**		M20x1,5		12	10	-6	73,1	43,6	17,1	6,5		24	
41.839-14-6*				M22x1,5		14	10	-6	73,7	44,2	18,2	6,5		27	
41.839-16-8*	41.839-16-8BA*	1T12DSA8**	1T12DSA8BA**	M24x1,5		16	12	-8	96,0	63,0	28,5	9,0		30	
41.839-20-10*	41.839-20-10BA*	1T16DSA10**	1T16DSA10BA**	M30x2,0		20	16	-10	105,5	68,9	31,0	12,0		36	
41.839-25-12*	41.839-25-12BA*	1T20DSA12**	1T20DSA12BA**	M36x2,0		25	19	-12	121,9	84,9	36,0	15,0		46	
41.839-30-16*	41.839-30-16BA*	1T25DSA16**	1T25DSA16BA**	M42x2,0		30	25	-16	134,0	93,5	41,8	20,0		50	

* Sockets must be ordered separately.

* Fassungen müssen separat bestellt werden.

* Les jupes doivent être commandées sep.

* Le boccole devono essere ordinate sep.

* Los manguitos tienen que pedirse por separado.

** Part numbers include sockets.

** Teil-Nr. beinhaltet Fassung.

** L'embout-Nr. avec la jupe.

** Part Number include la boccola.

** Los números de parte incluyen los manguitos.