



**Part no.: 50133387**  
**KSS ET-M12-8A-RJ45-A-P7-050**  
**Interconnection cable**



Figure can vary

## Contents

- Technical data
- Electrical connection

Part no.: 50133387 – KSS ET-M12-8A-RJ45-A-P7-050 – Interconnection cable

## Technical data

### Basic data

Suitable for interface Ethernet

### Electrical data

#### Performance data

### Connection

#### Connection 1

Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	8 -pin
Encoding	X-coded
Design	Axial

#### Connection 2

Type of connection	RJ45
No. of pins	8 -pin
Design	Axial
Type	Male

#### Cable properties

Number of conductors	8 Piece(s)
Sheathing color	Black
Shielded	Yes
Silicone-free	Yes
Cable design	Interconnection cable
Cable length	5,000 mm
Sheathing material	PUR

### Mechanical data

Width across flats 13 mm

### Environmental data

Ambient temperature, operation, flexible use -40 ... 80 °C

### Certifications


Degree of protection IP 67

### Classification

Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

## Electrical connection

Connection 1	
Type of connection	Connector
Thread size	M12
Type	Male
No. of pins	8 -pin
Encoding	X-coded
Design	Axial



Connection 2	
Type of connection	RJ45

