



FCxx*1)POG1

e.g. FC15POG1

RoHS compliant

*1) xx No. of contacts 09, 15, 25 or 37

xx	A [mm]	B [mm]	C [mm]
09	30.8	16.9	25
15	39.1	25.2	33.3
25	53	38.9	47.04
37	69.3	55.3	63.5

4	xx	Signal contact	P36 / Brass / AWG 20	G1 / C-Filter 1nF -20/+80%
3	1	Shell	Steel	tin plated
2	1	Sealing compound	Epoxy resin (-55°C - +85°C)	black
1	1	Insulator	Plastic	black
No. St.	Type Description/Material			
<small>Measurement without tolerance to ISO 2768-m</small> <small>NAME / DATE</small> <small>19-10-2005</small> <small>DRAWN</small> <small>CHECKED</small> <small>16-12-2009</small>				
SCALE 2:1				
TITLE				
D-Sub Filter-Connector				
DWG.NO.				FCxxPOG1
REV.				3

3	01-12-2009	22216		
2	04-07-2006	21767		
1				
REV.	DATE	CH.-NO.	REPLACEMENT FOR:	PAGES
			FCxxPOG1 b	1

