

Product information

68 01 200

End Cutting Nipper

DIN ISO 5748

- The head shape provides optimised movement when tightening steel mesh knots during reinforced concrete work
- With cutting edges for soft and hard wire
- Also suitable for twisting and cutting binding wire
- Cutting edges additionally hardened; cutting edge hardness approx. 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened



General	
Article No.	68 01 200
EAN	4003773013815
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	319 g
Dimensions	200 x 50 x 16 mm
Standard	DIN ISO 5748
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities soft wire (diameter)	Ø 4.0 mm
Cutting capacities medium hard wire (diameter)	Ø 3.5 mm
Cutting capacities hard wire (diameter)	Ø 2.8 mm
Cutting edge length mm (C)	31 mm

technical change and errors excepted

