



## Toggle switches

### 9041.0201

<b>Product number</b>	<b>9041.0201</b>
<b>Business unit</b>	Switches, Sensors & Controls
<b>Product family</b>	Toggle switches
<b>Actuation type</b>	direct
<b>Packing unit</b>	100
<b>ROHS conform</b>	yes
<b>Output</b>	catalogue miniature switch
<b>Switching function</b>	Changeover switch with OFF position in the center (DPDT - Center OFF)
<b>Material fixed contact</b>	Ag
<b>Contact system</b>	Electrical life 50000
<b>Number of poles</b>	2 - pole
<b>connections</b>	Solder terminal, sealed
<b>Mechanical life endurance</b>	100000
<b>Rating IEC</b>	4 A 30 V DC 5 A 48 V AC
<b>Contact resistance (new condition)</b>	< 20 mOhm
<b>Insulation resistance (new condition)</b>	> 1000 MOhm
<b>Voltage strength at 250 V</b>	small contact distance > 1000 V
<b>Ambient temperature</b>	-25 °C ... +70 °C
<b>Actuators and additional actuators</b>	lever: CuZn chrome-plated
<b>Housing description</b>	bracket plate: stainless steel
	base plate: DAP, olivegreen
	threaded socket: CuZn nickel-plated, hexagonal nuts of nickel-plated CuZn
<b>Connection surface</b>	bearing connection silver plated
	external connection silver plated
<b>Contact material</b>	Ag
<b>Contact type</b>	lifting contact
<b>Miscellaneous</b>	locking ring and toothed washer of galvanised and chromated steel
<b>Type of fastening</b>	central fastening M6 x 0.75

Technical changes reserved. Dimensions are not binding.

Detailed specifications available on request.