
PRODUCT-DETAILS

FLB0430

LT-PVC FLEX CONDUIT 20MM 30M BLK



General Information

Extended Product Type	FLB0430
Product ID	7TCA297020R0097
EAN	5011949202634
Catalog Description	LT-PVC FLEX CONDUIT 20MM 30M BLK
Long Description	Liquid Tight, Medium Flexibility Conduit, Nominal Conduit Size 20mm, 1/2 Inch US Trade Size, Outside Diameter 21.1mm, Inside Diameter 15.9mm, Static Bend Radius 80mm, Reel Length 30 Meters, Galvanised Steel Core, String Packing, PVC Covering, Black

Ordering

EAN	5011949202634
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	24.69 lb 11.197 kg
--------------------	-----------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

Additional Information

Application	Indoors/Outdoors, Marine, Buildings, Infrastructure
Brand / Label	Kopex
Color	Black
Flexibility	Medium
Inside Diameter	15.9 mm
Material	Galvanized Steel Core with String Packing and PVC Covering
Nominal Size	1/2 in NC20
Number of Batteries	0
Outside Diameter	21.1 mm
Product Name	flex metal conduit
Product Type	Liquid Tight Metallic Conduit
Radius	80 mm
Standards	BSI Kitemark KM-90009, Low Voltage Directive
UPC	786210276502

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	FLB0430
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	FLB0430

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

