

## Twist drill set in box, type N HSS, steam-treated

For universal use up to 1000 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

For drilling on hand-guided drills and CNC machines.

### Execution:

- Twist drill with universal standard geometry, roll forged

### Advantage:

- Long-term proven cutting geometry: excellent all-round properties and precise cutting behaviour
- Steam treatment ensures good adhesion to the drill and increases the service life



<b>Art. no.</b>	<b>11043 061</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11043061
<b>Composition of set</b>	1,0-10,5
<b>Pitch of drill diameter</b>	0.5 mm
<b>Number of pieces in assortment/set</b>	20 PCS
<b>Surface</b>	Vaporised
<b>Cutting material</b>	HSS
<b>Type</b>	N, roll forged
<b>DIN</b>	338
<b>Number of cutting edges</b>	2 PCS
<b>Gross Weight</b>	1.012 kg
<b>Product Group</b>	1AP

### EAN

4039247014729