

horizontal clamp with variable clamping height

with open clamping arm and angular base



Application:


Quick-action clamp with infinitely adjustable balancing function for workpieces with different clamping widths.

Version:

- galvanised and passivated.
- ergonomic, oil-resistant handle with large hand rest and soft components.
- protection against the loss of the clamping screw on the end of the clamping arm. complete with zinc-plated clamping bolt
- Size 20 clamping bolt M6 x 40 mm
- Size 50 clamping bolt M8 x 55 mm

Advantage:

- variable clamping height, for clamping different workpieces
- used for small lot sizes
- infinitely adjustable clamping force
- ergonomic 2 component handle
- protection against loss on clamping arm



Art. no.	26213 120
Size	50
Distance	8.2 mm
Basic length	85 mm
Min./max. length	20.5-30 mm
Drill hole	6.5 mm
Drill hole 2	6.5 mm
Length 2	40 mm
Length 3	31 mm
Height	88 mm
Overall height of lower handle	124 mm
Overall height of upper handle	158 mm
Max. adjustment range	30 mm
Min. adjustment range	1 mm
Thickness	13 mm
Distance 2	10.6 mm
Length	244 mm
Base plate width	57 mm
Hole distance 3	38.1 mm
Base plate length	51 mm
Tension force	3 kN
Height 2	13 mm

EAN-Code

402077200366 1