

Precision pointer

With rubber bellows

ATORN[®]

Application

For measuring lengths. Ideal for measuring instruments and flatness and straightness measurements

Version

- Impact-resistant
- Precision-guided measuring pin
- Connection for wire lifter
- Pointer fine adjustment
- Adjustable tolerance marks
- Measuring mechanism on ruby bearings
- suitable for internal precision measuring instruments
- With rubber bellows

Delivery

In case



Art. No.	33163 020
Calibration Group	K
Scale value	0.001 mm
Length measuring range	0.1 mm
Shaft diameter	8 mm
Shaft length	18 mm
Error limit	1.2 µm
With free stroke	Yes
Measurement force	1 N
Reversal error	0.5 µm
IP protection class	IP 53
Repeat accuracy	0.5 µm
DIN	879

EAN-Code

4050293156973

